



## Pliers for blind nuts with 2 arms

**359-22-N**

### SAM Outillage

10 rue Camille de RochetaillÃ©e  
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 08:51:13





## DESCRIPTION

### Pliers for blind nuts with 2 arms

Toggle-joint force multiplication system. Built-in return spring. Dia. M6 to M10: aluminium, steel and stainless steel nuts. Supplied with: anvils and threaded rods M6, M8 and M10, and tightening wrench.

## SPECIFIC DATA

Designation	TWO-ARM BLIND-NUT PLIERS
Sales reference	359-22-N
L (mm)	540
Weight (g)	4560
H (mm)	185

### SAM Outillage

10 rue Camille de RochetaillÃ©e  
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 08:51:13



Minimum openings (mm)	130
Maximum openings (mm)	520
Aluminium rivet maximum diameter mm	10
Steel rivet maximum diameter mm	10
Stainless steel rivet maximum diameter mm	10
Copper rivet maximum diameter mm	-
Guarantee	O   SAM TOOL guarantee.

**Guarantee applied****O | SAM TOOL guarantee.**

Guarantee without time limit on the tools used under normal conditions.

>> [Find out more](#)

**SAM Outillage**

10 rue Camille de RochetaillÃ©e  
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 08:51:13

