



Part Number : [2183360001](#)
Product Description : SW1 11.00mm Knurled Press-fit Locking Pin in Bag, 15.50mm Engagement Length
Series Number : 218336
Status : Active
Product Category : PCB Headers and Receptacles



Documents & Resources


Drawings
[2183360001_sd.pdf](#)

3D Models and Design Files
[2183360001_stp.zip](#)

Specifications
[2182310001-AS-000.pdf](#)
[2182310001-PS-000.pdf](#)
[2182310001-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not saleable
China RoHS	
EU ELV	Not saleable
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents
- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	218336
Description	SW1 11.00mm Knurled Press-fit Locking Pin in Bag, 15.50mm Engagement Length
Application	Power, Wire-to-Busbar
Component Type	PCB Header
Product Name	SW1
UPC	195842373396

Electrical

Current - Maximum per Contact	300.0A
Voltage - Maximum	1000V

Physical

Breakaway	No
Circuits (Loaded)	1
Circuits (maximum)	1
Diameter	11.00mm
Durability (mating cycles max)	50
Glow-Wire Capable	No
Height Above Board	15.50mm
Material - Metal	Copper Alloy
Material - Plating Mating	Silver
Material - Plating Termination	Silver
Net Weight	15.030/g
Number of Rows	1

Orientation	Vertical
Packaging Type	Bag
PCB Thickness - Recommended	1.50mm min.
Pitch - Mating Interface	N/A
Polarized to Mating Part	No
Polarized to PCB	No
Temperature Range - Operating	-40° to +125°C
Termination Interface Style	Press-Fit

This document was generated on Jan 28, 2025