




**Part Number :** [351500609](#)

**Product Description :** VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 6 Circuits, Natural, Glow-Wire Capable

**Series Number :** 35150

**Status :** Active

**Product Category :** Connector Housings



---

## Documents & Resources

### Drawings

[351500609\\_sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications

[351500000AS\\_ENG-000.pdf](#)

[351500000AS\\_KOR-000.pdf](#)


[PK-35150-005-001.pdf](#)

[PS-35150-003-001.pdf](#)

---

## Product Environment Compliance

### Compliance

|                    |   |
|--------------------|---|
| GADSL/IMDS         | Not Relevant  |
| China RoHS         | per SJ/T 11365-2006  |
| EU ELV             | Not Relevant  |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21  |
| REACH SVHC         | Not Contained per D(2025)4165-DC (25 June 2025)   |
| EU RoHS            | Compliant per EU 2015/863   |

## Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

## Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

## Part Details

### General

|              |   |
|--------------|---|
| Status       | Active  |
| Category     | Connector Housings  |
| Series       | 35150   |
| Description  | VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 6 Circuits, Natural, Glow-Wire Capable |
| Application  | Power, Wire-to-Wire   |
| Product Name | VersaBlade  |
| UPC          | 756054256732  |

### Agency

|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

### Physical

|                    |            |
|--------------------|------------|
| Circuits (maximum) | 6          |
| Color - Resin      | Natural    |
| Flammability       | 94V-0      |
| Gender             | Receptacle |

|                               |                |
|-------------------------------|----------------|
| Glow-Wire Capable             | Yes            |
| Keying to Mating Part         | None           |
| Lock to Mating Part           | Yes            |
| Material - Resin              | PET/PC         |
| Net Weight                    | 5.026/g        |
| Number of Rows                | 2              |
| Packaging Type                | Bag            |
| Panel Mount                   | No             |
| Pitch - Mating Interface      | 7.30mm         |
| Pitch - Termination Interface | 7.30mm         |
| Polarized to Mating Part      | Yes            |
| Stackable                     | No             |
| Temperature Range - Operating | -40° to +110°C |

---

## Mates With / Use With

### Mates with Part(s)

| Description                     | Part Number  |
|---------------------------------|--------------|
| VersaBlade Hybrid Plug Housings | <u>35151</u> |

### Use with Part(s)

| Description  | Part Number       |
|--|-------------------|
| VersaBlade Terminal Position Assurance (TPA) Retainer, 7.30mm Pitch, 3 Circuits, Natural | <u>351500390</u>  |
| VersaBlade Terminal Position Assurance (TPA) Retainer, 7.30mm Pitch, 3 Circuits, Red     | <u>351500392</u>  |
| VersaBlade Terminal Position Assurance (TPA) Retainer, 7.30mm Pitch, 3 Circuits, Yellow  | <u>351500393</u>  |
| VersaBlade Terminal Position Assurance (TPA) Retainer, 7.30mm Pitch, 3 Circuits, Blue    | <u>351500394</u>  |
| VersaBlade Male Crimp Terminal, 24-22 AWG, Type C  | <u>2270288400</u> |
| VersaBlade Female Crimp Terminal,  |                   |

|                                   |                   |
|-----------------------------------|-------------------|
| 24-22 AWG, Type C                 | <u>2270298400</u> |
| VersaBlade Male Crimp Terminals   | <u>35745</u>      |
| VersaBlade Female Crimp Terminals | <u>35746</u>      |
| VersaBlade Male Crimp Terminals   | <u>35747</u>      |

---

This document was generated on Sep 24, 2025