

Belt Sander LXT®

DBS180

18V • 600 – 1 700 m/min • 9 mm

Narrow tool for detail work

A light and easy-to-use belt sander powered by 18V LXT® battery. The belt speed can be adjusted between 600 – 1 700 m/min. This is an ideal tool for finishing, burr removal and working in confined areas. Movable LED light.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Brushless Motor	✓
Belt Speed	600 - 1700 m/min
Belt Size	9 x 533 mm
Sound Power Level (L _{WA})	88 dB(A)
Sound Pressure Level (L _{pA})	80 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	1,8 - 2,1 kg
Product Dimensions (L x W x H):	500 x 96 x 116 mm
Product net weight	1,4 kg
Angle range vertical	160 °
Vibration Level, Sanding Metal Plate	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Sanding Metal Plate	1,5 m/s ²
Vacuum cleaner connection Ø in / out	17/22 mm

User benefits

- Electric brake for maximum productivity and increased operator safety
- Variable speed control dial enables user to match the speed to the application for greater versatility
- Lock-on feature for continuous operation
- Brushless maintenance-free and long-life motor
- Movable LED
- Battery protection system automatically shuts off power when the battery level is low
- Compact to storage

Link to product - www.makitauk.com



Related products

Optional AC

122652-8

Dust nozzle Assembly



125158-5

Arm Assembly 9 mm



125159-3

Arm Assembly 13mm



140W02-3

Grip Base Complete



198043-5

Grip 36 set



Other

User manual

Parts drawing