

Product datasheet

Specifications



APC Easy UPS, 500VA, Floor/Wall Mount, 230V, 4x CEE 7/3 Schuko outlets, AVR

BV500I-GR

Overview

Lead time Usually in Stock

Main

Main Input Voltage	230 V AC 1 phase
Input Connection Type	Schuko CEE 7/7P
Input voltage limits	170...280 V
Network frequency	50/60 Hz +/- 5 Hz auto-sensing
Output voltage	230 V AC 1 phase
Rated power in W	300 W
rated power in VA	500 VA
Output connection type	4 Schuko CEE 7
Maximum configurable power in VA	500 VA
Maximum configurable power in W	300 W
Transfer time	6 ms typical : 10 ms maximum
UPS type	Line interactive
Wave type	Stepped approximation to a sinewave
Output frequency	50/60 Hz +/- 1 Hz unsynchronised

Complementary

Battery capacity	4.5 Ah
Battery type	Lead-acid internal included
Control panel	LED Status display with on line : on battery
Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm
Surge energy rate	156 J
Cable length	1.50 m
Number of cables	1
Colour	Black
Height	92.5 mm
Width	160.5 mm
Depth	305 mm
Net weight	3.9 kg



Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Mounting preference	No preference
Mounting mode	Not rack-mountable
Two post mountable	0
USB compatible	No
Mounting mode	Wall mount compact
Provided equipment	User manual
Number of power module filled slots	0
Number of power module free slots	0
Redundant	No
Range of product	Easy UPS
Product or component type	Uninterruptible power supply (UPS)

Environment

Product certifications	CE
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-20...50 °C
Storage altitude	0...15240 m
IP degree of protection	IP20
Relative humidity	0...90 %
Storage Relative Humidity	0...90 %
Acoustic level	40 dBA
Operating altitude	0...6667 ft

Batteries & Runtime

Run Time	View Runtime Graph 
Efficiency	View Efficiency Graph 
Battery type	Lead-acid battery
Battery voltage	12 V
Extended runtime	0
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	8 h
Battery life	3...5 year(s)

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	23.7 cm
Package 1 Width	37.3 cm

Package 1 Length	14.3 cm
Package 1 Weight	4.2 kg
SCC14	10731304338281
Pallet unit layers	5
Pallet layers	7

Contractual warranty

Warranty (in months)	24
-----------------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	150 kg CO2 eq.
Environmental Disclosure	Product Environmental Profile
Carbon footprint of the manufacturing phase [A1 to A3]	40 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0.4 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	108 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	0.4 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
SCIP Number	019b51cf-d7f1-4f06-ac85-1378fc94c7aa
REACH Regulation	REACH Declaration

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture


Recyclability potential, in %	62
End of life manual availability	End of Life Information
Removable battery	Yes
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Image of product / Alternate images

Alternative

