


Eaton 067731

Catalog Number: 067731

Eaton xEffect K-Type Terminal Enclosures Switch- & Controlgear Enclosure. Connection terminal, 800A, 4p, flat/round

General specifications



Product Name	Catalog Number
Eaton xEffect K-Type Terminal Enclosures Switch- & Controlgear Enclosure	067731
	EAN
	4015080677314
Product Length/Depth	Product Height
125 mm	140 mm
Product Width	Product Weight
294 mm	10.826 kg
Compliances	
RoHS conform	

Product specifications

Used with

General switchboard accessory
Accessory panel building

Special features

Conversion kits for strip terminal in cable connection available separately
Terminal covers available separately
Including labels for terminal marking U, V, W - X, Y, Z - L1, L2, L3 - T1, T2, T3 - PE, N, PEN, protective earth (ground) symbol
Relationship of rated operational current -terminal capacity to IEC/EN 60439, VDE 0660 Part 500 or EN 50021
Outer terminal for round or sectoral conductor, other side for Cu strip

Type

Accessory panel building
General switchboard accessory

Features

Contact safe

Accessory/spare part type

Terminations
Terminals, 160 – 1000 A

Connection type

Clamp
Screwing

Number of poles

Four-pole

Rated operation current (Ie)

800 A

Resources

Catalogs

[eaton-panel-building-accessories-catalog-ca008008en-en-us.pdf](#)

Declarations of conformity

[eaton-xeffect-k-type-terminals-declaration-of-conformity-en-us.pdf](#)
DA-DC-03_K95_K150_K240_K2x240_K3x185

Drawings

[eaton-control-panels-terminals-xeffect-k-type-terminal-3d-drawing.eps](#)

Installation instructions

[IL015110ZU](#)

mCAD model

[eaton-K3X185_4-drawing.dwg](#)
[eaton-K3X185_4-3d-model.stp](#)

System overview

[eaton-control-panels-terminals-xeffect-k-type-terminal-explosion-drawing-002.eps](#)

Mounting method

Screw

Suitable for

Useful for stranded conductors

Terminal capacity (copper band)

2 segments of 21 mm x 1 mm (11x) for flat strip

Nominal current

800 A

Number of connections (Less Than 6 mm squared)

0

Number of connections (Less Than AWG 6)

0

Number of connections (Greater Than 25 mm squared)

8

Number of connections (Greater Than 250 kcmil)

0

Number of connections (10 mm squared)

0

Number of connections (16 mm squared)

0

Number of connections (25 mm squared)

0

Number of connections (250 kcmil)

0

Number of connections (AWG 2)

0

Number of connections (AWG 4)

0

Number of connections (AWG 4/0)

0

Number of connections (AWG 6)

0

Number of connections (total)

8

Rated insulation voltage (Ui)

1000 VAC

Number of outputs

Terminal capacity (aluminum cable)95 mm² - 150 mm² (3x)150 mm² - 185 mm² (2x)**Terminal capacity (conductor)**

50 mm x 20 mm

Terminal capacity (copper/aluminum cable)120 mm² - 240 mm² (2x)50 mm² - 185 mm² (3x)**Conductor cross section, input - max**240 mm²**Conductor cross section, output - min**50 mm²**Conductor cross section, input - min**50 mm²**Conductor cross section, input AWG - min**1 mm²**Conductor cross section, input AWG - max**500 mm²**Conductor cross section, output - max**300 mm²**Conductor cross section, output AWG - max**0 mm²**Conductor cross section, output AWG - min**0 mm²**Number of inputs**

2