

FEATURES

- **Graphite and PTFE material:** Offers superior chemical resistance and durability
- **Maximum operating pressure of 8500 kPa:** Suitable for high-pressure applications
- **Maximum operating temperature of 280 °C:** Performs well in high-temperature environments
- **Rotary speed of 28 m/s:** Supports high-speed rotary applications
- **Section size of 10 mm:** Fits a variety of gland and valve sizes

RS PRO 8m Gland & Valve Packing, Graphite PTFE

RS Stock No: 606-554



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO gland and valve packing is designed for high-performance sealing in industrial applications. Made from a combination of graphite and polytetrafluoroethylene, it provides excellent resistance to high temperatures and pressures, making it ideal for demanding environments. Its primary benefit is ensuring reliable sealing in rotary and static applications.

General Specifications

Maximum Operating Pressure	8500 kPa
Product Type	Gland & Valve Packing
Rotary Speed	28 m/s
Section	10 mm
Sub Type	Gland Packing

Mechanical Specifications

Length	8 m
Material	Graphite, Polytetrafluoroethylene

Operation Environment Specifications

Maximum Operating Temperature	280 °C
-------------------------------	--------

Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, RoHS
---------------------	----------------------------