

TE Internal #: 2108613-5
Preloaded - C-Clip PCB Spring Contact, Scalable, Side Protected,
2.4 mm [.094 in] Uncompressed Height, 2.9 mm [.114 in] Length, 1
mm [.039 in] Width

[View on TE.com >](#)



Connectors > Contacts > PCB Spring Contacts



Spring Finger Type: **Preloaded - C-Clip**
Scalable: **Yes**
Side Protected: **Yes**
Uncompressed Height: **2.4 mm [.094 in]**
Product Length: **2.9 mm [.114 in]**

Features

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Connector System	Board-to-Board
Spring Finger Type	Preloaded - C-Clip
Scalable	Yes

Configuration Features

Number of Positions	1
Side Protected	Yes

Contact Features

Contact Underplating Material	Nickel
Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material	Gold
Contact Working Range (Low)	2.1 mm[.083 in]
Contact Working Range (High)	2.5 mm[.098 in]
Point of Contact Area Plating Material	Gold



Contact Current Rating (Max)	.5 A
------------------------------	------

Dimensions

Uncompressed Height	2.4 mm[.094 in]
Product Length	2.9 mm[.114 in]
Product Width	1 mm[.039 in]

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Packaging Features

Packaging Method	Tape & Reel
Packaging Quantity	6000

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # 2108610-5
1.4H SPRING FINGER WITH EMBOSS

Customers Also Bought

TE Part #4-2176091-7
RP 2A 0.25W 174R 0.1% 25PPM 1K RL

TE Part #2108693-4
1.1H SPRING FINGER WITH EMBOSS

TE Part #6-1676481-3
CPF 0603 2K4 0.1% 25PPM 1K RL

TE Part #9-2176089-8
RP 1J 0.166W 124K 0.1% 25PPM 1K RL

TE Part #TRM-433-LT
Module LT 433MHz AM OOK XCVR

TE Part #L9000046-01
Antenna 2.4 FPC LV 7x45 200 UFL

TE Part #2-1879215-0
CPF 0402 6K34 0.1% 25PPM 1K RL

TE Part #244854-E
SMCQ 12 M AB VV 8-03 CL * H007 137 E005

TE Part #5104338-7
A/L LOW PRO HDR 34P VERT HT

TE Part #7-1393788-5
V23079F1108B301

Documents

Product Drawings

2.4H SPRING FINGER WITH EMBOSS

English

CAD Files

3D PDF



3D

Customer View Model

[ENG_CVM_CVM_2108613-5_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2108613-5_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2108613-5_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Product Specification](#)

English