



SIMATIC, fail-safe electronic module for ET200iSP, 4F-AI HART Ex I, up to category 4 (EN954-1)/ SIL3 (IEC61508)/PLE (ISO13849), for connecting (HART) 2-wire transmitters, supported HART protocol version 7.0, Ex ib (ia Ga) IIC T4 Gb, Ex ib [ia IIC Da] IIC T4 Gb, Ex ib [ia] I Mb

General information	
Product brand name	SIMATIC
Product family	ET 200iSP
Product category	Analog module input
Product type designation	4F-AI I Ex HART
Installation type/mounting	
Rack mounting	No
Front mounting	Yes
Rail mounting	Yes
Wall mounting/direct mounting	Yes
Supply voltage	
Type of supply voltage	DC
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	30 V
Input current	
Current consumption, typ.	315 mA
from supply voltage L+, max.	490 mA; int. Powerbus
Output voltage	
Power supply to the transmitters	
<ul style="list-style-type: none"> <li>• short-circuit proof</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• Supply current, max.</li> </ul>	25 mA; Plus 4 mA per channel
Power loss	
Power loss, typ.	3.8 W
Power loss, max.	5.4 W
Address area	
Address space per module	
<ul style="list-style-type: none"> <li>• Address space per module, max.</li> </ul>	16 byte; 12 bytes in the I area / 4 bytes in the O area
Hardware configuration	
Fieldbus connection via separate transceiver	Yes
Analog inputs	
Number of analog inputs	4
Cycle time (all channels) max.	See data in manual
Input ranges	
<ul style="list-style-type: none"> <li>• Voltage</li> </ul>	No
<ul style="list-style-type: none"> <li>• Current</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• Thermocouple</li> </ul>	No
<ul style="list-style-type: none"> <li>• Resistance thermometer</li> </ul>	No
<ul style="list-style-type: none"> <li>• Resistance</li> </ul>	No
Input ranges (rated values), currents	

• 0 to 20 mA	Yes
• 4 mA to 20 mA	Yes
<b>Cable length</b>	
• shielded, max.	500 m
<b>Analog value generation for the inputs</b>	
Measurement principle	integrating (Sigma-Delta)
<b>Integration and conversion time/resolution per channel</b>	
• Resolution with overrange (bit including sign), max.	16 bit
• Integration time, parameterizable	Yes
• Interference voltage suppression for interference frequency $f_1$ in Hz	50 / 60 Hz
<b>Smoothing of measured values</b>	
• parameterizable	Yes; in 4 stages
• Step: None	Yes; 1x cycle time
• Step: low	Yes; 4x cycle time
• Step: Medium	Yes; 16x cycle time
• Step: High	Yes; 64x cycle time
<b>Encoder</b>	
<b>Connection of signal encoders</b>	
• for current measurement as 2-wire transducer — Burden of 2-wire transmitter, max.	Yes 750 $\Omega$
<b>Errors/accuracies</b>	
Linearity error (relative to input range), (+/-)	0.015 %
Temperature error (relative to input range), (+/-)	0.005 %/K
Crosstalk between the inputs, min.	-50 dB
Repeat accuracy in steady state at 25 °C (relative to input range), (+/-)	0.015 %
<b>Operational error limit in overall temperature range</b>	
• Current, relative to input range, (+/-)	0.35 %
<b>Basic error limit (operational limit at 25 °C)</b>	
• Current, relative to input range, (+/-)	0.1 %
<b>Interference voltage suppression for <math>f = n \times (f_1 \pm 1 \%)</math>, <math>f_1</math> = interference frequency</b>	
• Series mode interference (peak value of interference < rated value of input range), min.	40 dB
• Common mode interference, min.	50 dB
<b>Interfaces</b>	
Number of PROFINET interfaces	0
<b>Protocols</b>	
Supports protocol for PROFINET IO	No
PROFIsafe	Yes
PROFIBUS	No
<b>Further protocols</b>	
• other bus systems	No
<b>Interrupts/diagnostics/status information</b>	
<b>Alarms</b>	
• Diagnostic alarm	Yes; Parameterizable
<b>Diagnoses</b>	
• Diagnostic information readable	Yes
• Wire-break	Yes
• Short-circuit	Yes
<b>Diagnostics indication LED</b>	
• Group error SF (red)	Yes
<b>Potential separation</b>	
<b>Potential separation analog inputs</b>	
• between the channels	No
• between the channels and backplane bus	Yes
• Between the channels and load voltage L+	Yes; Power bus
<b>Permissible potential difference</b>	
between different circuits	60 V DC/30 V AC

<b>Degree and class of protection</b>	
IP degree of protection	IP30
<b>Standards, approvals, certificates</b>	
CE mark	Yes
Suitable for safety functions	Yes
reference designation according to IEC 81346-2 (2009)	K
<b>Highest safety class achievable in safety mode</b>	
• acc. to EN 954	4
• Performance level according to ISO 13849-1	PLe
• SIL acc. to IEC 61508	SIL 3
<b>Use in hazardous areas</b>	
• ATEX marking	II 2 G (1) GD Ex ib[jia Ga][jia IIIC Da] IIC T4 GB and I M2 Ex ib[jia Ma] I Mb
• ATEX certificate	10 ATEX 0058
• Explosion protection category for gas	ATEX gas explosion protection, Zone 1
• Explosion protection category for dust	ATEX dust explosion protection, Zone 21 always install in corresponding enclosure
• associated equipment (Ex ia)	Yes
• associated equipment (Ex ib)	Yes
<b>Connection method</b>	
Design of electrical connection	Screw/spring-type terminal
<b>Dimensions</b>	
Width	30 mm
Height	129 mm
Depth	136.5 mm
<b>Weights</b>	
Weight, approx.	299 g
<b>Classifications</b>	

	Version	Classification
eClass	14	27-24-26-01
eClass	12	27-24-26-01
eClass	9.1	27-24-26-01
eClass	9	27-24-26-01
eClass	8	27-24-26-01
eClass	7.1	27-24-26-01
eClass	6	27-24-26-01
ETIM	10	EC001596
ETIM	9	EC001596
ETIM	8	EC001596
ETIM	7	EC001596
IDEA	4	3562
UNSPSC	15	32-15-17-05

**Approvals / Certificates**

**General Product Approval**

[China RoHS](#)



[Miscellaneous](#)



[Metrological Approval](#)

General Product Approval

For use in hazardous locations



[FM](#)



[Miscellaneous](#)

For use in hazardous locations Functional Safety



[CCC-Ex](#)



[Miscellaneous](#)

[TUEV](#)

Functional Safety Maritime application Environment

[Type Examination Certificate](#)

[TUEV](#)



last modified:

4/29/2025