

SACC-MCI-M12MS-8CON - Contact carrier



1440928

<https://www.phoenixcontact.com/in/products/1440928>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, 8-position, Pin, straight, M12, coding: A, Front mounting, Square flange, Crimp connection, 0.25 mm²

Your advantages

- Convenient field assembly: device connectors for fast on-site mounting
- Contact carriers that are designed for assembly or available with preassembled litz wires
- Standard pin assignments for signal and power transmission with a uniform design-in design

Commercial data

Item number	1440928
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	ABQ
Product key	ABQCED
Catalog page	Page 45 (C-2-2019)
GTIN	4046356533768
Weight per piece (including packing)	1.4 g
Weight per piece (excluding packing)	1.36 g
Customs tariff number	85366990
Country of origin	DE

Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

Product properties

Product type	Contact insert
Number of positions	8
No. of cable outlets	1
Seal present	no
Shielded	no
Coding	A
Thread type	M12

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Electrical properties

Rated surge voltage	0.8 kV
Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	30 V
Nominal current I_N	2 A

Connection data

Connection method	Crimp connection
-------------------	------------------

Signaling

Status display	no
Status display present	No

Material specifications

Flammability rating according to UL 94	V0
Contact carrier material	PA 6.6

Connector

Connection 1

Head design	Pin
Head cable outlet	straight

SACC-MCI-M12MS-8CON - Contact carrier



1440928

<https://www.phoenixcontact.com/in/products/1440928>

Head thread type	M12
Coding	A

Cable/line

Cable cross section	0.25 mm²
---------------------	----------

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
	IP67
Ambient temperature (operation)	-25 °C ... 85 °C (Plug / socket)
	-40 °C ... 85 °C (without mechanical actuation)
UL Type Rating	Type 4 (indoor use only)

Standards and regulations

M12


Standard designation	M12 connector
Standards/specifications	IEC 61076-2-101

Mounting

Mounting type	Front mounting Square flange 25 mm side length
Assembly note	25 mm side length


Drawings

Circuit diagram



Contact assignment of the M12 plug

Schematic diagram



Pin assignment M12 plug, 8-pos., view plug side

SACC-MCI-M12MS-8CON - Contact carrier



1440928

<https://www.phoenixcontact.com/in/products/1440928>

Classifications

ECLASS

ECLASS-11.0	27440223
ECLASS-12.0	27440116
ECLASS-13.0	27440223

ETIM

ETIM 9.0	EC003557
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-MCI-M12MS-8CON - Contact carrier



1440928

<https://www.phoenixcontact.com/in/products/1440928>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

SACC-MCI-M12MS-8CON - Contact carrier



1440928

<https://www.phoenixcontact.com/in/products/1440928>

Accessories

CC-0,8-ST-0,34-MS AU - Crimp contact

1452372

<https://www.phoenixcontact.com/in/products/1452372>



Crimp contact, Pin, turned, contact diameter: 0.8 mm, crimp range: 0.08 mm² ... 0.34 mm², Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1239799

SACC-MSQ-M12MS-25-3,2 SCO - Housing screw connection

1419959

<https://www.phoenixcontact.com/in/products/1419959>



Housing screw connection, M12-SPEEDCON, Front mounting, square flange 25 mm side length, Square flange, potted

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in