

PRODUCT-DETAILS

S202-K16 S202-K16 Miniature Circuit Breaker - 2P - K - 16 A



General Information	
Extended Product Type	S202-K16
Product ID	2CDS252001R0467
EAN	4016779507417
Catalog Description	S202-K16 Miniature Circuit Breaker - 2P - K - 16 A

Long Description

System pro M compact S200 miniature circuit breakers are current limiting. They have two different tripping mechanisms, the delayed thermal tripping mechanism for overload protection and the electromechanic tripping mechanism for short circuit protection. They are available in different characteristics (B,C,D,K,Z), configurations (1P,1P+N,2P,3P,3P+N,4P), breaking capacities (up to 6 kA at 230/400 V AC) and rated currents (up to 63A). All MCBs of the product range S200 comply with IEC/EN 60898-1, IEC/EN 60947-2, UL1077 allowing the use for residential, commercial and industrial applications. Bottom-fitting auxiliary contact can be mounted on S200 to save 50% space.

ABB EcoSolutions ABB EcoSolutions Yes

Circular Value		
Circular Design Principles Recyclability Rate	Design for Closing Resource	Loops - Standard EN45555 - 87.8 %
Offered with Extended Lifetime		Product Durability
Offered with Takeback		Take Back for Recycling
© 2024 ABB. All rights reserved.	2024/02/16	Subject to chang

Services

End of Life Instructions	QAKK108/68A3133

Eco Transparency	
Environmental Product Declaration - EPD	9AKK108467A7832

Technical	
Standards	IEC/EN 60898-1 IEC/EN 60947-2
	UL 1077
Tripping Characteristic	K
Rated Operational Voltage	acc. to IEC 60898-1 400 V AC acc. to IEC 60898-1 400 V acc. to IEC 60947-2 440 V AC
Operational Voltage	Maximum (Incl. Tolerance) 125 V DC Maximum (Incl. Tolerance) 440 V AC
Rated Insulation Voltage (U_i)	acc. to IEC/EN 60664-1 440 V
Rated Impulse Withstand Voltage (U_{imp})	4 kV at 2000 m 5 kV at Sea Level 6.2 kV
Dielectric Test Voltage	50/60 Hz, 1 min: 2 kV
Input Voltage Type	AC/DC
Rated Current (I _n)	16 A
Rated Short-Circuit Capacity	(AC) 6 kA (DC) 6 kA (400 V AC) 6 kA (400 V) 6 kA
Rated Ultimate Short-Circuit Breaking Capacity (I _{cu})	(125 V DC) 10 kA (230 V AC) 20 kA (400 V AC) 10 kA (440 V AC) 10 kA (48 V DC) 20 kA (230 V) 20 kA (400 V) 10 kA
Rated Conditional Short- Circuit Current (I _{nc})	(230 V) 20 kA (400 V) 20 kA
Rated Service Short- Circuit Breaking Capacity (I _{cs})	(230 V AC) 15 kA (400 V AC) 7.5 kA (440 V AC) 7.5 kA
Frequency (f)	50 Hz
Rated Frequency (f)	50 / 60 Hz 50 60 Hz
Power Loss	$4\ W$ at Rated Operating Conditions per Pole 2 W
Power Supply Connection	Arbitrary
Contact Position Indication	Red ON / Green OFF
Energy Limiting Class	3
Electrical Endurance	20000 AC cycle
Mechanical Endurance	20000 cycle
Number of Protected Poles	2
Number of Poles	2
Overvoltage Category	III
Tightening Torque	2.8 N·m
Mounting Type	DIN-Rail
Screw Terminal Type	Failsafe Bi-directional Cylinder-lift Terminal
Actuator Marking	1/0
Actuator Material	Insulation Group II, Black, Sealable

Housing Material	Insulation Group II, RAL 7035		
Mounting on DIN Rail	TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715		
Mounting Position	any		
Recommended Screw Driver	Pozidriv 2		
Accessories Available	Yes		
Connecting Capacity	Busbar 10 / 10 mm² Flexible with Ferrule 0.75 25 mm² Flexible 0.75 25 mm² Rigid 0.75 35 mm² Rigid 0.75 35 mm² Stranded 0.75 35 mm²		
Installation Size	acc. to DIN 43880 1		
Wire Stripping Length	12.5 mm		
Terminal Type	Screw Terminals		

Material Compliance	
RoHS Information	2CDK403001D0607
RoHS Status	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
RoHS Date	0335
REACH Declaration	9AKK108468A9644
REACH Information	False - does not contains substances > 0.1 mass percentage
Conflict Minerals Reporting Template (CMRT)	9AKK108468A3363
SCIP	e6800e55-46b1-49a3-881b-0f66d0e903ad Germany (DE)

Environmental	
Ambient Air Temperature	Operation -25 +55 °C Storage -40 +70 °C
Degree of Protection	IP20 IP40 Enclosure with Cover IP40
Pollution Degree	3
Environmental Conditions	28 cycles with 55 $^{\circ}\text{C}$ / 90-96 $\%$ and 25 $^{\circ}\text{C}$ / 95-100 $\%$
Resistance to Vibrations	20 Cycles with Load 0.8 In: 5g 5 150 5 Hz
Resistance to Shock acc. to IEC 60068-2-27	25g 2 shocks 13 ms

Technical UL/CSA	
Maximum Operating Voltage UL/CSA	110 V DC 480Y / 277 V AC
Interrupting Rating acc. to UL1077	(277 V AC) 6 kA (480Y / 277 V AC) 6 kA (240 V) 10 kA
Connecting Capacity UL/CSA	Busbar 18-8 AWG Conductor 18-4 AWG
Tightening Torque <u>UL/CSA</u>	18 in·lb

Dimensions	
Width in Number of Modular Spacings	2
Product Net Width	35 mm

Product Net Height	88 mn	
Product Net Depth /	69 mn	
Length		
Product Net Weight	0.25 kg	
Pole Net Weight	0.125 kg	
Built-In Depth (t ₂)	69 mn	
Dimension Diagram	2CDC022007F0010	
Ordering Ordering		
Package Level 1 Units	carton 5 piece	
Package Level 1 Gross Weight	1.3 kg	
E-Number (Finland)	3210902	
E-Number (Sweden)	2100715	
Certificates and Declarations		
Certification Agency	EN IEC UI	
Declaration of Conformity - CE	2CDK403001D0603	
Declaration of Conformity - UKCA	9AKK108467A50	
Installation		
Installation Instructions and Manuals	2CDS207104P0002	
Instructions and Manuals	2CDS207104P000:	
	2CDS207104P0002 9AKK107991A8329	
Popular Downloads Data Sheet, Technical Information	9AKK107991A8329	
Popular Downloads Data Sheet, Technical Information Pt Characteristic	9AKK107991A8329	
Popular Downloads Data Sheet, Technical Information Pt Characteristic Classifications	9AKK107991A8329 9AKK107992A5103	
Popular Downloads Data Sheet, Technical Information Pt Characteristic Classifications ETIM 8 ETIM 9	9AKK107991A832: 9AKK107992A5103 9AKK107992A5103 EC000042 - Miniature circuit breaker (MCB EC000042 - Miniature circuit breaker (MCB	
Popular Downloads Data Sheet, Technical Information It Characteristic Classifications ETIM 8 ETIM 9 WEEE Category	9AKK107991A8329 9AKK107992A5103 9AKK107992A5103 EC000042 - Miniature circuit breaker (MCB EC000042 - Miniature circuit breaker (MCB 5. Small Equipment (No External Dimension More Than 50 cm	
Popular Downloads Data Sheet, Technical Information It Characteristic Classifications ETIM 8 ETIM 9 WEEE Category WEEE B2C / B2B	9AKK107991A8329 9AKK107992A5103 9AKK107992A5103 EC000042 - Miniature circuit breaker (MCB EC000042 - Miniature circuit breaker (MCB 5. Small Equipment (No External Dimension More Than 50 cm Business To Business	
Popular Downloads Data Sheet, Technical Information It Characteristic Classifications ETIM 8 ETIM 9 WEEE Category WEEE B2C / B2B CN8	9AKK107991A8329 9AKK107992A5103 9AKK107992A5103 EC000042 - Miniature circuit breaker (MCB EC000042 - Miniature circuit breaker (MCB 5. Small Equipment (No External Dimension More Than 50 cm Business To Business 8536 20 16	
Popular Downloads Data Sheet, Technical Information Pt Characteristic Classifications ETIM 8 ETIM 9 WEEE Category WEEE B2C / B2B CN8 UNSPSC	9AKK107991A8329 9AKK107992A5103 EC000042 - Miniature circuit breaker (MCB EC000042 - Miniature circuit breaker (MCB 5. Small Equipment (No External Dimension More Than 50 cm Business To Business 8536 20 10 39121603	
Popular Downloads Data Sheet, Technical		

Accessories

Identifier	Description	Туре	Quantity	Unit Of Measure
2CDS200922R0001	S2C-S/H6R Signal / Auxiliary Contact	S2C-S/H6R	1	piece
2CDS200912R0001	S2C-H6R Auxiliary Contact	S2C-H6R	1	piece
2CDS200970R0001	S2C-H01 Auxiliary Contact	S2C-H01	1	piece
2CDS200970R0002	S2C-H10 Auxiliary Contact	S2C-H10	1	piece
2CDS200936R0001	S2C-H11L Auxiliary Contact	S2C-H11L	1	piece
2CDS200936R0002	S2C-H20L Auxiliary Contact	S2C-H20L	1	piece
2CDS200936R0003	S2C-H02L Auxiliary Contact	S2C-H02L	1	piece
2CDS200946R0001	S2C-H6-11R Auxiliary Contact	S2C-H6-11R	1	piece
2CDS200946R0002	S2C-H6-20R Auxiliary Contact	S2C-H6-20R	1	piece
2CDS200946R0003	S2C-H6-02R Auxiliary Contact	S2C-H6-02R	11	piece
2CDS200909R0001	S2C-A1 Shunt Trip	S2C-A1	1	piece
2CDS200909R0002	S2C-A2 Shunt Trip	S2C-A2	1	piece
2CSS200911R0001	S2C-UA 12 DC Undervoltage Release S	S2C-UA 12 DC	1	piece
2CSS200911R0002	S2C-UA 24 AC Undervoltage Release S	S2C-UA 24 AC	1	piece
2CSS200911R0003	S2C-UA 48 AC Undervoltage Release S	S2C-UA 48 AC	1	piece
2CSS200911R0004	S2C-UA 110 AC Undervoltage Release	S2C-UA 110 AC	1	piece
2CSS200911R0005	S2C-UA 230 AC Undervoltage Release	S2C-UA 230 AC	1	piece
2CSS200911R0006	S2C-UA 400 AC Undervoltage Release	S2C-UA 400 AC	1	piece
2CSS200911R0007	S2C-UA 24 DC Undervoltage Release S	S2C-UA 24 DC	1	piece
2CSS200911R0008	S2C-UA 48 DC Undervoltage Release S	S2C-UA 48 DC	1	piece
2CSS200911R0009	S2C-UA 110 DC Undervoltage Release	S2C-UA 110 DC	1	piece
2CSS200911R0010	S2C-UA 230 DC Undervoltage Release	S2C-UA 230 DC	1	piece
2CSS201997R0013	S2C-CM1 Motor Operating Device	S2C-CM1	1	piece
2CSS203997R0013	S2C-CM2/3 Motor Operating Device	S2C-CM2/3	1	piece
2CSS204997R0013	S2C-CM4 Motor Operating Device	S2C-CM4	1	piece
GHS2001901R0003	S2C-DH Mechanical Accessories	S2C-DH	1	piece
2CSS200998R0001	S2C-BP Mechanical tripping device	S2C-BP	1	piece
2CSS200999R0001	S2C-EST Plug-in base	S2C-EST	1	piece
2CDS200918R0001	S2C-NT Hand Operated Neutral	S2C-NT	1	piece
2CCA880100R0001	CMS-100PS Sensor	CMS-100PS	1	piece
2CCA880101R0001	CMS-101PS Sensor	CMS-101PS	1	piece
2CCA880102R0001	CMS-102PS Sensor	CMS-102PS	1	piece

Categories

 $Low\ Voltage\ Products\ and\ Systems\ \rightarrow\ Modular\ DIN\ Rail\ Products\ \rightarrow\ Miniature\ Circuit\ Breakers\ MCBs\ \rightarrow\ Miniature\ MCBs\ \rightarrow\ Miniature\ MCBs\ \rightarrow\ Miniature\ MCBs\ \rightarrow\ MCBs\ \rightarrow\ Miniature\ MCBs\ \rightarrow\ Minia$









3605