



Part Number : 02082003  
Product Description : MLX Male Crimp  
Terminal 42023, 14-20 AWG, Reel, Brass, Tin  
(Sn) Plating  
Series Number : 42023  
Status : Active  
Product Category : Crimp Terminals  
Engineering Number : 42023-2A1  
Packaging Alternative : 0002082004 (Bag)



Documents & Resources

Drawings

[Drawing 002082003\\_sd.pdf](#)


Specifications

[Product Specification PS-42022-0001-001.pdf](#)

[Test Summary TS-42022-0001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

[Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	Crimp Terminals
Series	42023
Description	MLX Male Crimp Terminal 42023, 14-20 AWG, Reel, Brass, Tin (Sn) Plating
Application	Power, Wire-to-Wire
Product Family	MLX Power Connectors
Product Name	MLX
UPC	800753615656

#### Physical

Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	450.000/mg
Packaging Type	Reel
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.52-3.30mm
Wire Size (AWG)	14, 16, 18, 20
Wire Size mm <sup>2</sup>	N/A

#### Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

## Application Tooling

### Global

Description	Part Number
Extraction Tool for MLX 2.13mm Diameter Pin and Socket Crimp Terminals	<u>0011010168</u>
PremiumGrade Hand Crimp Tool for MLX Pin and Socket Terminals, 14-20 AWG	<u>0638116800</u>
FineAdjust Applicator for Crimp Terminals, 14-20 AWG Wire with 2.08-2.50mm Diameter Insulation	<u>0639007500</u>
FineAdjust Applicator for Crimp Terminals, 14-20 AWG Wire with 2.65-3.30mm Diameter Insulation	<u>0639009800</u>
FineAdjust Applicator for Crimp Terminals, 14-20 AWG Wire with 2.41-2.95mm Diameter Insulation	<u>0639009900</u>
T2 Terminator for MLX Crimp Terminals, 14-20 AWG	<u>0639107500</u>
T2 Terminator Tooling Die for Crimp Terminals, 14-20 AWG Wire	<u>0639109800</u>
T2 Terminator Tooling Die for Crimp Terminals, 14-20 AWG Wire	<u>0639109900</u>