

## SKINDICHT® SVF-M

SKINDICHT® SVF-M, flat cable gland with automatically fitting lateral sealing lips, optimum strain relief



Assembly time



Maximum vibration protection



Wide clamping range

### Benefits

Lateral sealing lips fit automatically around various cable dimensions

Cable-specific seal dimensions are no longer necessary

Large opening allows clamping of up to two flat cables

Optimum strain relief

Tolerance

### Application range

For inserting flat cables

Control cabinet manufacturing

Conveyor systems

Pumps

Lifts

### Product Make-up

Metric connection thread acc. to DIN EN 60423

Basis for technical information DIN IEC 62444

### Note

For suitable flat cables, refer to ÖLFLEX® LIFT F for indoor applications or ÖLFLEX® CRANE F for outdoor applications

Counter nut to be used: SKINDICHT® SM-M

### Technical Data

Classification:

ETIM 5.0 Class-ID: EC000441

ETIM 5.0 Class-Description: Cable screw gland

Caution:

The installation dimensions  
can be found in appendix T21

Material:

Body: nickel-plated brass

Seal: CR

Protection rating:

IP 54

Temperature range:

-30°C to +100°C

Last Update (06.07.2017)

©2017 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

**SKINDICHT® SVF-M****Note**

Photographs are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.



**SKINDICHT® SVF-M**

Article number	Article designation / size	Min./max. flat cable width	Min./max. cable thickness (mm)
SKINDICHT® SVF-M			
52107320	M 20/16	- / 15	- / 5
52107340	M 25/21	9 / 20	3 / 8
52107350	M 32/29	14 / 27	4 / 11.5
52107360	M 40/36	24 / 34	4 / 11.5
52107370	M 50/42	29 / 44	5 / 12
52107380	M 63/48	34 / 50	5 / 12

Last Update (06.07.2017)

©2017 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16