

Product datasheet

Specifications



Thalassa PHD outdoor heavy duty - aluminium cable gland plate - W750 D620

NSYPPC76HD

Main

Range	Thalassa
Product or component type	Cable gland plate
Accessory / separate part category	Cable management accessory
Application	Outdoor heavy duty
Application	Multi-purpose
Nominal width of the housing	750 mm
Nominal depth of the housing	620 mm
Range compatibility	Thalassa Thalassa PHD
Mounting location	Enclosure bottom
Type of gland plate	Plain aluminium
Device composition	fixing elements 1 plate separate gasket
Quantity per set	Set of 1
Material	Aluminium

Complementary

Surface finish	Brushed finish
Fixing mode	Tool less - screw type quarter-turn
Height	15 mm
Width	Nominal: 750 mm Real: 760 mm
Depth	Nominal : 620 mm
Thickness	3 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.500 cm
Package 1 Width	64.000 cm
Package 1 Length	77.000 cm
Package 1 Weight	2.110 kg
Unit Type of Package 2	PAM

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number of Units in Package 2	20
Package 2 Height	49.000 cm
Package 2 Width	100.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	54.200 kg


Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.


[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

 Materials and Packaging	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
SCIP Number	B8d0fb33-5e43-4121-80bd-e0d068ed5eda

Use Again

 Repack and remanufacture	
Take-back	No