

JNU25

JALSENSEI SAS ESD

S1P SRC
EN ISO 20345:2011
35 to 47

- **Synthetic nubuck / Textil**
- **Semelle J-nude PU / TPU**
- **Safety toe cap and midsole no metallic**
- **Antistatic and dissipative**



- ❖ Safety boot, urban sport type, protecting the electronic devices against electrostatic discharge phenomena. Electrostatic dissipative shoes ESD Environmental Class II tested according to EN 61340-4-3 and EN 61340-5-1.
- ❖ Synthetic nubuck, Inserts and collar in technical textiles . Color grey / black. Silkscreened Jallatte applies. Pu reinforcement to the front of the sole.
- ❖ Upper lined in breathable **3D mesh** with honeycomb structure to improve the peripheral ventilation of the foot, dries out rapidly.
- ❖ Vamp lining in non-woven fabric, resists scuffing and acid perspiration.
- ❖ Padded tongue for good instep protection, combined with two side bellows to prevent any dirt from getting into the boots.
- ❖ Padded ergonomic collar in compact flexible foam, lined for extra comfort and better ankle and Achilles tendon protection.
- ❖ Lace up on two pairs of eyelets and 3 pairs of fabric loops . Lace-loop keeps tongue in place as you walk. Black laces : 140 cm.
- ❖ **ESD** footbed single-block structure made of soft polyurethane and textile, anatomical, perforated in the front part and with heel shock absorbers.
- ❖ Ergonomic shoe with **broad synthetic polymer toe cap**, for saving on weight (50% lighter than steel) and removal of perspiration from around the forefoot. Impact resistance to **200 Joules**.
- ❖ New manufacturing **process** : antiperforation inner sole and insert in **FleXtane™ ESD By Jallatte** material, antistatic, **100% composite**. Sewn directly onto the bootstrap and covering **100% of the foot** for all-round protection. **100% composite** materials: lighter than steel, non-magnetic, non-conductive of heat or cold.
- ❖ Heel stiffener to reinforce the heel seat.
- ❖ **Innovative soles all in flexibility**, bi-component **Softane/ TPU ESD** for natural foot movement.

Slip resistance tests results

EN Standard : EN ISO 20345 : 2011

Requirement SRC (SRA+SRB)

SRA Test ground : ceramic / lubricant : water and detergent

On flat **0,43** (>0,32) – On the heel **0,33** (>0,28)

SRB Test ground steel/lubricant : glycerine

On flat **0,22** (>0,18) – On the heel **0,21** (>0,13)

- Lightweight and durable TPU outsole.
- Confort soles very flexible.
- Independents treads for high stability in every positions.
- Gridded outsole for natural foot movement.
- High slip resistance with the grooves in the front and the back of the sole.

Poids	Brut (42) : 1352 g / Net (42) : 1144 g		
Pointure	35 au 39	40 au 45	46 au 47
Conditionnement	5 paires	10 paires	5 paires
Dimensions cartons (mm)	685 x 255 x 345	685 x 505 x 345	685 x 255 x 345
Dimensions boites (mm)	340 x 245 x 133		

