



92.03



Approvals  
(according to type):



- RATED VALUES: 16 A - 250 V
- INSULATION:  $\geq 6$  kV (1.2/50 $\mu$ s) between coil and contacts
- PROTECTION CATEGORY: IP 20
- AMBIENT TEMPERATURE: (-40...+70)°C
- TORQUE: 0.8 Nm
- MAX WIRE SIZE:

|                 | solid wire | flexible wire |
|-----------------|------------|---------------|
| mm <sup>2</sup> | 1x10 / 2x4 | 1x6 / 2x4     |
| AWG             | 1x8 / 2x12 | 1x10 / 2x12   |

| Relay type                                                  | 62.32        | 62.33        |
|-------------------------------------------------------------|--------------|--------------|
| Clamp terminal socket: panel or 35 mm rail (EN 50022) mount | BLUE         | 92.03 92.03  |
|                                                             | BLACK*       | 92.03.10     |
| Retaining clip                                              | 092.71       | 092.71       |
| Modules                                                     | 99.02        | 99.02        |
| Timer modules                                               | 86.10, 86.20 | 86.10, 86.20 |



92.03



99.02

| 99 Series modules for 92.03 socket |                     | BLUE           | BLACK*           |
|------------------------------------|---------------------|----------------|------------------|
| Diode                              | (6...220) V DC      | 99.02.3.000.00 | 99.02.3.000.00.0 |
| Diode (inverted polarity)          | (6...220) V DC      | 99.02.2.000.00 | 99.02.2.000.00.0 |
| LED                                | (6...24) V DC/AC    | 99.02.0.024.59 | 99.02.0.024.59.0 |
| LED                                | (28...60) V DC/AC   | 99.02.0.060.59 | 99.02.0.060.59.0 |
| LED                                | (110...240) V DC/AC | 99.02.0.230.59 | 99.02.0.230.59.0 |
| LED + Diode                        | (6...24) V DC       | 99.02.9.024.99 | 99.02.9.024.99.0 |
| LED + Diode                        | (28...60) V DC      | 99.02.9.060.99 | 99.02.9.060.99.0 |
| LED + Diode                        | (110...220) V DC    | 99.02.9.220.99 | 99.02.9.220.99.0 |
| LED + Diode (inverted polarity)    | (6...24) V DC       | 99.02.9.024.79 | 99.02.9.024.79.0 |
| LED + Diode (inverted polarity)    | (28...60) V DC      | 99.02.9.060.79 | 99.02.9.060.79.0 |
| LED + Diode (inverted polarity)    | (110...220) V DC    | 99.02.9.220.79 | 99.02.9.220.79.0 |
| LED + Varistor                     | (6...24) V DC/AC    | 99.02.0.024.98 | 99.02.0.024.98.0 |
| LED + Varistor                     | (28...60) V DC/AC   | 99.02.0.060.98 | 99.02.0.060.98.0 |
| LED + Varistor                     | (110...240) V DC/AC | 99.02.0.230.98 | 99.02.0.230.98.0 |
| RC circuit                         | (6...24) V DC/AC    | 99.02.0.024.09 | 99.02.0.024.09.0 |
| RC circuit                         | (28...60) V DC/AC   | 99.02.0.060.09 | 99.02.0.060.09.0 |
| RC circuit                         | (110...240) V DC/AC | 99.02.0.230.09 | 99.02.0.230.09.0 |
| No - remanence                     | (110...240) V AC    | 99.02.8.230.07 | 99.02.8.230.07.0 |