

Jul.1.2018 Copyright 2018 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case that the application demands a high level of reliability, such as automotive,
please contact a company representative for further information.

TO

	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE		COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△						△					
△						△					
APPLICABLE STANDARD											
RATING	OPERATING TEMPERATURE RANGE	-35 °C TO +85 °C(NOTE1)					STORAGE TEMPERATURE RANGE	-10 °C TO +60 °C			
	VOLTAGE	250 V AC					APPLICABLE CONNECTOR	DF1B-*DS-2.5RC			
	CURRENT	3 A									
SPECIFICATIONS											
ITEM		TEST METHOD				REQUIREMENTS			QT	AT	
CONSTRUCTION											
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.				ACCORDING TO DRAWING.			x	x	
MARKING		CONFIRMED VISUALLY.							x	x	
ELECTRIC CHARACTERISTICS											
CONTACT RESISTANCE		100 mA (DC OR 1000 Hz).				30 mΩ MAX.			x	—	
INSULATION RESISTANCE		500 V DC.				1000 MΩ MIN.			x	—	
VOLTAGE PROOF		650 V AC FOR 1 min.				NO FLASHOVER OR BREAKDOWN.			x	—	
MECHANICAL CHARACTERISTICS											
MECHANICAL OPERATION		30 TIMES INSERTIONS AND EXTRACTIONS.				① CONTACT RESISTANCE: 30 mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			x	—	
VIBRATION		FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, AT 2 h, FOR 3 DIRECTIONS.				① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			x	—	
SHOCK		490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.				① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② CONTACT RESISTANCE: 30 mΩ MAX. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			x	—	
ENVIRONMENTAL CHARACTERISTICS											
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55→ 5 TO 35→+85→ 5 TO 35 °C TIME 30→ 5 MAX → 30→ 5 MAX min UNDER 5 CYCLES.				① CONTACT RESISTANCE: 30 mΩ MAX. ② INSULATION RESISTANCE: 1000 MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			x	—	
DAMP HEAT (STEADY STATE)		EXPOSED AT 40 ± 2 °C, 90 ~ 95 %, 96 h.				① CONTACT RESISTANCE: 30 mΩ MAX. ② INSULATION RESISTANCE: 1000 MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			x	—	
RESISTANCE TO SOLDERING HEAT		1) AUTOMATIC SOLDERING (FLOW) SOLDER TEMPERATURE, 260 °C FOR IMMERSION,DURATION, 5 sec. 2) MANUAL SOLDERING SOLDERING IRON TEMPERATURE : 300 °C, SOLDERING TIME : 3 sec. NO STRENGTH ON CONTACT.				NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.			x	—	
SOLDERABILITY		SOLDERED AT SOLDER TEMPERATURE, 235 °C FOR INSERTION DURATION, 5 s.				SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMERSED.			x	—	
REMARKS											
NOTE1: INCLUDE THE TEMPERATURE RISING BY CURRENT.						DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED	
						F.Matsuki '04.03.25	H.Umehara '04.03.25	T.Miyazaki '04.03.25	T.Gao '04.03.25		
Unless otherwise specified, refer to JIS C 5402.											
Note QT:Qualification Test AT:Assurance Test x:Applicable Test											
HIROSE ELECTRIC CO., LTD.						SPECIFICATION SHEET			PART NO. DF1BZ- * DP-2.5DS		
CODE NO.(OLD) CL			DRAWING NO. ELC4-305815-01			PART NO. CL541			1/1		