

CUC-IND-J1ST-A/R4LS-LED - RJ45 PCB connector



1091950
<https://www.phoenixcontact.com/gb/products/1091950>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



RJ45 PCB connector, design: RJ45, degree of protection: IP20, number of positions: 8, 10 Gbps, material: Metal, connection method: THR reflow/THT wave

Your advantages

- Ideal for demanding applications due to the high shock and vibration resistance as well as the extended temperature range
- 360° shielding ensures reliable transmission, even in industrial applications
- Housing shield springs enable an optimized EMC shielding concept
- With integrated hybrid LEDs as optical status indicators of data transmission
- Enables data transmission rates of up to 10 Gbps
- Automated handling process thanks to reflow capability
- The extended temperature range from -40°C to +105°C enables use in demanding industrial applications
- Tray packing

Commercial data

Item number	1091950
Packing unit	84 pc
Minimum order quantity	84 pc
Sales key	ABNADA
Product key	ABNADA
GTIN	4055626906447
Weight per piece (including packing)	5.74 g
Weight per piece (excluding packing)	5.7 g
Customs tariff number	85366930
Country of origin	CN

Technical data

Product properties

Product type	Data connector (device side)
Type	RJ45
Number of positions	8
Connection profile	RJ45
Type of packaging	Tray
Housing shield springs	No
Number of slots	1
Type	Socket
Shielded	yes
LED	yes

Insulation characteristics

Overvoltage category	I
Degree of pollution	2

Electrical properties

Rated voltage (III/2)	72 V DC
Rated surge voltage	1.5 kV DC
Rated surge voltage (III/3)	1.5 kV
Rated surge voltage	1 kV DC
Rated current	1.5 A
Frequency range	10 Hz ... 500 Hz
Insulation resistance	> 500 MΩ
Test voltage	1 kV DC
Test voltage Core/Core	1 kV DC
Test voltage Core/Shield	1.50 kV DC
Transmission medium	Copper
Transmission speed	10 Gbps
Power transmission	PoE++

Connection data

Connection technology

Connection method	THR reflow/THT wave
-------------------	---------------------

Dimensions

Width	16.2 mm
Height	16.5 mm
Length	17.1 mm
Installed height	12.80 mm
Orientation to PCB	90.00 °

CUC-IND-J1ST-A/R4LS-LED - RJ45 PCB connector



1091950

<https://www.phoenixcontact.com/gb/products/1091950>

Data pin length	3.30 mm
-----------------	---------

Material specifications

Material Metal surface contact area (top layer)	Au (1.27 µm/50 µ")
Material Metal surface contact area (middle layer)	Ni
Material Metal surface soldering area (top layer)	Au
Material Metal surface soldering area (middle layer)	Ni
Material	Copper alloy (Housing (shielding))
Flammability rating according to UL 94	V0
Housing material	Metal
Housing surface material	Ni
Contact material	Copper alloy
Contact surface material	Gold

Cable/line

Test voltage Core/Core	1 kV DC
Test voltage Core/Shield	1.50 kV DC
Halogen-free	yes

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 750
Insertion force per signal contact	< 20.00 N
Extraction force per signal contact	< 20 N

Environmental and real-life conditions

Test specification

Frequency	10-500 Hz
Sweep speed	1 octave/min
Amplitude	0.35 mm
Acceleration	50.00 m/s ²
Test duration	20.00 s

Test specification

Specification	IEC60068-2-27
Acceleration	295.00 m/s ²

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 105 °C
Ambient temperature (storage/transport)	-40 °C ... 105 °C

Mounting

Mounting type	THR soldering
---------------	---------------

CUC-IND-J1ST-A/R4LS-LED - RJ45 PCB connector




1091950

<https://www.phoenixcontact.com/gb/products/1091950>

Processing notes

Moisture Sensitive Level	MSL 2
Classification temperature T _c	260 °C
Solder cycles in the reflow	3

Drawings



Classification wave soldering profile


CUC-IND-J1ST-A/R4LS-LED - RJ45 PCB connector



1091950

<https://www.phoenixcontact.com/gb/products/1091950>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1091950>



cUL Recognized
Approval ID: FILE E 335024



UL Recognized
Approval ID: FILE E 335024

CUC-IND-J1ST-A/R4LS-LED - RJ45 PCB connector



1091950

<https://www.phoenixcontact.com/gb/products/1091950>

Classifications

ECLASS

ECLASS-13.0	27460201
-------------	----------

ETIM

ETIM 9.0	EC002637
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CUC-IND-J1ST-A/R4LS-LED - RJ45 PCB connector



1091950

<https://www.phoenixcontact.com/gb/products/1091950>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk