

# RF-17S1N8A9V02 - Coupler connector



1614000

<https://www.phoenixcontact.com/gb/products/1614000>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Coupler connector, straight, Screw locking mechanism, M23, number of positions: 17, contact connection type: Socket, shielded: yes, degree of protection: IP67, cable diameter range: 6 mm . .. 10 mm, number of positions: 17, connection method: Crimp connection, series: RF, this item is undergoing a smooth changeover, lead-free alternative in accordance with RoHS II without exception 6c (Pb < 0.1%) possible on request in advance

## Commercial data

Item number	1614000
Packing unit	20 pc
Minimum order quantity	20 pc
Note	Made to order (non-returnable)
Sales key	ABRAGW
Product key	ABRAGW
GTIN	4046356443876
Weight per piece (including packing)	109.18 g
Weight per piece (excluding packing)	108.152 g
Customs tariff number	85366990
Country of origin	DE

# RF-17S1N8A9V02 - Coupler connector



1614000

<https://www.phoenixcontact.com/gb/products/1614000>

## Technical data

### Notes

Order information:	Order crimp contacts Ø 1 mm separately
--------------------	--

### Product properties

Product type	Circular connector (cable-side)
Series	RF
Application	Feedback, signal
Number of positions	17
Connection profile	17
Shielded	yes
Coding	N
Thread type	M23

### Material specifications

Seal material	FPM
Housing material	Metal
Housing material	High-grade steel 1.4305

### Connection data

Conductor connection	
Connection method	Crimp connection

### Electrical properties

Contact	
Contact diameter	1 mm
Max. current	8 A
Nominal voltage U <sub>N</sub>	48 V AC 74 V DC
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

### Connector

Type	straight
Direction of rotation	Standard

Connection 1	
Head design	Socket

### Cable/line

External cable diameter	6 mm ... 10 mm
-------------------------	----------------

### Environmental and real-life conditions

# RF-17S1N8A9V02 - Coupler connector



1614000

<https://www.phoenixcontact.com/gb/products/1614000>

## Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-20 °C ... 125 °C
Altitude	2000 m


# RF-17S1N8A9V02 - Coupler connector

1614000

<https://www.phoenixcontact.com/gb/products/1614000>

## Drawings

Dimensional drawing



Dimensional drawing

# RF-17S1N8A9V02 - Coupler connector




1614000

<https://www.phoenixcontact.com/gb/products/1614000>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1614000>

	<b>cUL Recognized</b>			
	Approval ID: E153698-20090723			
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
	48 V	1 A	26	-

	<b>UL Recognized</b>			
	Approval ID: E153698-20090723			
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
	48 V	1 A	26	-

# RF-17S1N8A9V02 - Coupler connector



1614000

<https://www.phoenixcontact.com/gb/products/1614000>

## Classifications

### ECLASS

ECLASS-13.0	27440116
-------------	----------

### ETIM

ETIM 9.0	EC002635
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# RF-17S1N8A9V02 - Coupler connector



1614000

<https://www.phoenixcontact.com/gb/products/1614000>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	8114c391-098b-4473-bce9-acb56466c273

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)