


# Geberit Mapress Stainless Steel cap



Example image



## APPLICATION PURPOSES

- For cold and hot potable water
- For cooling and heating water without antifreeze agent
- For cooling and heating water with antifreeze agent
- For district heating water ≤ 120 °C
- For saturated steam ≤ 120 °C
- For service water and process water
- For treated water
- For rainwater with a pH value ≥ 5.5
- For grey and black water with a pH value ≥ 5.5

- For extinguishing water (wet)
- For extinguishing water (wet/dry, dry)
- For sprinklers (wet)
- For chemicals and technical liquids
- For compressed air (oil purity class 0–3)
- For negative pressure
- For inert gases (e.g. nitrogen)
- For industrial gases (e.g. acetylene, shielding gases)
- For technical building systems, industry and shipbuilding
- For permanent termination of pipe ends

## CHARACTERISTICS

- Pressing indicator
- Leaky if unpressed
- Seal ring made of CIIR, black
- Pressing socket with transparent protection plug

## TECHNICAL DATA

Product material                      CrNiMo steel 1.4401 (EN 10088)

| Art. no. | DN | d, ø<br>mm | L<br>cm | Z<br>cm |
|----------|----|------------|---------|---------|
| 33212    | 12 | 15         | 2.3     | 0.3     |
| 33213    | 15 | 18         | 2.3     | 0.3     |
| 33214    | 20 | 22         | 2.4     | 0.3     |

| Art. no. | DN  | d <sub>ø</sub><br>mm | L<br>cm | z<br>cm |
|----------|-----|----------------------|---------|---------|
| 33215    | 25  | 28                   | 2.6     | 0.3     |
| 33216    | 32  | 35                   | 2.9     | 0.3     |
| 33217    | 40  | 42                   | 3.3     | 0.3     |
| 33218    | 50  | 54                   | 3.8     | 0.3     |
| 33219    | 65  | 76.1                 | 6       | 0.7     |
| 33220    | 80  | 88.9                 | 6.7     | 0.7     |
| 33221    | 100 | 108                  | 8.2     | 0.7     |