

Eaton 135735

Catalog Number: 135735

Eaton Moeller® series E65 Thru-beam photoelectric sensor, transmitter, Sn=15m, 4L, 10-30VDC, NPN, PNP, quad 40, insulated material, M12

General specifications



Product Name	Catalog Number
Eaton Moeller® series E65 Thru-beam photoelectric sensor	135735
	EAN
	4015081325283
Product Length/Depth	Product Height
139.7 mm	139.7 mm
Product Width	Product Weight
38.1 mm	0.11 kg
Certifications	Catalog Notes
Certified by UL for use in Canada	Yellow
CSA-C22.2 No. 14	
UL File No.: E166051	
UL	
UL 508	
UL Category Control No.: NRKH, NRKH7	
CSA File No.: UL report applies to both US and Canada	
CE	
IEC/EN 60947-5-2	

Product specifications

Type

Optical sensors

Device type

Transmitter

Electric connection type

Connector M12

Fitted with:

Transmitter (for combination with detector)

Enclosure material

Plastic

Enclosure type

Cuboid

Explosion safety category for dust

None

Explosion safety category for gas

None

Functions

Thru-light beam

Protection against wire breakage

Short-circuit protection

For combination with detector

Protection against polarity reversal

Voltage type

DC

Wire size

0

Connection type

Plug-in connection M12 x 1

4-wire

Cable sheath material

Polyvinyl chloride (PVC)

Light type

Polarity free red light

Degree of protection

NEMA 4X

IP68

Resources

Catalogs

Product Range Catalog Sensors – products, basic information, applications

Declarations of conformity

DA-DC-00004657.pdf

DA-DC-00004652.pdf

Drawings

eaton-proximity-switches-dimensions-012.eps

eaton-proximity-switches-e65-diffuse-reflective-sensor-dimensions.eps

eaton-proximity-switches-e65-3d-drawing.eps

Installation instructions

IL05305004Z

mCAD model

DA-CD-90_28290_004

DA-CS-90_28290_004

Interface type

Other

LED indicator

Status indication of Operating voltage: Green LED

Status indication of Switching state: Red LED

Switch function type

Other

Load current

Max. 100 mA (I_e)

Laser protection class

None

Operation agent-safety class

Safety class 2

Shock resistance

50 g, Mechanical, Shock duration 10 ms

Optical surface material

Plastic

Output current (mA) - max

0 mA

Output current at protected output - max

0 mA

Rated control supply voltage (Us) at AC, 50 Hz - max

0 V

Rated control supply voltage (Us) at AC, 50 Hz - min

0 V

Rated control supply voltage (Us) at AC, 60 Hz - max

0 V

Rated control supply voltage (Us) at AC, 60 Hz - min

0 V

Rated control supply voltage (Us) at DC - max

30 V

Rated control supply voltage (Us) at DC - min

10 V

Rated switching distance (S_n)

15000 mm

Reflector distance - min

0 mm

Sensor height

55 mm

Sensor length

41 mm

Switching distance - max

15000 mm

Switching voltage of OSSD at state high

0 V

Transmission range of the safety field

0 m

Voltage rating - max

30 V

Safety type (IEC 61496-1)

1

Switching frequency

0 Hz

Sensing mode

Light-/dark switching

Switching output type

PNP

Sensor material

Insulated material

Wavelength of the sensor

660 nm

Width sensor

33 mm

Product category

E65 SM Series

Response time

1 ms

Ambient operating temperature - max

55 °C

Ambient operating temperature - min

-25 °C

Ambient storage temperature - max

70 °C

Ambient storage temperature - min

-25 °C

Diameter sensor

0 mm

Light dot size

0 mm²

Number of contact energized outputs with signalling function

0

Number of outputs (protected contact energized)

0

Number of outputs (protected semiconductor)

0

Number of outputs (semiconductor with signaling function)

0

Opening angle

0 °

Operating temperature - max

55 °C

Operating temperature - min

-25 °C

Operational current (Ib) in the switched state at 24 V DC

40 A

Adjustment type

Other



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.
All other trademarks are property of their respective owners.



Eaton.com/socialmedia