



output coupler with plug-in relay, 230 V AC/DC, 1 change-over contact, spring-loaded terminal (push-in), width 6.2 mm, thermal current 6 A, hard gold-plated

product brand name	SIRIUS
product category	SIRIUS 3RQ4 coupling relay, narrow design
product designation	Coupling relay with plug-in relay
design of the product	output coupling link
product type designation	3RQ4
General technical data	
display version LED	Yes
product feature protective coating on printed-circuit board	No
product component	
• relay output	Yes
• semi-conductor output	No
power loss [W] maximum	1.2 W
consumed active power	1.3 W
insulation voltage for overvoltage category III according to IEC 60664 with degree of pollution 3 rated value	300 V
surge voltage resistance rated value	4 kV
maximum permissible voltage for protective separation	
• between control and auxiliary circuit	300 V
• between control and auxiliary circuit according to IEC 60947-1	300 V
percental drop-out voltage related to the input voltage	10 %
flammability class of enclosure material	UL94 V-0
shock resistance	
• according to IEC 60068-2-27	sinusoidal half-wave 15g / 11 ms
vibration resistance	
• according to IEC 60068-2-6	6 ... 150 Hz: 2 g
operating frequency maximum	72 000 1/h
switching behavior	monostable
mechanical service life (operating cycles) typical	10 000 000
electrical endurance (operating cycles)	
• at AC-15 at 250 V typical	100 000
thermal current	6 A
reference code according to IEC 81346-2	K
Substance Prohibitance (Date)	09/26/2024
SVHC substance name	Lead - 7439-92-1
Weight	34 g
Control circuit/ Control	
control supply voltage at AC	
• at 50 Hz rated value	230 V
• at 60 Hz rated value	230 V
control supply voltage frequency	

• 1 rated value	50 Hz
• 2 rated value	60 Hz
control supply voltage at DC rated value	230 V
operating range factor control supply voltage rated value at DC	
• initial value	0.8
• full-scale value	1.1
operating range factor control supply voltage rated value at AC at 50 Hz	
• initial value	0.8
• full-scale value	1.1
operating range factor control supply voltage rated value at AC at 60 Hz	
• initial value	0.8
• full-scale value	1.1
ON-delay time	
• at AC maximum	10 ms
• at DC maximum	8 ms
OFF-delay time maximum	10 ms
Switching Function	
design of the switching function positively driven	No
Digital Outputs	
property of the output short-circuit proof	No
Mechanical data	
product component plug-in socket	Yes
design of the relay operating mechanism	poled
Short-circuit protection	
design of the fuse link for short-circuit protection of the auxiliary switch required	fuse gG: 4 A
Auxiliary circuit	
type of switching contact	Changeover contact
material of contact coating	hard gold-plated
material of switching contacts	AgSnO2 hard gold-plated
number of CO contacts for auxiliary contacts	1
operational current of auxiliary contacts at AC-15	
• at 24 V	3 A
• at 250 V	3 A
operational current of auxiliary contacts at DC-13	
• at 24 V	1 A
• at 125 V	0.2 A
• at 250 V	0.1 A
contact reliability of auxiliary contacts	one incorrect switching operation of 100 million switching operations (5 V, 1 mA)
Main circuit	
type of voltage	AC/DC
ampacity of the output relay at AC-15 at 250 V at 50/60 Hz	3 A
ampacity of the output relay at DC-13	
• at 24 V	1 A
• at 125 V	0.2 A
• at 250 V	0.1 A
Electromagnetic compatibility	
electromagnetic compatibility	acc. to EN 60947-5-1
EMC emitted interference according to IEC 60947-1	ambience A (industrial sector)
EMC immunity according to IEC 60947-1	corresponds to degree of severity 3
conducted interference	
• due to burst according to IEC 61000-4-4	2 kV
• due to conductor-earth surge according to IEC 61000-4-5	2 kV
• due to conductor-conductor surge according to IEC 61000-4-5	1 kV
field-based interference according to IEC 61000-4-3	10 V/m
electrostatic discharge according to IEC 61000-4-2	6 kV contact discharge / 8 kV air discharge
Display	

display version as status display by LED		LED green	
Connections/ Terminals			
product function removable terminal		No	
type of electrical connection			
• for auxiliary and control circuit		spring-loaded terminals (push-in)	
type of connectable conductor cross-sections			
• solid		1x (0.25 ... 2.5 mm²)	
• finely stranded with core end processing		1x (0.25 ... 1.5 mm²)	
• finely stranded without core end processing		1x (0.25 ... 2.5 mm²)	
• for AWG cables solid		1 x (20 ... 14)	
• for AWG cables stranded		1x (20 ... 14)	
connectable conductor cross-section			
• solid		0.25 ... 2.5 mm²	
• finely stranded with core end processing		0.25 ... 1.5 mm²	
• finely stranded without core end processing		0.25 ... 2.5 mm²	
AWG number as coded connectable conductor cross section			
• solid		20 ... 14	
• stranded		20 ... 14	
size of the screwdriver tip		PZ1	
stripped length		10 mm	
Installation/ mounting/ dimensions			
mounting position		any	
fastening method		snap-on mounting	
height		93 mm	
width		6.2 mm	
depth		88.5 mm	
required spacing			
• with side-by-side mounting			
— forwards		0 mm	
— backwards		0 mm	
— upwards		0 mm	
— downwards		0 mm	
— at the side		0 mm	
• for grounded parts			
— forwards		0 mm	
— backwards		0 mm	
— upwards		0 mm	
— at the side		0 mm	
— downwards		0 mm	
• for live parts			
— forwards		0 mm	
— backwards		0 mm	
— upwards		0 mm	
— downwards		0 mm	
— at the side		0 mm	
Ambient conditions			
installation altitude at height above sea level maximum		2 000 m	
ambient temperature			
• during operation		-25 ... +60 °C	
• during storage		-40 ... +85 °C	
• during transport		-40 ... +85 °C	
relative humidity during operation		10 ... 95 %	
Approvals Certificates			
General Product Approval		other	Environment



[Confirmation](#)



Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RQ4118-2AF01>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RQ4118-2AF01>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)


<https://support.industry.siemens.com/cs/ww/en/ps/3RQ4118-2AF01>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RQ4118-2AF01&lang=en

Characteristic: Derating

<https://support.industry.siemens.com/cs/ww/en/ps/3RQ4118-2AF01/manual>



last modified:

5/16/2025