

4

3

2

1


© 2024 TE Connectivity. All Rights Reserved.

REVISIONS

| P | LTR | DESCRIPTION             | DATE      | DWN | APVD |
|---|-----|-------------------------|-----------|-----|------|
|   | BA  | INITIAL DRAWING RELEASE | 04SEP2024 | AR  | GT   |
|   |     |                         |           |     |      |
|   |     |                         |           |     |      |
|   |     |                         |           |     |      |

FOR FURTHER DETAILS PLEASE REFER TO  
THICK FILM PRECISION RESISTOR TYPE RT73 SERIES


RECOMMENDED LAND PATTERN




| TYPE    | SIZE (INCH) | A (mm) | B (mm) | C (mm) | D (mm) |
|---------|-------------|--------|--------|--------|--------|
| RT73 2A | 0805        | 1.3    | 2.5    | 1.05   | 0.6    |

RoHS Compliant

| TYPE<br>(INCH SIZE CODE) | L<br>(mm) | W<br>(mm) | c<br>(mm) | d<br>(mm)                           | t<br>(mm) |
|--------------------------|-----------|-----------|-----------|-------------------------------------|-----------|
| 2A (0805)                | 2.0±0.2   | 1.25±0.1  | 0.25±0.15 | 0.3 <sup>+0.2</sup> <sub>-0.1</sub> | 0.5±0.1   |




|                                                                                       |                                        |                  |           |                                                                                                       |           |            |
|---------------------------------------------------------------------------------------|----------------------------------------|------------------|-----------|-------------------------------------------------------------------------------------------------------|-----------|------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                |                                        | DWN<br>ASHOK RAJ | 04SEP2024 |  TE Connectivity |           |            |
| DIMENSIONS:<br>mm                                                                     |                                        | CHK<br>TRACY G   | 04SEP2024 |                                                                                                       |           |            |
|  | TOLERANCES UNLESS OTHERWISE SPECIFIED: | APVD<br>TRACY G  | 04SEP2024 | NAME<br>THICK FILM PRECISION RESISTOR<br>TYPE RT73 2A SERIES                                          |           |            |
|                                                                                       |                                        | PRODUCT SPEC     | -         |                                                                                                       |           |            |
|                                                                                       |                                        | APPLICATION SPEC | -         | SIZE                                                                                                  | CAGE CODE | DRAWING NO |
| MATERIAL                                                                              | FINISH                                 | WEIGHT           | -         | A3                                                                                                    | 00779     | C=2176766  |
| -                                                                                     | -                                      | CUSTOMER DRAWING | SCALE     | 50:1                                                                                                  | SHEET     | 1 OF 5     |
| -                                                                                     | -                                      |                  |           |                                                                                                       | REV       | BA         |

REVISIONS

| P | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|-----|-------------|------|-----|------|
|   | -   | SEE SHEET 1 | -    | -   | -    |
|   |     |             |      |     |      |
|   |     |             |      |     |      |
|   |     |             |      |     |      |

SCHEDULE

| TCPN        | CATALOGUE NUMBER | PART DESCRIPTION                  | PART STATUS |
|-------------|------------------|-----------------------------------|-------------|
| 2176766-1   | RT73F2A133KBDT   | RT 2A 0.25W 133K 0.1% 25PPM 5K RL | PRODUCTION  |
| 2176766-2   | RT73F2A137KBDT   | RT 2A 0.25W 137K 0.1% 25PPM 5K RL | PRODUCTION  |
| 2176766-3   | RT73F2A140KBDT   | RT 2A 0.25W 140K 0.1% 25PPM 5K RL | PRODUCTION  |
| 2176766-4   | RT73F2A143KBDT   | RT 2A 0.25W 143K 0.1% 25PPM 5K RL | PRODUCTION  |
| 2176766-5   | RT73F2A147KBDT   | RT 2A 0.25W 147K 0.1% 25PPM 5K RL | PRODUCTION  |
| 2176766-6   | RT73F2A150KBDT   | RT 2A 0.25W 150K 0.1% 25PPM 5K RL | PRODUCTION  |
| 2176766-7   | RT73F2A154KBDT   | RT 2A 0.25W 154K 0.1% 25PPM 5K RL | PRODUCTION  |
| 2176766-8   | RT73F2A158KBDT   | RT 2A 0.25W 158K 0.1% 25PPM 5K RL | PRODUCTION  |
| 2176766-9   | RT73F2A162KBDT   | RT 2A 0.25W 162K 0.1% 25PPM 5K RL | PRODUCTION  |
| 1-2176766-0 | RT73F2A165KBDT   | RT 2A 0.25W 165K 0.1% 25PPM 5K RL | PRODUCTION  |
| 1-2176766-1 | RT73F2A169KBDT   | RT 2A 0.25W 169K 0.1% 25PPM 5K RL | PRODUCTION  |
| 1-2176766-2 | RT73F2A174KBDT   | RT 2A 0.25W 174K 0.1% 25PPM 5K RL | PRODUCTION  |
| 1-2176766-3 | RT73F2A178KBDT   | RT 2A 0.25W 178K 0.1% 25PPM 5K RL | PRODUCTION  |
| 1-2176766-4 | RT73F2A182KBDT   | RT 2A 0.25W 182K 0.1% 25PPM 5K RL | PRODUCTION  |
| 1-2176766-5 | RT73F2A187KBDT   | RT 2A 0.25W 187K 0.1% 25PPM 5K RL | PRODUCTION  |
| 1-2176766-6 | RT73F2A191KBDT   | RT 2A 0.25W 191K 0.1% 25PPM 5K RL | PRODUCTION  |
| 1-2176766-7 | RT73F2A196KBDT   | RT 2A 0.25W 196K 0.1% 25PPM 5K RL | PRODUCTION  |
| 1-2176766-8 | RT73F2A200KBDT   | RT 2A 0.25W 200K 0.1% 25PPM 5K RL | PRODUCTION  |
| 1-2176766-9 | RT73F2A205KBDT   | RT 2A 0.25W 205K 0.1% 25PPM 5K RL | PRODUCTION  |
| 2-2176766-0 | RT73F2A210KBDT   | RT 2A 0.25W 210K 0.1% 25PPM 5K RL | PRODUCTION  |
| 2-2176766-1 | RT73F2A215KBDT   | RT 2A 0.25W 215K 0.1% 25PPM 5K RL | PRODUCTION  |
| 2-2176766-2 | RT73F2A221KBDT   | RT 2A 0.25W 221K 0.1% 25PPM 5K RL | PRODUCTION  |
| 2-2176766-3 | RT73F2A226KBDT   | RT 2A 0.25W 226K 0.1% 25PPM 5K RL | PRODUCTION  |
| 2-2176766-4 | RT73F2A232KBDT   | RT 2A 0.25W 232K 0.1% 25PPM 5K RL | PRODUCTION  |
| 2-2176766-5 | RT73F2A237KBDT   | RT 2A 0.25W 237K 0.1% 25PPM 5K RL | PRODUCTION  |


|                                                                                                  |  |                               |  |                                                                                                                 |  |
|--------------------------------------------------------------------------------------------------|--|-------------------------------|--|-----------------------------------------------------------------------------------------------------------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                           |  | DWN<br>ASHOK RAJ<br>04SEP2024 |  | <div>TE Connectivity</div> |  |
| DIMENSIONS:<br>mm                                                                                |  | CHK<br>TRACY G<br>04SEP2024   |  |                                                                                                                 |  |
| <div></div> |  | APVD<br>TRACY G<br>04SEP2024  |  | NAME<br>THICK FILM PRECISION RESISTOR<br>TYPE RT73 2A SERIES                                                    |  |
|                                                                                                  |  | PRODUCT SPEC                  |  |                                                                                                                 |  |
|                                                                                                  |  | APPLICATION SPEC              |  |                                                                                                                 |  |
| MATERIAL                                                                                         |  | WEIGHT                        |  | SIZE                                                                                                            |  |
| -                                                                                                |  | -                             |  | A3                                                                                                              |  |
| -                                                                                                |  | -                             |  | 00779                                                                                                           |  |
|                                                                                                  |  | CUSTOMER DRAWING              |  | SCALE 1:1                                                                                                       |  |
|                                                                                                  |  |                               |  | SHEET 2 OF 5                                                                                                    |  |
|                                                                                                  |  |                               |  | REV BA                                                                                                          |  |
|                                                                                                  |  |                               |  |                                                                                                                 |  |

REVISIONS

| P | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|-----|-------------|------|-----|------|
|   | -   | SEE SHEET 1 | -    | -   | -    |
|   |     |             |      |     |      |
|   |     |             |      |     |      |
|   |     |             |      |     |      |

SCHEDULE

| TCPN        | CATALOGUE NUMBER | PART DESCRIPTION                  | PART STATUS |
|-------------|------------------|-----------------------------------|-------------|
| 2-2176766-6 | RT73F2A243KBTD   | RT 2A 0.25W 243K 0.1% 25PPM 5K RL | PRODUCTION  |
| 2-2176766-7 | RT73F2A249KBTD   | RT 2A 0.25W 249K 0.1% 25PPM 5K RL | PRODUCTION  |
| 2-2176766-8 | RT73F2A255KBTD   | RT 2A 0.25W 255K 0.1% 25PPM 5K RL | PRODUCTION  |
| 2-2176766-9 | RT73F2A261KBTD   | RT 2A 0.25W 261K 0.1% 25PPM 5K RL | PRODUCTION  |
| 3-2176766-0 | RT73F2A267KBTD   | RT 2A 0.25W 267K 0.1% 25PPM 5K RL | PRODUCTION  |
| 3-2176766-1 | RT73F2A274KBTD   | RT 2A 0.25W 274K 0.1% 25PPM 5K RL | PRODUCTION  |
| 3-2176766-2 | RT73F2A280KBTD   | RT 2A 0.25W 280K 0.1% 25PPM 5K RL | PRODUCTION  |
| 3-2176766-3 | RT73F2A287KBTD   | RT 2A 0.25W 287K 0.1% 25PPM 5K RL | PRODUCTION  |
| 3-2176766-4 | RT73F2A294KBTD   | RT 2A 0.25W 294K 0.1% 25PPM 5K RL | PRODUCTION  |
| 3-2176766-5 | RT73F2A301KBTD   | RT 2A 0.25W 301K 0.1% 25PPM 5K RL | PRODUCTION  |
| 3-2176766-6 | RT73F2A309KBTD   | RT 2A 0.25W 309K 0.1% 25PPM 5K RL | PRODUCTION  |
| 3-2176766-7 | RT73F2A316KBTD   | RT 2A 0.25W 316K 0.1% 25PPM 5K RL | PRODUCTION  |
| 3-2176766-8 | RT73F2A324KBTD   | RT 2A 0.25W 324K 0.1% 25PPM 5K RL | PRODUCTION  |
| 3-2176766-9 | RT73F2A332KBTD   | RT 2A 0.25W 332K 0.1% 25PPM 5K RL | PRODUCTION  |
| 4-2176766-0 | RT73F2A340KBTD   | RT 2A 0.25W 340K 0.1% 25PPM 5K RL | PRODUCTION  |
| 4-2176766-1 | RT73F2A348KBTD   | RT 2A 0.25W 348K 0.1% 25PPM 5K RL | PRODUCTION  |
| 4-2176766-2 | RT73F2A357KBTD   | RT 2A 0.25W 357K 0.1% 25PPM 5K RL | PRODUCTION  |
| 4-2176766-3 | RT73F2A365KBTD   | RT 2A 0.25W 365K 0.1% 25PPM 5K RL | PRODUCTION  |
| 4-2176766-4 | RT73F2A374KBTD   | RT 2A 0.25W 374K 0.1% 25PPM 5K RL | PRODUCTION  |
| 4-2176766-5 | RT73F2A383KBTD   | RT 2A 0.25W 383K 0.1% 25PPM 5K RL | PRODUCTION  |
| 4-2176766-6 | RT73F2A392KBTD   | RT 2A 0.25W 392K 0.1% 25PPM 5K RL | PRODUCTION  |
| 4-2176766-7 | RT73F2A402KBTD   | RT 2A 0.25W 402K 0.1% 25PPM 5K RL | PRODUCTION  |
| 4-2176766-8 | RT73F2A412KBTD   | RT 2A 0.25W 412K 0.1% 25PPM 5K RL | PRODUCTION  |
| 4-2176766-9 | RT73F2A422KBTD   | RT 2A 0.25W 422K 0.1% 25PPM 5K RL | PRODUCTION  |
| 5-2176766-0 | RT73F2A432KBTD   | RT 2A 0.25W 432K 0.1% 25PPM 5K RL | PRODUCTION  |


|                                                                                       |  |                                                                                 |           |                                                                                                       |                 |           |
|---------------------------------------------------------------------------------------|--|---------------------------------------------------------------------------------|-----------|-------------------------------------------------------------------------------------------------------|-----------------|-----------|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                |  | DWN<br>ASHOK RAJ                                                                | 04SEP2024 |  TE Connectivity |                 |           |
|                                                                                       |  | CHK<br>TRACY G                                                                  | 04SEP2024 |                                                                                                       |                 |           |
| DIMENSIONS:<br>mm                                                                     |  | TOLERANCES UNLESS OTHERWISE SPECIFIED:                                          |           | NAME<br>THICK FILM PRECISION RESISTOR<br>TYPE RT73 2A SERIES                                          |                 |           |
|  |  | 0 PLC ±-<br>1 PLC ±-<br>2 PLC ±-<br>3 PLC ±-<br>4 PLC ±-<br>ANGLES ±-<br>FINISH |           |                                                                                                       |                 |           |
| MATERIAL                                                                              |  | WEIGHT                                                                          |           | RESTRICTED TO                                                                                         |                 |           |
| -                                                                                     |  | -                                                                               |           | -                                                                                                     |                 |           |
| -                                                                                     |  | -                                                                               |           | -                                                                                                     |                 |           |
| CUSTOMER DRAWING                                                                      |  |                                                                                 |           | SCALE<br>1:1                                                                                          | SHEET<br>3 OF 5 | REV<br>BA |

REVISIONS

| P | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|-----|-------------|------|-----|------|
|   | -   | SEE SHEET 1 | -    | -   | -    |
|   |     |             |      |     |      |
|   |     |             |      |     |      |
|   |     |             |      |     |      |

SCHEDULE

| TCPN        | CATALOGUE NUMBER | PART DESCRIPTION                  | PART STATUS |
|-------------|------------------|-----------------------------------|-------------|
| 5-2176766-1 | RT73F2A442KBTD   | RT 2A 0.25W 442K 0.1% 25PPM 5K RL | PRODUCTION  |
| 5-2176766-2 | RT73F2A453KBTD   | RT 2A 0.25W 453K 0.1% 25PPM 5K RL | PRODUCTION  |
| 5-2176766-3 | RT73F2A464KBTD   | RT 2A 0.25W 464K 0.1% 25PPM 5K RL | PRODUCTION  |
| 5-2176766-4 | RT73F2A475KBTD   | RT 2A 0.25W 475K 0.1% 25PPM 5K RL | PRODUCTION  |
| 5-2176766-5 | RT73F2A487KBTD   | RT 2A 0.25W 487K 0.1% 25PPM 5K RL | PRODUCTION  |
| 5-2176766-6 | RT73F2A499KBTD   | RT 2A 0.25W 499K 0.1% 25PPM 5K RL | PRODUCTION  |
| 5-2176766-7 | RT73F2A511KBTD   | RT 2A 0.25W 511K 0.1% 25PPM 5K RL | PRODUCTION  |
| 5-2176766-8 | RT73F2A523KBTD   | RT 2A 0.25W 523K 0.1% 25PPM 5K RL | PRODUCTION  |
| 5-2176766-9 | RT73F2A536KBTD   | RT 2A 0.25W 536K 0.1% 25PPM 5K RL | PRODUCTION  |
| 6-2176766-0 | RT73F2A549KBTD   | RT 2A 0.25W 549K 0.1% 25PPM 5K RL | PRODUCTION  |
| 6-2176766-1 | RT73F2A562KBTD   | RT 2A 0.25W 562K 0.1% 25PPM 5K RL | PRODUCTION  |
| 6-2176766-2 | RT73F2A576KBTD   | RT 2A 0.25W 576K 0.1% 25PPM 5K RL | PRODUCTION  |
| 6-2176766-3 | RT73F2A590KBTD   | RT 2A 0.25W 590K 0.1% 25PPM 5K RL | PRODUCTION  |
| 6-2176766-4 | RT73F2A604KBTD   | RT 2A 0.25W 604K 0.1% 25PPM 5K RL | PRODUCTION  |
| 6-2176766-5 | RT73F2A619KBTD   | RT 2A 0.25W 619K 0.1% 25PPM 5K RL | PRODUCTION  |
| 6-2176766-6 | RT73F2A634KBTD   | RT 2A 0.25W 634K 0.1% 25PPM 5K RL | PRODUCTION  |
| 6-2176766-7 | RT73F2A649KBTD   | RT 2A 0.25W 649K 0.1% 25PPM 5K RL | PRODUCTION  |
| 6-2176766-8 | RT73F2A665KBTD   | RT 2A 0.25W 665K 0.1% 25PPM 5K RL | PRODUCTION  |
| 6-2176766-9 | RT73F2A681KBTD   | RT 2A 0.25W 681K 0.1% 25PPM 5K RL | PRODUCTION  |
| 7-2176766-0 | RT73F2A698KBTD   | RT 2A 0.25W 698K 0.1% 25PPM 5K RL | PRODUCTION  |
| 7-2176766-1 | RT73F2A715KBTD   | RT 2A 0.25W 715K 0.1% 25PPM 5K RL | PRODUCTION  |
| 7-2176766-2 | RT73F2A732KBTD   | RT 2A 0.25W 732K 0.1% 25PPM 5K RL | PRODUCTION  |
| 7-2176766-3 | RT73F2A750KBTD   | RT 2A 0.25W 750K 0.1% 25PPM 5K RL | PRODUCTION  |
| 7-2176766-4 | RT73F2A768KBTD   | RT 2A 0.25W 768K 0.1% 25PPM 5K RL | PRODUCTION  |
| 7-2176766-5 | RT73F2A787KBTD   | RT 2A 0.25W 787K 0.1% 25PPM 5K RL | PRODUCTION  |


|                                                                                       |  |                                                                       |  |                                                                                                       |  |                                                              |  |                            |  |                    |  |
|---------------------------------------------------------------------------------------|--|-----------------------------------------------------------------------|--|-------------------------------------------------------------------------------------------------------|--|--------------------------------------------------------------|--|----------------------------|--|--------------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                |  | DWN<br>ASHOK RAJ 04SEP2024                                            |  |  TE Connectivity |  |                                                              |  |                            |  |                    |  |
| DIMENSIONS:<br>mm                                                                     |  | CHK<br>TRACY G 04SEP2024                                              |  |                                                                                                       |  |                                                              |  |                            |  |                    |  |
|  |  | TOLERANCES UNLESS OTHERWISE SPECIFIED:                                |  | APVD<br>TRACY G 04SEP2024                                                                             |  | NAME<br>THICK FILM PRECISION RESISTOR<br>TYPE RT73 2A SERIES |  |                            |  |                    |  |
|                                                                                       |  | 0 PLC ±-<br>1 PLC ±-<br>2 PLC ±-<br>3 PLC ±-<br>4 PLC ±-<br>ANGLES ±- |  | PRODUCT SPEC                                                                                          |  |                                                              |  |                            |  |                    |  |
|                                                                                       |  | MATERIAL<br>-<br>-                                                    |  | FINISH<br>-<br>-                                                                                      |  |                                                              |  | APPLICATION SPEC<br>-<br>- |  |                    |  |
|                                                                                       |  | WEIGHT<br>-                                                           |  | SIZE<br>A 3                                                                                           |  | CAGE CODE<br>00779                                           |  | DRAWING NO<br>C-2176766    |  | RESTRICTED TO<br>- |  |
| CUSTOMER DRAWING                                                                      |  |                                                                       |  | SCALE<br>1:1                                                                                          |  | SHEET<br>4 OF 5                                              |  | REV<br>BA                  |  |                    |  |

REVISIONS

| P | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|-----|-------------|------|-----|------|
|   | -   | SEE SHEET 1 | -    | -   | -    |
|   |     |             |      |     |      |
|   |     |             |      |     |      |
|   |     |             |      |     |      |

SCHEDULE

| TCPN        | CATALOGUE NUMBER | PART DESCRIPTION                  | PART STATUS |
|-------------|------------------|-----------------------------------|-------------|
| 7-2176766-6 | RT73F2A806KBTD   | RT 2A 0.25W 806K 0.1% 25PPM 5K RL | PRODUCTION  |
| 7-2176766-7 | RT73F2A825KBTD   | RT 2A 0.25W 825K 0.1% 25PPM 5K RL | PRODUCTION  |
| 7-2176766-8 | RT73F2A845KBTD   | RT 2A 0.25W 845K 0.1% 25PPM 5K RL | PRODUCTION  |
| 7-2176766-9 | RT73F2A866KBTD   | RT 2A 0.25W 866K 0.1% 25PPM 5K RL | PRODUCTION  |
| 8-2176766-0 | RT73F2A887KBTD   | RT 2A 0.25W 887K 0.1% 25PPM 5K RL | PRODUCTION  |
| 8-2176766-1 | RT73F2A909KBTD   | RT 2A 0.25W 909K 0.1% 25PPM 5K RL | PRODUCTION  |
| 8-2176766-2 | RT73F2A931KBTD   | RT 2A 0.25W 931K 0.1% 25PPM 5K RL | PRODUCTION  |
| 8-2176766-3 | RT73F2A953KBTD   | RT 2A 0.25W 953K 0.1% 25PPM 5K RL | PRODUCTION  |
| 8-2176766-4 | RT73F2A976KBTD   | RT 2A 0.25W 976K 0.1% 25PPM 5K RL | PRODUCTION  |
| 8-2176766-5 | RT73F2A1M0BTD    | RT 2A 0.25W 1M0 0.1% 25PPM 5K RL  | PRODUCTION  |
| 8-2176766-6 | RT73F2A1M02BTD   | RT 2A 0.25W 1M02 0.1% 25PPM 5K RL | PRODUCTION  |
| 8-2176766-7 | RT73F2A1M05BTD   | RT 2A 0.25W 1M05 0.1% 25PPM 5K RL | PRODUCTION  |
| 8-2176766-8 | RT73F2A1M07BTD   | RT 2A 0.25W 1M07 0.1% 25PPM 5K RL | PRODUCTION  |
| 8-2176766-9 | RT73F2A1M1BTD    | RT 2A 0.25W 1M1 0.1% 25PPM 5K RL  | PRODUCTION  |
| 9-2176766-0 | RT73F2A1M13BTD   | RT 2A 0.25W 1M13 0.1% 25PPM 5K RL | PRODUCTION  |
| 9-2176766-1 | RT73F2A1M15BTD   | RT 2A 0.25W 1M15 0.1% 25PPM 5K RL | PRODUCTION  |
| 9-2176766-2 | RT73F2A1M18BTD   | RT 2A 0.25W 1M18 0.1% 25PPM 5K RL | PRODUCTION  |
| 9-2176766-3 | RT73F2A1M21BTD   | RT 2A 0.25W 1M21 0.1% 25PPM 5K RL | PRODUCTION  |
| 9-2176766-4 | RT73F2A1M24BTD   | RT 2A 0.25W 1M24 0.1% 25PPM 5K RL | PRODUCTION  |
| 9-2176766-5 | RT73F2A1M27BTD   | RT 2A 0.25W 1M27 0.1% 25PPM 5K RL | PRODUCTION  |
| 9-2176766-6 | RT73F2A1M3BTD    | RT 2A 0.25W 1M3 0.1% 25PPM 5K RL  | PRODUCTION  |
| 9-2176766-7 | RT73F2A1M33BTD   | RT 2A 0.25W 1M33 0.1% 25PPM 5K RL | PRODUCTION  |
| 9-2176766-8 | RT73F2A1M37BTD   | RT 2A 0.25W 1M37 0.1% 25PPM 5K RL | PRODUCTION  |
| 9-2176766-9 | RT73F2A1M4BTD    | RT 2A 0.25W 1M4 0.1% 25PPM 5K RL  | PRODUCTION  |

|                                                                                       |  |                                                                       |           |                                                                                                       |                 |           |
|---------------------------------------------------------------------------------------|--|-----------------------------------------------------------------------|-----------|-------------------------------------------------------------------------------------------------------|-----------------|-----------|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                |  | DWN<br>ASHOK RAJ                                                      | 04SEP2024 |  TE Connectivity |                 |           |
|                                                                                       |  | CHK<br>TRACY G                                                        | 04SEP2024 |                                                                                                       |                 |           |
| DIMENSIONS:<br>mm                                                                     |  | TOLERANCES UNLESS OTHERWISE SPECIFIED:                                |           | NAME<br>THICK FILM PRECISION RESISTOR<br>TYPE RT73 2A SERIES                                          |                 |           |
|  |  | 0 PLC ±-<br>1 PLC ±-<br>2 PLC ±-<br>3 PLC ±-<br>4 PLC ±-<br>ANGLES ±- |           |                                                                                                       |                 |           |
| MATERIAL                                                                              |  | FINISH                                                                |           | RESTRICTED TO                                                                                         |                 |           |
| -                                                                                     |  | -                                                                     |           | -                                                                                                     |                 |           |
| -                                                                                     |  | -                                                                     |           | -                                                                                                     |                 |           |
| CUSTOMER DRAWING                                                                      |  |                                                                       |           | SCALE<br>1:1                                                                                          | SHEET<br>5 OF 5 | REV<br>BA |