

GHO 26-82 D

Specifications

Name	GHO 26-82 D
Master-Order-No.	0 601 5A4 300
Internal ID	38966
Status	OK
Created	2015-07-17 (mrauscher)

Description

Product line

- ▶ Trade / Industry

Title

- ▶ GHO 26-82 D Professional

Positioning

- ▶ Comfortable to use due to chip clearance on both sides and cutting depth adjustment up to 2.6 mm

User benefit

- ▶ Powerful 710 W motor for cutting depths of up to 2.6 mm
- ▶ Sturdy, flat aluminium base plate for the best planing results
- ▶ Wood chip clearance to left or right, as desired

Product type

- ▶ Planer

Technical data

Rated power input	710 W
Adjustable depth of cut	3 mm
Weight	2,8 kg
Adjustable rebating depth	9 mm
No-load speed	18000 rpm
Planing width	82 mm
Cutter width	82 mm

Noise/vibration information

Noise level	The A-rated noise level of the power tool is typically as follows: Sound pressure level 84 dB(A); Sound power level 95 dB (A). Uncertainty K= 3 dB.
-------------	---

CSO Selection

Order No. 1	0 601 5A4 370
-------------	---------------

Linked digital objects

Product image



ID: #213709

Operating Instructions, Western Europe




ID: #218602

Operating Instructions, Eastern Europe



ID: #218602

Dimensional drawing



ID: #233051

Application image



ID: #221077

ID: #219823

ID: #219819

GHO 26-82 D

CSO Selection

EAN-Code	3165140771191
Scope Of Supply	Carrying case Parallel guide Allen key KW 2.5 (ET no. 1 907 950 003) Fabric dust bag
Baretool number	3601EA4370
SOL Date	01.05.2016

Order No. 2	0 601 5A4 360
EAN-Code	3165140771177
Scope Of Supply	Carrying case Parallel guide Allen key KW 2.5 (ET no. 1 907 950 003) Fabric dust bag
Baretool number	3601EA4360
SOL Date	01.05.2016

10.08.2016 16:26:55

RBGB - Großbritannien - English