



3 SETTINGS FOR VARIABLE FAN SPEED



WHEEL-MOUNTED STEEL FRAME
FOR OUTSTANDING MOBILITY



PULL HANDLES FOR EASY MOVEMENT



ADJUSTABLE TILTING HEAD ROTATES
360° ON VERTICAL AXIS

ITEM. 05637

SIP 24" HEAVY-DUTY DRUM FAN

HEAVY-DUTY DRUM FAN FOR POWERFUL INDOOR AIR CIRCULATION

PRODUCT OVERVIEW

The **SIP 24" Heavy-Duty Drum Floor Fan** delivers powerful variable speed airflow to help cool spaces and circulate air in a variety of industrial environments. Wheel-mounted on a cradled steel frame, the drum enclosed, heavy-duty 3-blade fan can be rotated between 360° on its vertical axis to maximise air circulation and coverage.

Fans are essential in helping to provide improved air quality to indoor spaces.

FEATURES & BENEFITS

✓ POWERFUL AIRFLOW

A heavy-duty 3-blade fan is powered from a 120w motor to deliver powerful and consistent airflow coverage.

✓ VARIABLE SPEED SETTINGS

3 settings for variable fan speed:

- **Low:** 900rpm
- **Medium:** 1100rpm
- **High:** 1300rpm

✓ DYNAMIC AIRFLOW FUNCTION

The adjustable tilting fan head can be rotated 360° on its vertical axis for greater airflow coverage.

THIS PRODUCT COMES WITH AN SIP 2-YEAR SILVER WARRANTY*

FIND OUT MORE AT SIP-GROUP.COM/WARRANTY



ITEM. 05637

SIP 24" HEAVY-DUTY DRUM FAN

FEATURES & BENEFITS CONT.

✔ OUTSTANDING MOBILITY

The wheel-mounted cradled steel frame is fitted with pull handles which allows the fan to be easily moved between locations for use.

✔ ENHANCED SAFETY FEATURES

Fan blades are fully enclosed with solid mesh steel guarding for greater user safety.

A robust and balanced steel frame maintains fan stability when in use.

APPLICATIONS & USES

**DELIVERS POWERFUL VARIABLE SPEED
AIR CIRCULATION TO INDOOR SPACES**

**PERFECT FOR INDUSTRIAL, COMMERCIAL
& AGRICULTURAL WORKSHOP AREAS**

ITEM NO.	05637		
INPUT SUPPLY	230v (13A)		
MOTOR POWER	120w (0.16hp)		
POWER CABLE	200cm		
FAN DIAMETER	Ø 24" (609mm)		
SPEED SETTINGS	3 speed settings		
	Low	Medium	High
	900rpm	1100rpm	1300rpm
NOISE LEVEL	67dB(A)		
NET WEIGHT	11kg		
GROSS WEIGHT	12.7kg		
PRODUCT DIMENSIONS	695(H) x 665(W) x 258mm(D)		
PACKAGED DIMENSIONS	820(H) x 810(W) x 310mm(D)		