

PRODUCT SPOTLIGHT



DIN Rail Enclosures

Load centres for residential commercial applications



OVERVIEW


Robust surface mount plastic DIN rail loadcentre with hinged cover to protect control equipment.

ADVANTAGES

- Easily mounted base and cover protects control equipment
- Includes earth and neutral links
- Compliant with Australian Wiring Rules to meet all glow-wire standards up to 960°C
- Robust high impact resistant plastic construction
- Metal DIN rail provides robust mounting of DIN equipment
- Cover secures with robust steel screws
- Designed with generous space for wiring
- Supplied with standard circuit ID labels



SELECTION GUIDE



Catalogue No.	Poles	Dimensions (mm)			Links (all 16mm ² tunnels)	
		Height	Width	Depth	Earth	Neutral
LCP06	6	210	134	100	—	7
LCP09	9	210	188	100	4	7
LCP12	12	210	242	100	4	9
LCP18	18	210	350	100	4	14+7

