
ISO cylinder DSNU-25-320-PPV-A Part number: 34721 ★ Core product range



Data sheet

Feature	Value
Stroke	320 mm
Piston diameter	25 mm
Piston rod thread	M10x1,25
Cushioning	PPV: Pneumatic cushioning adjustable at both ends
Assembly position	Any
Conforms to standard	CETOP RP 52 P
	ISO 6432
Piston-rod end	Male thread
Design structure	Piston
	Piston rod
	Cylinder barrel
Position detection	For proximity sensor
Variants	Single-ended piston rod
Operating pressure	1 10 bar
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010[7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further
	operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Ambient temperature	-20 80 °C
Maritime classification	see certificate
Impact energy in end positions	0.3 J
Cushioning length	17 mm
Theoretical force at 6 bar, return stroke	247.4 N
Theoretical force at 6 bar, advance stroke	294.5 N
Moving mass with 0 mm stroke	71 g
Additional weight per 10 mm stroke	11 g
Basic weight for 0 mm stroke	238 g
Additional mass factor per 10 mm of stroke	6 g
Mounting type	with accessories
Pneumatic connection	G1/8
Materials note	Conforms to RoHS
Material cover	Wrought Aluminium alloy
	neutral anodisation
Material seals	NBR
	TPE-U(PU)
Material piston rod	High alloy steel, non-corrosive
Material cylinder barrel	High alloy steel, non-corrosive



FESTO