

LED Lighting LF3D/LF1D





Excellent optical performance and robust construction suitable for use in machine tools




# LUMIFE



# Effective solution for machine tools

LED lighting inside machine tool allows for clear identification of chatter marks



#### BEFORE

#### Hard to see chatter marks

Glares from LED lighting inside the machine tool could be mistaken as chatter marks while visually checking the machine operation. This often caused chatter marks to be left untreated, delaying maintenance and worsening the situation.





# AFTER

LED lighting improves machining efficiency

IDEC's unique optical technology enables the light to shine evenly on the surface, suppressing multiple shadows and allowing the operator to see scratches and unevenness on the workpiece. LF3D lighting makes it possible to check whether chatter marks have been generated or not easily, at a glance. Provides high-quality and uniform lighting on the surface of target objects and inside the work area

# Eliminates the multi-shadow effect






Reduced multi-shadow effect enables easy visual inspection of the machined surface. [Patent pending (LF3D)]

# Reduces reflection from light source


LED light source reflects on the workpiece and stripes appear. The LF3D LED allows the light to be evenly distributed to provide natural lighting, and enables visual inspection. [Patent pending (LF3D)]



LF3D-S (surface mount)

LF3D-F (recessed mount)

# Select from standard or diffused light distribution depending on the machine tool needs




## Equipped with glare mode to prevent operators from glare during maintenance

[Patent pending (LF3D)]

Modes can be changed by just the wiring. Complicated settings such as PWM and dedicated controllers are not required.

> Application example: Functions with opening & closing of doors / switching with control panel





\*1) Approx. 40% illumination

# Rugged construction and environmentally resistant

## Suitable for use in machine tools



#### Degree of protection IP67G / IP69K

Oil-resistant gasket and unique structural design achieves IP67G protection degree. (\*1)

Withstands exposure to water and oil. (\*2)

IP69K for use in high-pressure, high-temperature washdown. \*1) IP67F (LF1D)

\*2) Oil used for testing: Insoluble oil JIS N3-8



#### Robust material


Reinforced glass, stainless steel, zinc diecast, extruded aluminum prevents damage from scraps



## Resistant to high temperature

Wide operating temperature range (up to 55°C).

# Improved design and user-friendly



# Wide variety of connector types available



# Wide selection of models to suit a various machine tools

	For small machines	For small t	For large machines	
	$\langle \rangle$		NEW Contraction of the second se	
Application	Brightly lights machine tool tips and inside small machines		s brilliant light on the <mark>edges</mark> of tools used lens provides <mark>wide light</mark> k areas.	Wide illumination inside the work area or replacements for fluorescent lamps
Part no.	LF1D-C	LF3D-S	LF3D-F	LF1D-H/J
Shape	Surface mount	Surface mount	Recessed mount	Surface mount
Luminous Flux (typ.)	560 Im	<b>1700</b> lm		2000 lm (LF1D-H) 3000 lm (LF1D-J)
Reference Illuminance (typ.) at 1.0m directly below	180 lx	1800 lx (standard distribution) 1000 lx (diffused distribution)		560 lx (LF1D-H) 840 lx (LF1D-J)
Dimensions (W $\times$ H $\times$ D)	50 x 25 x 100 mm	$55.8\times17.5\times310\text{ mm}$	$80 \times 27 \times 307$ mm	$\begin{array}{c} 84 \times 24.8 \times 365 \text{ mm} \\ (\text{LF1D-H}) \\ 84 \times 24.8 \times 510 \text{ mm} \\ (\text{LF1D-J}) \end{array}$

# LF3D/LF1D LED Lighting

## 

#### LF3D LED Lighting

#### LF3D

#### Package Quantity: 1

Model		LF3D				
Light distribution		Standard		Diffused		
Style		Surface mount (*1)	Recessed mount	Surface mount (*1)	Recessed mount	
Illumination surface		Reinforced glass				
Connection direction	Cable / Connector	Part no. (Ordering no.)				
Side	5m cable	LF3D-SB2S05M		LF3D-SB1S05M		
	M8 connector	LF3D-SB2S2		LF3D-SB1S2	_	
Rear		_	LF3D-FB2B05M		LF3D-FB1B05M	
	5m cable		LF3D-F1B2B05M (*2)		LF3D-F1B1B05M (*2)	
			LF3D-F2B2B05M (*3)		LF3D-F2B1B05M (*3)	
		LF3D-SB2B1	LF3D-FB2B1			
	M12 connector		LF3D-F1B2B1 (*2)	LF3D-SB1B1	LF3D-FB1B1	
			LF3D-F2B2B1 (*3)			

\*1) Contact IDEC for customers using LF1D–E (EH/EN) or LF1D–F (FH).

\*2) Size and mounting centers compatible with LF2D–E (EH/EN). (LF3D-F1)


\*3) Size and mounting centers compatible with LF2D–F (FH). (LF3D-F2)

#### **Performance Specifications**

Model	LF3D			
Style	Uniform light source / slim type			
Light distribution	Standard Diffused			
Rated voltage	24V DC			
Operating voltage range	21.6 to 26.4V DC			
Rated Power (typ.) (at rated voltage)	9.2W			
Illumination color	Cool white			
Color temp. (typ.)	5700K			
Luminous Flux (typ.)	1700 lm			
Reference Illuminance (typ.) at 1.0m directly below	1800 lx 1000 lx			
Insulation resistance	$100M\Omega$ minimum (500V DC megger)			
Dielectric strength	1000V AC, 50/60Hz, 1 minute			
Vibration resistance (damage limits)	Frequency 5 to 55Hz, amplitude 0.5mm			
Shock resistance (damage limits)	1000m/s <sup>2</sup>			
Operating temperature	-30 to +55°C (no freezing)			
Operating relative humidity	45 to 85%RH (no condensation)			
Storage temperature	-35 to +70°C (no freezing)			
Operating atmosphere	No corrosive gas			
Light source life (*1)	50,000 hours (The illumination duration in which the brightness maintains a minimum of 70%) (Ta = $25^{\circ}$ C, $45^{\circ}$ RH max.)			
Degree of protection (*2)	Surface mount: IP65, IP67, IP67G, IP69K			
	Recessed mount: IP65, IP67, IP67G			
Glare save mode (GS-Mode) (*3)	White wire (pin no.1) - open: 100% light on White wire (pin no.1) and brown wire (pin no.2) - short-circuit: dim light			
Material (Main parts)	Main body:AluminumFront cover (surface mount):Stainless steelFlange (recessed mount):AluminumSide cover:Zinc die-cast (plating)Illumination part surface:Reinforced glassGasket:NBR			
Weight (approx.)	LF3D-S: 680g (*4) LF3D-F1: 830g (*4) LF3D-F: 770g (*4) LF3D-F2: 870g (*4)			
Light Distribution Curve (reference value) (unit: cd/1000 lm)				

- Due to variations in LED elements, products may vary in illumination color and illuminance.
- \*1) Not a guaranteed value. The actual life may differ depending on the operating environment and conditions. Specifications are subject to change without notice.
- Ta is the ambient temperature of this product.
- \*2) Testing conditions specified by IEC60529 (IP67), JIS C 0920 (IP67F/IP67G), and DIN40050-9 (IP69K)
- Not guaranteed for every operating condition (the rated value of the protective structure is when the product is mounted.)
- \*3) Dimming differs according to the operating environment. Not a fixed value. (Ta=25°C typ.)
- \*4) Weight of cable type.

#### Cross-sectional direction of light distribution



#### **Internal Circuit**

	Housing
Brown (pin no. 1)—	Constant-current
Blue (pin no. 3)—	power supply
White (pin no. 2)—	+ LED

#### LF1D LED Lighting

#### LF1D

LF1D-H/LF1D	)-J Long type	Package Quantity:		
Model		LF1D-H	LF1D-J	
Mount style		Surface mount		
Illumination sur	face	Reinforced glass		
Cable direction	Cable length	Part no. (Ordering no.)		
Side	5m	LF1D-H2F-2N-350	LF1D-J2F-2N-350	
Side	1.5m + M12 connector	LF1D-H2F-2N-3B0	LF1D-J2F-2N-3B0	
Rear	5m	LF1D-H2F-2N-450	LF1D-J2F-2N-450	
	1.5m + M12 connector	LF1D-H2F-2N-4B0	LF1D-J2F-2N-4B0	

#### LF1D-C Mini model L=100mm Package quantity: 1


Shape	Surface mount				
Illumination Surface	Reinforced glass				
Cable	Length	Part No.			
Side	3m	LF1D-C2F-2W-330			
Side	5m	LF1D-C2F-2W-350			
Dook	3m	LF1D-C2F-2W-430			
Back	5m	LF1D-C2F-2W-450			

#### **Performance Specifications**


Model	LF1D-H	LF1D-J	LF1D-C		
Style	Long type L=365mm	Long type L=510mm	Mini		
Light distribution	Diffused				
Rated voltage	24V DC		24V DC		
Operating voltage range	21.6 to 26.4V DC		21.6 to 26.4V DC		
Rated Power (typ.) (at rated voltage)	18.4W	27.6W	4.6W		
Illumination color	Neutral white	·	White		
Color temp. (typ.)	4700K		5,700K		
Luminous Flux (typ.)	2000 lm	3000 lm	560 lm		
Reference Illuminance (typ.) at 1.0m directly below	560 lx	840 lx	180 lx		
Insulation resistance	100MΩ minimum (500V DC m	egger)			
Dielectric strength	1000V AC, 50/60Hz, 1 minute				
Vibration resistance (damage limits)	Frequency 5 to 55Hz, amplitud	le 0.5mm			
Shock resistance (damage limits)	1000m/s2				
Operating temperature	-30 to +55°C (no freezing)				
Operating relative humidity	45 to 85%RH (no condensation)				
Storage temperature	-35 to +70°C (no freezing)				
Operating atmosphere	No corrosive gas				
Light source life (*1)	50,000 hours (The illumination duration in which the brightness maintains a minimum of 70%) (Ta=25°C, 45%RH max.)				
Degree of protection (*2)	IP67, IP67F, IP69K				
Material (Main parts)	Main body:AluminumFront cover (surface mount):Stainless steelIllumination part surface:Reinforced glassGasket:NBR				
Weight (approx.)	LF1D-H2F-2N-350: 1200g	LF1D-J2F-2N-350: 1600g	LF1D-C2F-2W-350: 420g		
Light Distribution Curve (reference value) (unit: cd/1000 lm)			90° 60° 200 30° 0°		


- Due to variations in LED elements, products may vary in illumination color and illuminance.
- \*1) Not a guaranteed value. The actual life may differ depending on the operating environment and conditions. Specifications are subject to change without notice. Ta is the ambient temperature of this product.
- \*2) Testing conditions specified by IEC60529 (IP67), JIS C 0920 (IP67F/IP67G), and DIN40050-9 (IP69K) Not guaranteed for every operating condition (the rated value of the protective structure is when the product is mounted.)

# Cross-sectional direction of light distribution



### **Internal Circuit**






8

#### **Dimensions (LF1D)**


Dimensions in mm

Note: For mounting hole layout and the size of mounting screws on the back of the LED unit, see the specification sheet and dimensions supplied with the product.


#### LF1D-H [long type] L=365mm] / LF1D-J [long type L=510mm]



#### Connector Wiring LF1D-H/J2F-2\*-\*B\* (M12 connector)




M12 connector: SAC-4P-MS SC0/150/1.5



Use a connector on the power supply side that satisfies the degree of protection. Recommended connector: Phoenix Contact SAC-4P-1.5-PUR/FS SCO

#### LF1D-C (mini model)



#### Accessories (LF3D)

#### Accessories exclusive for LF3D

Item	Shape	Туре	Part no. (Ordering no.)	Package quantity	Remarks
Mounting Bracket	Example(LF9Z-B21)	Side connection	LF9Z-B21	2 (for right and left, supplied with mounting screws)	mounting LF1D-E (EN/ EH) from the back with the same mounting centers.
		Back connection	LF9Z-B22	2 (for right and left, supplied with mounting screws)	
M12 connector cable	$\bigcirc$	Straight	LF9Z-CM13	1	Longth: 2m
	$\langle \rangle$	Right angle	LF9Z-CM23	1	Length: 3m

• Accessories are not supplied with the product.

#### 🕂 Safety Precautions

- Do not disassemble, repair, or modify the product. Otherwise electric shock, fire, or malfunction may occur.
- Turn off power before wiring. Make sure that the temperature has lowered sufficiently before wiring.
- To prevent electric shock or damage, ensure that the wiring is correct.
- Do not stare directly into the LED while it is lit, and do not project the light towards other people, otherwise eyes may be injured.
- The product is a general-purpose industrial electric device.
- Ensure correct operating temperature. Operating temperature is the ambient temperature where the product will be used. Temperature exceeding the specified value may cause rise in internal temperature and cause damage to the unit.

# • When using this product as part of or in connection with electrical equipment for general use (\*), use a DC power supply unit with a PSE mark that conforms to the technical standards of the Product Safety Electrical Appliance & Material (PSE). For installation, follow the laws and regulations such as technical standards for electrical equipment and construction equipment standards.

- \*) Electrical facilities mainly for general residences and stores, receiving AC 600V or less, and small power generation facilities.
- The product is for indoor use only. Do not use outdoors, otherwise insulation failure, electric shock, or failure may result.
- Do not use for applications which may cause harm or injury in case a malfunction or failure occurs.

#### Instructions

- Due to variations in LED elements, products may vary in illumination color and illuminance.
- Before designing equipment and powering up the product, confirm the specifications described in the instruction sheet.
- Apply voltage within the rated value, otherwise the LED elements maybe damaged.
- Do not use or store in a location subject to vibration and shock, otherwise electric shock or failure will result.
- Do not loosen screws, otherwise the protection characteristics will be impaired.
- To clean the cover, use a soft cloth with water or neutral detergent. Do not use solvents such as thinners, benzene, or alkaline, otherwise, discoloration, deterioration, or decrease in strength may occur.
- When using this product in environments subject to dust and water, make sure that the wiring part of cable or wire are dustproof/waterproof. Otherwise leakage, electric shock, or failure may occur.

- Do not use in the following locations:
  - ① Locations subject to high water pressure (environments exceeding protection degree IPX5, IPX7X or IPX9K in accordance with IEC 60529.)
  - ② Locations subject to dust (environments exceeding protection degree IP6X in accordance with IEC 60529.
  - ③ Environment subject to corrosive gases, volatile gases, flammable gases, or chemicals that could affect the safety and reliability of the product.
  - ④ Locations subject to electric or magnetic fields.
  - ⑤ Subject to flammable substances.
- © Exposed to direct sunlight, near heaters, high temperatures.
- ⑦ Exposed to salt water.
- Subject to condensation or freezing, such as cold storage warehouse or air cooler outlet (make sure that condensation or freezing do not occur).
   Exposed to ozone, radiation, UV or other locations where safety and reli-
- Exposed to ozone, radiation, UV or other locations where safety and reliability of the product.
- When using the product as a UL/c-UL listed product, use a Class 2 power supply.
- Some metal parts are surface treated and the appearance may vary depending on each part. Also, some scratches may appear on the surface but does not affect product performance.

#### Warranty

• The warranty period is one year after delivery to the specified location.

\*Exceptions to warranty coverage

The warranty period is reduced to six (6) months if the product is run continuously over 20 hours.


 In the event of a failure caused by our responsibility within the above period, we will replace the product free of charge at the place where the product was purchased or delivered.

\*Does not include expenses required for mounting, replacing, or installation work.

- Because internal elements deteriorate after 8 to 10 years of installation even if they have no defects in appearance, inspection and/or replacement
  are recommended. Operation condition: temperature 30°C, 3,000-hour operation per year (10 hours per day). (JIS C 8105-1)
- Product life is shortened under high operating temperature or when it is lit for long hours.
- Inspection and/or cleaning by user every 6 months is recommended.
- Inspection by contractors is recommended every 3 years.
- Do not use the product for a long time without inspection, otherwise smoke, fire, or electric shock may occur.

For details on mounting, wiring, and circuit examples, see the instruction manual from the below URL.

LF3D-S/F https://product.idec.com/?product=LF3D LF3D-F1 https://product.idec.com/?product=LF3D-F1 LF3D-F2 https://product.idec.com/?product=LF3D-F2







LF3D-F1



LF3D-S/F

URL

<sup>•</sup> LED lighting have a product life.

#### LF3D/LF1D LED Lighting



Interlock switches with solenoid



HS5L: 4-contact switches suitable for small doors. 2-contact switches suitable for food machinery and injection molding machines.

Safety edge switches

Conforms to ISO 13856-2 (pressure-sensitive protective devices).

Available August, 2021

Ensures safety without reducing the opening/closing speed of automatic doors. The rubber part is made of oil-resistant NBR material, suitable for environments where oil mist is dispersed.

Prevent momentary stops that cause machine failures



Safety relay modules

Improves productivity by predictive maintenance of safety systems

HR6S

HS1T: 5000N locking strength is suitable for large machines and equipment, ensuring operator safety.

E30BK1



Switching power supplies PS5R-V



High performance DIN rail power supplies with low profile, space saving 6-direction mounting, and spring-up terminals for wiring efficiency and safety. Mounting brackets are also available for direct mounting. Compliant with SEMI-F47 standards. (Certified for 208V AC input voltage.)

Smart RFID reader to manage user authority/log control




KW2D



The compact RFID reader mounts on ø22 panel cut-out. Water- and oil-proof with verification functions. Suitable for controlling and tracking access to production sites.

Reduce the cost of relay replacement





Durable and compact slim power relays with high contact allowable current.

# 

**30** COMPANIES

75

75 YEARS OF EXPERIENCE

- 3,900 EMPLOYEES WORLDWIDE
  - 100 000 + REFERENCES

# **EMEA SALES & CUSTOMER SUPPORT**

Contact our safety specialists at eu.support@idec.com

#### BENELUX

Belgicastraat 7/1 1930 ZAVENTEM Belgium BEL: (+32) 27 25 05 00 NL: (+31) (70) 799 91 51 be.sales@apem.com

#### FRANCE

55, avenue Edouard Herriot BP1 82303 CAUSSADE Cedex (+33) 5 63 93 14 98 fr.commercial@apem.com

#### GERMANY

Gewerbehof Giesing Paulsdorfferstr. 34, 2. OG D-81549 MUNICH MUNICH: (+49) 89 45 99 11 0 HAMBURG: (+49) 40 253054 0 info@apem.de

#### ITALY

Via Marconi 147G 12030 MARENE (CN) (+39) 0172 74 3170 apem.italia@apem.com

#### SWEDEN

Torshamnsgatan 39 S-16440 KISTA (+46) 8 626 38 00 info@apem.se

#### UNITED KINGDOM

Drakes Drive LONG CRENDON, Bucks HP18 9BA England (+44) 1 844 202400 sales@apem.co.uk

idec-emea.com

To receive our latest news, subscribe to our bimonthly newsletter: https://bit.ly/3x06NgE

Follow us on LinkedinFollow us on Youtube

