

Technical Information

Liquiline Compact CM72

Single-parameter transmitter for Memosens sensors

Space-saving transmitter for monitoring and controlling processes in industry and the environmental sector

Application

The CM72 transmitter can be used in all sectors and by plant manufacturers in these sectors and supports sensors with the blue Memosens plug-in head:

- pH sensors
- ORP sensors
- Contacting conductivity sensors
- Oxygen sensors

Direct connection to PLC via:
4 to 20 mA

Your benefits

- Space-saving installation:
 - The two-wire device fits into an assembly and does not require a separate power supply.
 - Minimum inventory
- Fast commissioning and maintenance:
 - Thanks to its permanent configuration, the CM72 does not need to be commissioned and can start measurement immediately.
 - All of the benefits of Memosens technology: lab-calibrated sensors, hot plug & play
 - The status of the transmitter and the connected sensor is indicated by a red/green LED.
- Suitable for all locations
Regardless of whether your measuring point is exposed to dust, steam, rain, snow, heat or cold, the CM72 is always exactly the transmitter you need!




Function and system design

Measuring system

The overview shows examples of measuring systems. Other sensors and assemblies can be ordered for conditions specific to your application (www.endress.com/products).

A complete measuring system comprises the following components:

- Liquiline compact transmitter
- Sensors with Memosens technology
- Assemblies to suit the sensors used



A0036844

1 Example of a measuring system

- 1 Measuring point with assembly and Memosens sensor
- 2 Liquiline Compact CM72
- 3 Junction box (optional)
- 4 PLC (programmable logic controller)

Sensor connection

Sensors with Memosens protocol

Sensor types	Sensors
Digital sensors with inductive Memosens plug-in head	<ul style="list-style-type: none"> ▪ pH sensors ▪ ORP sensors ▪ Oxygen sensors ▪ Conductivity sensors

Communication and data processing

Communication protocols:

4 to 20 mA

-  For configuration with the measured value and the current output turndown, select the option in the order structure when ordering. This cannot be changed at a later stage.

Dependability

Reliability

Memosens

Memosens makes your measuring point safer and more reliable:

- Non-contact, digital signal transmission enables optimum galvanic isolation
- No contact corrosion
- Completely watertight
- Sensor can be calibrated in a lab, thus increasing the availability of the measuring point in the process
- Predictive maintenance thanks to recording of sensor data, e.g.:
 - Total hours of operation
 - Hours of operation with very high or very low measured values
 - Hours of operation at high temperatures
 - Number of steam sterilizations
 - Sensor condition



 2 *Plug & Play with Memosens technology*

A0035116

The status of the transmitter and the connected sensor is indicated by a red/green LED.



 3 *LED display*

A0036843

Security

Measured value compensation

pH:

Temperature

Oxygen:

- Temperature
- Air pressure

Conductivity:

Temperature

Compensation of temperature dependency is linear.

Input


Measured variable	<p>The transmitter is designed for digital Memosens sensors with an inductive plug-in head:</p> <ul style="list-style-type: none"> ▪ pH ▪ ORP ▪ Conductive conductivity ▪ Dissolved oxygen <p>Depending on the order version, the measuring range is configured to suit the sensor type:</p> <ul style="list-style-type: none"> ▪ pH sensor: 0 to 14 pH ▪ ORP: -1500 mV to +1500 mV ▪ Conductivity: 0 to 20 $\mu\text{S}/\text{cm}$ ▪ Conductivity: 0 to 500 $\mu\text{S}/\text{cm}$ ▪ Conductivity: 0 to 20 mS/cm ▪ Conductivity: 0 to 500 mS/cm ▪ Oxygen: 0 to 200 $\mu\text{g}/\text{l}$ ▪ Oxygen: 0 to 20 mg/l
Measuring range	→ Documentation of the connected sensor
Type of input	Digital sensor inputs for Memosens-sensors

Output

Output signal	4 ... 20 mA, galvanically isolated from the sensor circuits
Linearization	Linear
Transmission behavior	Linear

Power supply

Supply voltage	<p>12.6 to 30 VDC (when failure current setting > 20 mA)</p> <p>14 to 30 VDC (when failure current setting < 4 mA)</p>
-----------------------	------------------------------------------------------------------------------------------------------------------------------



4 Supply voltage and load

A0036752

The lower voltage value in each case applies only to a load resistance of 0 Ohm.

NOTICE

The device does not have a power switch

- ▶ At the supply point, the power supply must be isolated from dangerous live cables by double or reinforced insulation in the case of devices with a 24 V power supply.


Cable specification	Cable length: <ul style="list-style-type: none"> ■ Max. 3 m (10 ft) ■ Max. 7 m (23 ft) ■ Max. 15 m (49 ft)
Overvoltage protection	IEC 61 000-4-4 and IEC 61 000-4-5 with +/- 1 kV

Performance characteristics

Resolution	Current output $< 5 \mu\text{A}$
Repeatability	→ Documentation of the connected sensor
Response time	Current output $t_{90} = \text{max. } 500 \text{ ms}$ for an increase from 0 to 20 mA
Tolerance	Current output Typical measuring tolerances: $< \pm 20 \mu\text{A}$ (if current value = 4 mA) $< \pm 50 \mu\text{A}$ (for current values 4 to 20 mA) at 25 °C (77 °F) each additional tolerance depending on the temperature: $< 1.5 \mu\text{A/K}$

Environment

Ambient temperature range	-20 to 85 °C (-4 to 185 °F) The maximum ambient temperature depends on the process temperature and the transmitter's installation position. <ul style="list-style-type: none"> ▶ Make sure that the ambient temperature at the transmitter does not exceed 85 °C (185 °F). Example for ambient conditions in Endress+Hauser assemblies: <ul style="list-style-type: none"> ■ for open installation (without protective cover, i.e. free convection at the transmitter), e.g. CPA442, CPA842 ■ for enclosed installation (with protective cover), e.g. CPA871, CPA875, CPA842 $T_{\text{ambient}} = \text{max. } 60 \text{ °C (140 °F)}$ $T_{\text{process}} = \text{max. } 100 \text{ °C (212 °F)}$, in continuous operation $T_{\text{process}} = \text{max. } 140 \text{ °C (284 °F)}$, < 2h (for sterilization)
----------------------------------	-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------



A0046638

5 Installation position of transmitter with or without protective cover

1 Ambient temperature $T_{ambient}$

2 Process temperature $T_{process}$

Storage temperature -40 to +85 °C (-40 to 185 °F)

Relative humidity 5 to 95 %

Degree of protection IP 67
IP 68
NEMA Type 6

Electromagnetic compatibility (EMC)

- EN 61326-1
- EN 61326-2-3
- NAMUR NE 21

Electrical safety EN 61010-1


Operating height < 2000 m (< 6562 ft) above MSL

Pollution degree

Complete device:	Pollution level 4
Internal:	Pollution level 2

Mechanical construction

Dimensions



A0033272

6 Dimensions in mm (inch)

Materials

Components	Material
Housing, cover	Peek 151
Strain relief	EPDM (peroxide crosslinked)
Axial ring	Peek 450 G
Optical waveguide	PC transparent

Impact loads

The product is designed for mechanical impact loads of 1 J (IK06) as per the requirements of EN 61010-1.

Weight

without cable	Approx. 42 g (1.5 oz)
3 m (9 f) cable	Approx. 190 g (7 oz)
7 m (23 f) cable	Approx. 380 g (13 oz)
15 m (49 f) cable	Approx. 760 g (27 oz)
For every 1 m (3 f) of cable	Approx. 48 g (2 oz)

Operability

Operating concept

i For configuration with the measured value and the current output turndown, select the option in the order structure when ordering. This cannot be changed at a later stage.

Certificates and approvals

Current certificates and approvals that are available for the product can be selected via the Product Configurator at www.endress.com:

1. Select the product using the filters and search field.
2. Open the product page.

3. Select **Configuration**.

Ordering information

Product page www.endress.com/CM72

Product Configurator

1. **Configure**: Click this button on the product page.
 2. Select **Extended selection**.
 - ↳ The Configurator opens in a separate window.
 3. Configure the device according to your requirements by selecting the desired option for each feature.
 - ↳ In this way, you receive a valid and complete order code for the device.
 4. **Apply**: Add the configured product to the shopping cart.
-  For many products, you also have the option of downloading CAD or 2D drawings of the selected product version.
5. **Show details**: Open this tab for the product in the shopping cart.
 - ↳ The link to the CAD drawing is displayed. If selected, the 3D display format is displayed along with the option to download various formats.

Scope of delivery

The scope of delivery includes:

- CM72
- Brief Operating Instructions

Accessories

Device-specific accessories

Sensors

pH glass electrodes

Memosens CPS11E

- pH sensor for standard applications in process and environmental engineering
- Digital with Memosens 2.0 technology
- Product Configurator on the product page: www.endress.com/cps11e



Technical Information TI01493C

Memosens CPS31E

- pH sensor for standard applications in drinking water and swimming pool water
- Digital with Memosens 2.0 technology
- Product Configurator on the product page: www.endress.com/cps31e



Technical Information TI01574C

Memosens CPS41E

- pH sensor for process technology
- With ceramic junction and KCl liquid electrolyte
- Digital with Memosens 2.0 technology
- Product Configurator on the product page: www.endress.com/cps41e



Technical Information TI01495C

Memosens CPS71E

- pH sensor for chemical process applications
- Digital with Memosens 2.0 technology
- Product Configurator on the product page: www.endress.com/cps71e



Technical Information TI01496C

Memosens CPS171D

- pH electrode for bio-fermenters with digital Memosens technology
- Product Configurator on the product page: www.endress.com/cps171d



Technical Information TI01254C

Memosens CPS91E

- pH sensor for heavily polluted media
- With open aperture
- Digital with Memosens 2.0 technology
- Product Configurator on the product page: www.endress.com/cps91e



Technical Information TI01497C

Memosens CPF81E

- pH sensor for mining operations, industrial water and wastewater treatment
- Digital with Memosens 2.0 technology
- Product Configurator on the product page: www.endress.com/cpf81e



Technical Information TI01594C

Enamel pH electrodes

Ceramax CPS341D

- pH electrode with pH-sensitive enamel
- Meets highest demands of measuring accuracy, pressure, temperature, sterility and durability
- Product Configurator on the product page: www.endress.com/cps341d



Technical Information TI00468C

ORP sensors

Memosens CPS12E

- ORP sensor for standard applications in process and environmental engineering
- Digital with Memosens 2.0 technology
- Product Configurator on the product page: www.endress.com/cps12e



Technical Information TI01494C

Memosens CPS42E

- ORP sensor for process technology
- Digital with Memosens 2.0 technology
- Product Configurator on the product page: www.endress.com/cps42e



Technical Information TI01575C

Ceragel CPS72D

- ORP electrode with reference system including ion trap
- Product Configurator on the product page: www.endress.com/cps72d



Technical Information TI00374C

Memosens CPF82E

- ORP sensor for mining operations, industrial water and wastewater treatment
- Digital with Memosens 2.0 technology
- Product Configurator on the product page: www.endress.com/cpf82e



Technical Information TI01595C

Orbipore CPS92D

- ORP electrode with open aperture for media with high dirt load
- Product Configurator on the product page: www.endress.com/cps92d



Technical Information TI00435C

*pH-ISFET sensors***Tophit CPS441D**

- Sterilizable ISFET sensor for low-conductivity media
- Liquid KCl electrolyte
- Product Configurator on the product page: www.endress.com/cps441d



Technical Information TI00352C

Tophit CPS471D

- Sterilizable and autoclavable ISFET sensor for food and pharmaceuticals, process engineering
- Water treatment and biotechnology
- Product Configurator on the product page: www.endress.com/cps471d



Technical Information TI00283C

Tophit CPS491D

- ISFET sensor with open aperture for media with high dirt load
- Product Configurator on the product page: www.endress.com/cps491d



Technical Information TI00377C

*Conductivity sensors with conductive measurement of conductivity***Memosens CLS15E**

- Digital conductivity sensor for measurements in pure and ultrapure water
- Conductive measurement
- With Memosens 2.0
- Product Configurator on the product page: www.endress.com/cls15e



Technical Information TI01526C

Memosens CLS16E

- Digital conductivity sensor for measurements in pure and ultrapure water
- Conductive measurement
- With Memosens 2.0
- Product Configurator on the product page: www.endress.com/cls16e



Technical Information TI01527C

Memosens CLS21E

- Digital conductivity sensor for media with medium or high conductivity
- Conductive measurement
- With Memosens 2.0
- Product Configurator on the product page: www.endress.com/cls21e



Technical Information TI01528C

Memosens CLS82E

- Hygienic conductivity sensor
- Digital with Memosens 2.0 technology
- Product Configurator on the product page: www.endress.com/cls82e



Technical Information TI01529C

*Oxygen sensors***Memosens COS22E**

- Hygienic amperometric oxygen sensor with maximum measurement stability over multiple sterilization cycles
- Digital with Memosens 2.0 technology
- Product Configurator on the product page: www.endress.com/cos22e



Technical Information TI01619C

Memosens COS51E

- Amperometric oxygen sensor for water, wastewater and utilities
- Digital with Memosens 2.0 technology
- Product Configurator on the product page: www.endress.com/cos51e



Technical Information TI01620C

Memosens COS81E

- Hygienic optical oxygen sensor with maximum measurement stability over multiple sterilization cycles
- Digital with Memosens 2.0 technology
- Product Configurator on the product page: www.endress.com/cos81e



Technical Information TI01558C

Software

Memobase Plus CYZ71D

- PC software to support laboratory calibration
- Visualization and documentation of sensor management
- Sensor calibrations stored in database
- Product Configurator on the product page: www.endress.com/cyz71d



Technical Information TI00502C

DeviceCare SFE100

Configuration tool for HART, PROFIBUS and FOUNDATION Fieldbus field devices

DeviceCare is available for download at www.software-products.endress.com. You need to register in the Endress+Hauser software portal to download the application.



Technical Information TI01134S

Other accessories

Cable junction with Velcro strip

Cable junction with Velcro strip

- 4 pieces, for sensor cable
- Order No. 71092051

System components

RIA15

- Process display unit, Digital display unit for integration into 4-20 mA circuits
- Panel mounting
- With optional HART communication



Technical Information TI01043K



71601178

www.addresses.endress.com
