Disclaimer. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications



PanelSeT SFM plain partial door - 1000x600 mm - 20M

NSYMPD20M6

Main

Range	PanelSeT
Accessory / separate part category	Enclosure accessory
Product or component type	Partial door
Application	Compartmentalised application
For enclosure nominal dimensions	- W: 600 mm
Total number of 50 mm modules	20
Mounting location	Front
Range compatibility	PanelSeT PanelSeT SFM
Device composition	1 partial door 2 hinges 1 5 mm double bar insert
Quantity per set	Set of 1

Complementary

Material	Steel
Colour	Grey (RAL 7035)
Surface finish	Epoxy-polyester powder
Lock type	Lock 5 mm double bar
Number of locks	1
Door type	External plain
Door opening side	Reversible (120 °)
Height	Nominal: 1000 mm
Width	Nominal: 600 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	101.000 cm
Package 1 Width	58.000 cm
Package 1 Length	7.000 cm
Package 1 Weight	10.870 kg
Unit Type of Package 2	P12

Number of Units in Package 2	10
Package 2 Height	86.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	120.650 kg

Contractual warranty

Coverage	Core product
Warranty	18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

∅ Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	77
Environmental Disclosure	Product Environmental Profile

Use Better

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	52da316e-d4e1-4114-85c0-32a03b2934fd
REACh Regulation	REACh Declaration

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No