

# PRODUCT DATASHEET

## DL CMFT ZB D200 P 30W 93040 OP WT

DOWNLIGHT COMFORT ZIGBEE OPAL | Downlight luminaires with aluminum housing, high luminous efficacy and external Zigbee 3.0 driver



PERFOR-  
MANCE  
CLASS

### Areas of application

- Direct replacement for recessed luminaires with fluorescent lamps
- Offices, conference rooms
- Reception areas, foyers, corridors, elevators

### Product benefits

- Suitable luminaire for DIRECT EASY / VIVARES Zigbee and other Zigbee 3.0 Light Management Systems
- Extended services such as energy monitoring and remote maintenance possible with Zigbee versions
- Energy savings thanks to high system efficacy: up to 120 lm/W
- Highly versatile due to Multi Select functions
- High color rendering index CRI > 90
- External driver for extended flexibility and easy installation
- Through wiring possible via additional connector box accessory
- Type of protection: IP44
- Easy installation with fast connection
- Further variants with DALI-2 driver, Zigbee driver or Emergency Conversion Kit available

### Product features

- IoT-ready luminaire with Zigbee 3.0 technology
- Aluminum luminaires with 4 different cut-outs and opal diffuser
- Very homogenous light distribution
- Multi Color function
- Consistent lighting color  $\leq 3$  SDCM
- Lifetime (L80/B10): 70,000 h (at 25 °C)





---

**TECHNICAL DATA****Electrical data**

|                                                             |                     |
|-------------------------------------------------------------|---------------------|
| Nominal wattage                                             | 30.00 W             |
| Nominal voltage                                             | 220...240 V         |
| Mains frequency                                             | 0/50/60 Hz          |
| Nominal current                                             | 144.000 mA          |
| Inrush current                                              | 27.9 A              |
| Inrush current time $T_{h50}$                               | 178 $\mu$ s         |
| Max. number of luminaires per miniature circuit breaker B16 | 14                  |
| Max. number of luminaires per miniature circuit breaker C10 | 12                  |
| Max. number of luminaires per miniature circuit breaker C16 | 20                  |
| Power factor $\lambda$                                      | > 0.90              |
| Total harmonic distortion                                   | < 15 %              |
| Protection class                                            | II                  |
| Operating mode                                              | External LED driver |
| Dimming interface                                           | Zigbee Direct / IoT |

**Photometrical data**

|                                              |                         |
|----------------------------------------------|-------------------------|
| Luminous flux                                | 3600 lm / 3300 lm       |
| Luminous efficacy                            | 120 lm/W / 110 lm/W     |
| Color temperature                            | 3000 K / 4000 K         |
| Light color (designation)                    | Warm White / Cool White |
| Color rendering index Ra                     | > 90                    |
| Standard deviation of color matching         | < 3 sdcn                |
| Low flicker                                  | Yes                     |
| Flickering metric (Pst LM)                   | < 1                     |
| Stroboscope effect metric (SVM)              | < 0.4                   |
| Photobiological safety group acc. to EN62778 | RG1                     |
| Photobiological safety group acc. to EN62471 | RG0                     |
| Beam angle                                   | 100 °                   |




### Adjustable attributes


| Nominal wattage | Color temperature | Luminous flux | Luminous efficacy |
|-----------------|-------------------|---------------|-------------------|
| 30W             | 3000K             | 3300lm        | 110lm/W           |
| 30W             | 4000K             | 3600lm        | 120lm/W           |

### Dimensions & Weight

|                |           |
|----------------|-----------|
| Diameter       | 215.00 mm |
| Height         | 59.00 mm  |
| Product weight | 580.00 g  |



DL CMFT ZB D200 P 30W 93040 OP



DL CMFT ZB D250 P 42W 93040 OP

Materials & Colors

|                                            |                    |
|--------------------------------------------|--------------------|
| Product color                              | White              |
| Housing color                              | White              |
| RAL Color (most similar)                   | RAL 9003           |
| Body material                              | Aluminum           |
| Cover material                             | Polycarbonate (PC) |
| Glow Wire Test according to IEC 60695-2-12 | 650 °C             |
| Mercury content                            | 0.0 mg             |

Application & Mounting

|                                        |                                                                                                                                                      |
|----------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------|
| Ambient temperature range              | -20...+40 °C                                                                                                                                         |
| Temperature range at storage           | -20...+80 °C                                                                                                                                         |
| Type of connection                     | Screwless terminal, 3-POLE (L, N, PE)                                                                                                                |
| Type of protection                     | IP44/IP20                                                                                                                                            |
| Protection class IK (shock resistance) | IK03                                                                                                                                                 |
| Dimmable                               | Yes                                                                                                                                                  |
| Type of dimming                        | ZIGBEE                                                                                                                                               |
| IoT ready                              | Support of Zigbee Data Clusters: 0x0302 (Luminaire Asset Management), 0x0702 (Smart Energy: Metering), 0x0B04 (Electrical Measurement) <sup>1)</sup> |
| Mounting type                          | Recessed                                                                                                                                             |
| Mounting location                      | Ceiling                                                                                                                                              |
| Application environment                | Indoor                                                                                                                                               |
| Mounting diameter                      | 200 mm                                                                                                                                               |
| Mounting depth                         | 59 mm                                                                                                                                                |
| With light source                      | Yes                                                                                                                                                  |

|                          |    |
|--------------------------|----|
| Replaceable light source | No |
|--------------------------|----|

1) Internet of Things. Supports data transfer via gateway to cloud-based monitoring platforms, such as LEDVANCE VIVARES Cloud

### Lifespan

|                            |                        |
|----------------------------|------------------------|
| Lifespan L70/B50 at 25 °C  | 100000 h <sup>1)</sup> |
| Lifespan L80/B10 at 25 °C  | 70000 h <sup>1)</sup>  |
| Lifespan L80/B50 at 25 °C  | 70000 h                |
| Lifespan L90/B10 at 25 °C  | 40000 h                |
| Number of switching cycles | 100000                 |

1) t[h]: L70 / B50 @ 25 °C (Ta), t[h]: L80 / B10 @ 25 °C (Ta), t[h]: L90 / B10 @ 25 °C (Ta)

### Control gear

|                             |        |
|-----------------------------|--------|
| Output current              | 750 mA |
| ECG - Output ripple current | < 10 % |
| ECG - Length                | 178 mm |
| ECG - Width                 | 45 mm  |
| ECG - Height                | 25 mm  |

### Emergency lighting

|                                           |                                                                                 |
|-------------------------------------------|---------------------------------------------------------------------------------|
| Type of Emergency Lighting (EL)           | EL certified driver (0Hz / DC operation) for central battery operation included |
| Type of emergency operation test          | None                                                                            |
| Wattage in emergency operation mode       | 3 W                                                                             |
| Luminous flux in emergency operation mode | 372 lm                                                                          |

### Certificates & Standards

|                                                      |                 |
|------------------------------------------------------|-----------------|
| Standards                                            | CE / UKCA / TÜV |
| Luminaire with limited surface temperature, "D sign" | No              |
| Ball shot safe                                       | No              |
| Replaceable light source (EPREL)                     | Not replaceable |

### Additional product data

|                |                        |
|----------------|------------------------|
| Added function | MULTI SELECT / VIVARES |
|----------------|------------------------|

### Accessories Optional

| Product image                                                                      | Product name          | EAN           |
|------------------------------------------------------------------------------------|-----------------------|---------------|
|  | DL CMFT FRAME D200 WT | 4099854500022 |

| Product image                                                                    | Product name              | EAN           |
|----------------------------------------------------------------------------------|---------------------------|---------------|
|  | DL CMFT FRAME D200 GY     | 4099854500060 |
|  | DL CMFT FRAME D200 BK     | 4099854500046 |
|  | DL CMFT EXCH RING D200 GY | 4099854515460 |
|  | DL CMFT EXCH RING D200 BK | 4099854515347 |

### Components for light control

| Components Light Control                                                            |                                                     |               |
|-------------------------------------------------------------------------------------|-----------------------------------------------------|---------------|
| Product image                                                                       | Product name                                        | EAN           |
|  | MANUAL CONTROL UNIT SELECT DIRECT 100-240 TW RGB ZB | 4099854476334 |
|   | SENSOR DIRECT LS-PD-7 IR CI ZB                      | 4099854476358 |
|  | SWITCH KINETIC DIRECT 4B WT M ZB                    | 4099854589799 |
|  | SWITCH KINETIC DIRECT 4B WT G ZB                    | 4099854589812 |
|  | SWITCH KINETIC DIRECT 4B BK ZB                      | 4099854589836 |
|  | SWITCH KINETIC DIRECT 4B GR ZB                      | 4099854589850 |

| Product image                                                                    | Product name                | EAN           |
|----------------------------------------------------------------------------------|-----------------------------|---------------|
|  | VIVARES ZB CONTROL          | 4058075427488 |
|  | VIVARES ZB L/O SENS 220-240 | 4058075446182 |
|  | VIVARES ZB O SENS 220-240   | 4058075544222 |
|  | VIVARES ZB COUPLER          | 4058075463806 |
|  | VIVARES ZB SENS ADAPTER     | 4058075650107 |

## EQUIPMENT / ACCESSORIES

- Surface mounting frame available as separate accessory
- Security rope for luminaire included
- External control gear included
- Suitable for use with separate Emergency Conversion Box
- Gray and black exchangeable rings available as separate accessory
- Extension rings are available as separate accessory

## Safety advice

- All electrical connections must be made by a qualified person.
- Caution, risk of electric shock.
- The luminaires are not suitable for covering with thermally insulated material.

## DOWNLOAD DATA

| Documents and certificates                                                                                                | Document name                         |
|---------------------------------------------------------------------------------------------------------------------------|---------------------------------------|
|  User instruction / safety instructions | User Instruction G11249410 DL CMFT ZB |
|  Legal information                      | App Download guide                    |
|  Legal information                      | Safety Insert G11207793               |

| Documents and certificates                                                         |                                     | Document name                                           |
|------------------------------------------------------------------------------------|-------------------------------------|---------------------------------------------------------|
|    | Legal information                   | DL SLIM ALU CMFT                                        |
|    | Legal information                   | Informationstext 18 Abs 4 ElektroG                      |
|    | Declarations of conformity          | DL CMFT ZB                                              |
|    | Declarations of conformity UKCA     | DL CMFT ZB                                              |
|    | EU Data Act                         | SMART ZigBee Lamps and Luminaires                       |
| Photometric and lighting design files                                              |                                     | Document name                                           |
|    | IES file (IES)                      | DL CMFT ZB D200 P 30W 930 OP WT                         |
|    | IES file (IES)                      | DL CMFT ZB D200 P 30W 940 OP WT                         |
|   | LDT file (Eulumdat)                 | DL CMFT ZB D200 P 30W 930 OP WT                         |
|  | LDT file (Eulumdat)                 | DL CMFT ZB D200 P 30W 940 OP WT                         |
|  | UGR file (UGR table)                | DL CMFT ZB D200 P 30W 930 OP WT                         |
|  | UGR file (UGR table)                | DL CMFT ZB D200 P 30W 940 OP WT                         |
|  | Light distribution curve type cone  | DL CMFT ZB D200 P 30W 930 OP WT                         |
|  | Light distribution curve type cone  | DL CMFT ZB D200 P 30W 940 OP WT                         |
|  | Light distribution curve type polar | DL CMFT ZB D200 P 30W 930 OP WT                         |
|  | Light distribution curve type polar | DL CMFT ZB D200 P 30W 940 OP WT                         |
| CAD/BIM files                                                                      |                                     | Document name                                           |
|  | CAD STEP 3D                         | DL CMFT D200 MS OP                                      |
| Tender texts                                                                       |                                     | Document name                                           |
|  | Tender documents                    | DOWNLIGHT COMFORT ZIGBEE OPAL D200 P 30W 93040 OP WT-en |

## LOGISTICAL DATA

| Product code | Packaging unit (Pieces/Unit) | Dimensions (length x width x height) | Gross weight | Volume |
|--------------|------------------------------|--------------------------------------|--------------|--------|
|--------------|------------------------------|--------------------------------------|--------------|--------|

| Product code  | Packaging unit (Pieces/Unit) | Dimensions (length x width x height) | Gross weight | Volume                |
|---------------|------------------------------|--------------------------------------|--------------|-----------------------|
| 4099854620232 | Folding box<br>1             | 235 mm x 235 mm x 100 mm             | 747.00 g     | 5.52 dm <sup>3</sup>  |
| 4099854620249 | Shipping box<br>8            | 490 mm x 485 mm x 225 mm             | 7048.00 g    | 53.47 dm <sup>3</sup> |

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

---

### References / Links

– For Guarantee see [www.ledvance.com/guarantee](http://www.ledvance.com/guarantee)

---

### DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.