

Parker Product Datasheet



The main function of Ermeto DIN tube to tube high pressure hydraulic tube fittings is to connect different numbers of tubes. This broad range of fittings is available in steel and in stainless steel.

PART NUMBER: K15L71X
SHAPE: Cross
PRODUCT STYLE: Union
CONNECTION 1 SIZE: 15 mm (O.D.)
BODY MATERIAL: Stainless Steel
CONNECTION 1 TYPE: Male 24° Cone
ACCESSORIES INCLUDED: n/a
CONNECTION 2 TYPE: Male 24° Cone
CONNECTION 2 SIZE: 15 mm (O.D.)
CONNECTION 4 SIZE: 15 mm (O.D.)
CONNECTION 3 SIZE: 15 mm (O.D.)
CONNECTION 3 TYPE: Male 24° Cone
CONNECTION 4 TYPE: Male 24° Cone

PRODUCT OVERVIEW

The main function of Ermeto DIN tube to tube high pressure hydraulic tube fittings is to connect different numbers of tubes. This broad range of Ermeto DIN tube to tube high pressure hydraulic tube fittings, types G, GR, W, T, TR, K, SV, up to WSV is available in steel and in a stainless steel version. Depending on the specific application, the fittings can be delivered with cutting ring (EO-PSR or DPR) or elastomeric seal (EO-2).

Markets:

- Automotive
- Defence
- Energy
- Environment
- Industrial
- Infrastructure
- Machine Tools
- Material Handling
- Mobile
- Oil and Gas
- Power Generation
- Process
- Transportation
- Water

Applications:

Suitable for general hydraulic applications.

Features/ benefits:

- Steel and Stainless steel fittings have a high corrosion resistance to aggressive media and environmental influences. These features extend the range of applications.
- High pressure: Ermeto DIN tube to tube high pressure hydraulic tube fittings can be used in applications of up to 800 bar (S series) and 500 bar (L series), so that the fittings can be used in a wide range of applications.

TECH SPECIFICATIONS

DIVISION	High Pressure Connectors Europe Division
DIVISION	High Pressure Connectors Europe Division
MAXIMUM OPERATING PRESSURE	315 bar
FOR FLUID TYPE	Gases
FOR FLUID TYPE	Chemicals
FOR FLUID TYPE	Hydraulic Fluids
FOR FLUID TYPE	Fuels
FOR FLUID TYPE	Steam

INDUSTRY	Industrial Manufacturing Equipment
INDUSTRY	Construction
INDUSTRY	Agriculture
INDUSTRY	Automotive
INDUSTRY	Marine
INDUSTRY	Material Handling
INDUSTRY	Transportation
SPECIFICATIONS MET	ISO 8434
SPECIFICATIONS MET	DIN
SHAPE	Union
SHAPE	Cross
APPLICATION	Packaging
APPLICATION	Fuel Transfer
APPLICATION	Chemical Transfer
APPLICATION	Oilfield
APPLICATION	Hydraulics
APPLICATION	Mobile Equipment
BRAND	Ermeto
TECHNOLOGY	Fluid & Gas Handling
CONNECTION 1 SIZE	15 mm Tube O.D.
BODY MATERIAL	Stainless Steel
CONNECTION 1 TYPE	24° Cone
CONNECTION 1 TYPE	Male
PRODUCT SERIES	EO Light
PRODUCT TYPE	Hydraulic DIN Fittings
SEAL MATERIAL	n/a
CONFIGURATION	Tube to Tube

ACCESSORIES INCLUDED	n/a
CONNECTION 2 TYPE	24° Cone
CONNECTION 2 TYPE	Male
CONNECTION 2 SIZE	15 mm Tube O.D.
MAXIMUM AMBIENT TEMPERATURE	752 °F
MAXIMUM AMBIENT TEMPERATURE	400 °C
MINIMUM AMBIENT TEMPERATURE	-60 °C
MINIMUM AMBIENT TEMPERATURE	-76 °F
MAXIMUM FLUID TEMPERATURE	400 °C
MAXIMUM FLUID TEMPERATURE	752 °F
MINIMUM FLUID TEMPERATURE	-60 °C
MINIMUM FLUID TEMPERATURE	-76 °F
CONNECTION 4 SIZE	15 mm Tube O.D.
CONNECTION 3 SIZE	15 mm Tube O.D.
SEAL TYPE	Sealing Edge
CONNECTION 3 TYPE	24° Cone
CONNECTION 3 TYPE	Male
CONNECTION 4 TYPE	24° Cone
CONNECTION 4 TYPE	Male