


KEMET Part Number: MDC15104K630B53P3TUBE
(F153BA104K630T)

MDC, Film, Metallized Polyester, Dual-In-Line, 0.1 uF, 10%, 220 VAC, 630 VDC, 85°C, 15mm



Dimensions

L	11mm +/-0.2mm
L2	2.96mm +/-0.2mm
W	16.5mm +/-0.2mm
T	6.05mm +/-0.2mm
S	15mm +/-0.2mm
LL	1.7mm +/-0.2mm
F	0.5mm +/-0.05mm
X	0.35mm +/-0.05mm
Y	1.5mm +/-0.2mm

Packaging Specifications

Packaging:	Bulk, Tube
Packaging Quantity:	43

General Information

Supplier:	KEMET
Series:	MDC
Dielectric:	Metallized Polyester
Style:	Dual-In-Line
RoHS:	Yes
Lead:	L Leads

Specifications

Capacitance:	0.1 uF
Capacitance Tolerance:	10%
Voltage AC:	220 VAC
Voltage DC:	630 VDC
Temperature Range:	-55/+125°C
Rated Temperature:	85°C
Dissipation Factor:	0.80% 1kHz, 1.50% 10kHz, 2.50% 100kHz
Insulation Resistance:	30 GOhms
Inductance:	4 nH