



**FAG****61822-2RSR-Y**

Deep groove ball bearing

Deep groove ball bearing 618...-2RSR-Y,
single row, seals, brass sheet metal cage

Technical information



Your current product variant

Sealing	2RSR	Contact seal on both sides
Cage	Y	Brass sheet metal
Tolerance class	PN	Normal (PN)
Dimensional / heat stabilization	S0	Rings dimensional stabilized up to 150°
Lubricant	GA13	Ball bearing and insert bearing grease, standard for D>62mm
Radial internal clearance	CN (Group N)	Normal internal clearance
Bore type	Z	Cylindrical

Main Dimensions & Performance Data

d	110 mm	Bore diameter
D	140 mm	Outside diameter
B	16 mm	Width
C _r	30,000 N	Basic dynamic load rating, radial
C _{0r}	30,500 N	Basic static load rating, radial
C _{ur}	1,650 N	Fatigue load limit, radial
n _G	2,230 1/min	Limiting speed
≈m	0.54 kg	Weight

Mounting dimensions

d _{a min}	114.6 mm	Minimum diameter shaft shoulder
D _{a max}	135.4 mm	Maximum diameter of housing shoulder
r _{a max}	1 mm	Maximum fillet radius



Dimensions

r_{min}	1 mm	Minimum chamfer dimension
D_1	130.61 mm	Shoulder diameter outer ring
D_2	133.3 mm	Caliber diameter outer ring
d_1	119.7 mm	Shoulder diameter inner ring

Temperature range

T_{min}	-20 °C	Operating temperature min.
T_{max}	100 °C	Operating temperature max.

Calculation factors

f_0	16	Calculation factor
-------	----	--------------------

Characteristics

-  Radial load
-  Axial load in one direction
-  Axial load in two directions
-  Lifetime lubrication, freedom from maintenance
-  Grease Lubrication
-  Sealed on both sides