

Drywall Screwdriver LXT®

DFS452

18V • 0 – 4 000 min⁻¹

Reliable brushless screwdriver for drywall screws

A screwdriver for drywall screws with a precise depth control switch for quick and accurate operation at a speed of 4 000 min⁻¹. An ergonomic design ensures good grip. Variable speed control from the switch. The screwdriver has an LED light.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
No load speed	0 - 4000 min ⁻¹
Sound Pressure Level (L _{pA})	72 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	1,5 - 1,8 kg
Product Dimensions (L x W x H):	251 x 79 x 259 mm
Brushless Motor	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Driving Shank	1/4 "
Vibration Level, Screwdriving Without Impact	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Screwdriving Without Impact	1,5 m/s ²

User benefits

- Brushless maintenance-free and long-life motor
- Ergonomic soft grip handle provides increased comfort
- Depth adjustment
- Reversing switch
- LED light illuminates the work site
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makitauk.com



Related products

Optional AC

191L24-0

Autofeed Attachment, 25-55 mm



199155-7

Screw Bit, PH2, 130 mm



821550-0

Makpac case (2)



837805-3

MakPac (2) Inlay



Other

User manual

Parts drawing