

STELLA-DWC2

Universal road lighting (IESNA Type II Medium) beam with excellent mixed illuminance and luminance uniformity. Compatible with up to 23 mm LES size COBs.

TECHNICAL SPECIFICATIONS:

Dimensions Ø 90.0 mm

Height 19.3 mm

Fastening screw

Colour black

Box size 480 x 280 x 300 mm

Box weight 7.1 kg Quantity in Box 135 pcs ves 🕕


ROHS compliant



MATERIAL SPECIFICATIONS:


Material Colour Component **Type** STELLA-DWC2 Single lens Silicone clear STELLA-FRAME Holder PA66 black





2/14

PHOTOMETRIC DATA (MEASURED):



PHOTOMETRIC DATA (MEASURED):

bridgelux. LED FWHM Efficiency Peak intensity LEDs/each optic Light colour Required compon	White	90° 90° 90° 90° 90° 90° 90° 90° 90° 90°
bridgelux LED FWHM Efficiency Peak intensity LEDs/each optic Light colour Required compon	White	35° 0° 12° 30° 30° 30° 30° 30° 30° 30° 30° 30° 30
bridgelux LED FWHM Efficiency Peak intensity LEDs/each optic Light colour Required compon	White	200 200 200 200 200 200 200 200 200 200
bridgelux. LED FWHM Efficiency Peak intensity LEDs/each optic Light colour Required compon	White	90° 200 90° 20° 20° 20° 20° 20° 20° 20° 20° 20° 2
		500


PHOTOMETRIC DATA (MEASURED):

CREE 💠

LED CMA2550 FWHM Asymmetric

Efficiency 89 %
Peak intensity 0.400 cd/lm

LEDs/each optic 1
Light colour White
Required components:




CREE 🕏

LED CMA3090 FWHM Asymmetric Efficiency 89 %

Peak intensity 0.400 cd/lm

LEDs/each optic 1
Light colour White
Required components:




CREE 🕏

LED CXA/B 1816 & CXA/B 1820 & CXA 1850

FWHM Asymmetric
Efficiency 88 %
Peak intensity 0.600 cd/lm

LEDs/each optic 1
Light colour White
Required components:




CREE \$

LED CXA/B 25xx
FWHM Asymmetric
Efficiency 90 %

Peak intensity 0.400 cd/lm

LEDs/each optic 1 Light colour White Required components: Bender Wirth: 439 Typ L3



PHOTOMETRIC DATA (MEASURED):

CREE 💠

LED CXA/B 25xx

FWHM Asymmetric

Efficiency 88 %

Peak intensity 0.400 cd/lm LEDs/each optic 1

Light colour White Required components:

WNICHIA

LED COB J-Type


FWHM Asymmetric

89 % Efficiency

Peak intensity 0.600 cd/lm

LEDs/each optic 1 White Light colour

Required components:



OSRAM Opto Semiconductors

LED Soleriq S19


FWHM Asymmetric

Efficiency 90 %

Peak intensity 0.510 cd/lm

LEDs/each optic 1

Light colour White Required components:



LED Fortimo SLM L19 CoB

FWHM Asymmetric Efficiency 94 %

Peak intensity 0.400 cd/lm


LEDs/each optic 1

White Light colour

Required components:

Bender Wirth: 431 Typ Z1





PHOTOMETRIC DATA (MEASURED):


PHILIPS

LED Fortimo SLM L23 CoB

FWHM Asymmetric Efficiency 94 % Peak intensity 0.300 cd/lm

LEDs/each optic 1 Light colour White Required components: Bender Wirth: 431 Typ Z1






SAMSUNG

LED COB D Series LES 14.5 mm

FWHM Asymmetric Efficiency 88 % Peak intensity 0.520 cd/lm

LEDs/each optic 1 Light colour White Required components:






SAMSUNG

LED COB D Series LES 22 mm

FWHM Asymmetric
Efficiency 88 %
Peak intensity 0.400 cd/lm

LEDs/each optic 1
Light colour White
Required components:




SAMSUNG

LED COB D Series LES 22 mm

FWHM Asymmetric Efficiency 88 % Peak intensity 0.340 cd/lm

LEDs/each optic 1
Light colour White
Required components:



7/14

PHOTOMETRIC DATA (MEASURED):




LED

MJT COB LES 14.5

FWHM Asymmetric
Efficiency 88 %
Peak intensity 0.500 cd/lm

LEDs/each optic 1
Light colour White
Required components:




SEOUL SEMICONDUCTOR

LED MJT COB LES 14.5

FWHM Asymmetric Efficiency 90 % Peak intensity 0.500 cd/lm

LEDs/each optic 1
Light colour White
Required components:
Bender Wirth: 433 Typ Z1




SEOUL SEMICONDUCTOR

LED MJT COB LES 22

FWHM Asymmetric Efficiency 90 % Peak intensity 0.370 cd/lm

LEDs/each optic 1
Light colour White
Required components:
Bender Wirth: 431 Typ Z1



PHOTOMETRIC DATA (SIMULATED):


LED V10 Gen7 FWHM Asymmetric Efficiency 89 % Peak intensity 0.530 cd/lm LEDs/each optic 1 Light colour White Required components: Bender Wirth: 486 Typ L1	99° 390° 3
LED V13 Gen7 FWHM Asymmetric Efficiency 91 % Peak intensity 0.000 cd/lm LEDs/each optic 1 Light colour White Required components:	30° 90° 90° 90° 30° 30° 30° 30° 30° 30° 30° 30° 30° 3
LED V13 Gen7 FWHM Asymmetric Efficiency 93 % Peak intensity 40.494 cd/lm LEDs/each optic 1 Light colour White Required components: Bender Wirth: 477 Typ Z1	30° 50° 50° 50° 50° 50° 50° 50° 50° 50° 5
LED V22 Gen7 FWHM Asymmetric Efficiency 94 % Peak intensity 0.397 cd/lm LEDs/each optic 1 Light colour White Required components: Bender Wirth: 431 Typ Z1	30° 30° 30° 30° 30° 30° 30° 30° 30° 30°

PHOTOMETRIC DATA (SIMULATED):

bridgelux

LED V22 Gen7 **FWHM** Asymmetric Efficiency 94 % Peak intensity 0.397 cd/lm


LEDs/each optic 1 Light colour White Required components: Bender Wirth: 431 Typ Z1



bridgelux.

LED VERO10 **FWHM** Asymmetric 89 % Efficiency Peak intensity 0.560 cd/lm

LEDs/each optic 1 White Light colour Required components:




CITIZEN

LED CLL02x/CLU02x (LES10)

FWHM Asymmetric Efficiency 92 % Peak intensity 0.600 cd/lm


LEDs/each optic 1 Light colour White Required components:



CITIZEN

CLL03x/CLU03x **FWHM** Asymmetric Efficiency 91 % Peak intensity 0.520 cd/lm

LEDs/each optic 1 White Light colour Required components:




PHOTOMETRIC DATA (SIMULATED):

CITIZEN

LED CLL04x/CLU04x **FWHM** Asymmetric Efficiency 91 % Peak intensity 0.370 cd/lm


LEDs/each optic 1 Light colour White Required components: Bender Wirth: 431 Typ Z1



CREE &

LED CXA/B 1830 **FWHM** Asymmetric 91 % Efficiency Peak intensity 0.540 cd/lm


LEDs/each optic 1 White Light colour Required components:



CREE ÷

LED CXA/B 25xx **FWHM** Asymmetric Efficiency 90 % Peak intensity 0.440 cd/lm

LEDs/each optic 1 Light colour White Required components:




MUMILEDS

LED LUXEON CoB 1208

FWHM Asymmetric Efficiency 88 % Peak intensity 0.460 cd/lm

LEDs/each optic 1 White Light colour Required components: Bender Wirth: 431 Typ Z1




PHOTOMETRIC DATA (SIMULATED):



LED LUXEON CoB 1211 **FWHM** Asymmetric

Efficiency 89 % Peak intensity 0.400 cd/lm

LEDs/each optic 1 Light colour White Required components: Bender Wirth: 431 Typ Z1




M LUMILEDS

LED LUXEON CoB 1216/1812

FWHM Asymmetric 88 % Efficiency Peak intensity 0.330 cd/lm


LEDs/each optic 1 White Light colour Required components: Bender Wirth: 431 Typ Z1



ELUMINUS

LED CxM-22 (28x28) **FWHM** Asymmetric Efficiency 91 % Peak intensity 0.360 cd/lm


LEDs/each optic 1 Light colour White Required components: Bender Wirth: 431 Typ Z1



OSRAM Opto Semiconductors

LED Soleriq S13 **FWHM** Asymmetric Efficiency 91 % 0.550 cd/lm Peak intensity

LEDs/each optic 1 White Light colour Required components: Bender Wirth: 477 Typ Z1






PHOTOMETRIC DATA (SIMULATED):

PHILIPS

LED Fortimo SLM L23 + SLM holder (PI)

FWHM Asymmetric Efficiency 91 % Peak intensity 0.330 cd/lm

LEDs/each optic 1
Light colour White
Required components:





GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

Due to use of high power COB's with this product, special attention to proper thermal design is highly recommended. LEDiL has no liability for direct, indirect or consecutive damages arising from the LEDiL products being used outside of the recommended temperature range.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDIL Oy

Joensuunkatu 13 FI-24240 SALO Finland

LEDiL Inc.

228 West Page Street Suite D Sycamore IL 60178 USA

Local sales and technical support

www.ledil.com/ where_to_buy

Shipping locations

Salo, Finland Hong Kong, China

Distribution Partners

www.ledil.com/ where_to_buy