

Technical data



2207

Double-row self-aligning ball bearings



Self-aligning ball bearing, pressed steel cage, open

VISUAL (S)



PRODUCT DEFINITION

Brand	SNR
d - Internal diameter	35 mm
D - External diameter	72 mm
B - Bearing/Inner ring width	23 mm
d1 - External diameter inner ring	46,2 mm
D1 - Inner diameter outer ring	59,8 mm
rs - Min fillet radius	1,1 mm
Radial clearance class	CN
Precision class	P0
Mass	0,401 kg

PRODUCT PERFORMANCE

C - Dynamic load	21200000 mN
C0 - Static load	6600000 mN
Cu - Fatigue limit load	300000 mN
e - Coefficient	0.37
Y0 - Static axial load coefficient	1.77
Y1 - Lower axial load coefficient	1.69
Y2 - Upper axial load coefficient	2.62
N ref - Reference thermal speed	60000 °/s
N lim - Mechanical Limit Speed	72000 °/s
Tmin - Min operating temperature	233,15 °K
Tmax - Max operating temperature	393,15 °K



BEARING FREQUENCIES

BPFO - Over rolling frequency on outer ring (60 rpm)	5.777 Hz
BPFI - Over rolling frequency on inner (60 rpm)	8.223 Hz
BSF - Over rolling frequency on rolling element (60 rpm)	5.386 Hz
BRF - Rotational frequency - rolling element (60 rpm)	2.693 Hz
FTF - Rotational frequency - cage (60 rpm)	0.413 Hz

ABUTMENT

da min - Min shoulder diameter IR	41,5 mm
Da max - Max shoulder diameter OR	65,5 mm
ra max - Max shaft & housing fillet radius	1 mm

