


MIRO TR 24VDC SK 5P OPTO-COUPLER MODULE


IN: 48 VDC - OUT: 35 VDC / 2 A

Transistor 2 A
 24 V DC
 short-circuit protected
 Switching frequency: max. 1 kHz
 Screw terminals

[Link to Product](#)

Illustration





Product may differ from Image

Approvals



Input

Voltage range ON	10...48 V DC
Voltage range OFF	0...5 V DC
Control current	6 mA
LED display	LED (yellow)

General data

Test isolation voltage	3.75 kV
Mounting method	DIN-rail mountable (EN 60715)
Housing	Black plastic, flame retardant
Temperature range	-20...+60 °C
Dimensions H × W × D	90×6.2×65 mm

Output

Switching voltage	10...35 V DC
Switching current per output	1 mA...2 A (short-circuit protected)
Saturation voltage (across output)	max. 1.2 V DC
Leakage current (output is open)	max. 0.1 mA
Switching time ON/OFF	90/120 μs
Switching frequency	max. 1 kHz

Commercial data

country of origin	CZ
customs tariff number	85414090
minimum order quantity	1