



HLT3I-X0




- Broadest selection of sizes, styles, and colors to meet your application needs
- Adjustable, releasable, and reusable hundreds of times – ideal for applications requiring frequent moves, adds, or changes
- Hook and loop material maintains network data integrity by protecting against over-tensioning of high performance copper and fiber cables
- Easy to use and operator safe with no sharp edges

Note: Minimum 2" overlap required to achieve loop tensile rating

▪ Part Number	HLT3I-X0
▪ RoHS Compliancy Status	Compliant
▪ Part Description	Hook & Loop Cable Tie, Loop Tie, 12.0", Intermediate cross section
▪ Product Type	Cable Ties
▪ Material	Nylon Loop, Polyethylene Hook
▪ Color	Black
▪ CSA Certified	No
▪ UL Listed (File #E56854)	No
▪ UL Recognized (File #E56854)	No
▪ Length (In.)	12.0
▪ Length (mm)	305
▪ Width (In.)	.500
▪ Width (mm)	12.7
▪ CE Compliant	Yes
▪ Cross Section	Intermediate
▪ Head Width (In.)	1.00
▪ Head Width (mm)	25.4
▪ Locking Style	Hook & Loop
▪ Max. Bundle Diameter (In.)	3.18
▪ Max. Bundle Diameter (mm)	81
▪ Min. Bundle Diameter (In.)	.25
▪ Min. Bundle Diameter (mm)	6
▪ Min. Loop Tensile Strength (Lbs.)	40
▪ Min. Loop Tensile Strength (N)	178
▪ Pricing Description	Hook & Loop Tie, Loop Style, 12.0"L (305mm), .50"W (12.7mm), Black
▪ Temperature Range	0°F to 220°F

▪ Thickness (In.)	.10
▪ Thickness (mm)	2.5
▪ Min. Order UOM	PC
▪ Min. Order Qty.	10
▪ BOM Qty. (# of Pkgs.)	

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	MIN. LOOP * TENSILE lbs. (N)	CROSS SECTION	APPROXIMATE WEIGHT lbs/100 PIECES (g)
	MIN. in (mm)	MAX. in (mm)								
HLT21	.25 (6.4)	1.91 (48.5)	.100 (2.5)	.50 (12.7)	1.50 (38.1)	1.00 (25.4)	8.0 (203)	40 (178)	INTERMEDIATE	.48 (218)
HLT31	.25 (6.4)	3.18 (80.6)	.100 (2.5)	.50 (12.7)	1.50 (38.1)	1.00 (25.4)	12.0 (305)	40 (178)	INTERMEDIATE	.65 (295)

NOTES:

- 1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.
- * 2) MINIMUM 2" OVERLAP REQUIRED TO ACHIEVE LOOP TENSILE RATING.

								CAD FILENAME/LAYERS		DIMENSIONS IN PARENTHESIS ARE IN METRIC UNITS		
										SS_26938_06.PRT		
								PANDUIT		CORP. TINLEY PARK, ILLINOIS		
										TAK-TY™ HOOK & LOOP CABLE TIES HLT SERIES		
								UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± .030 (.XX) ± .125 ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.		
6	1/13/06	ERW		ADDED APPROX. WEIGHT PER 100 PIECES	26938	6		DRAWN BY KET	MAT'L: POLYETHYLENE HOOK/ NYLON KNIT LOOP	SCALE NONE		
5	5/3/05	ERW	JVL	REMOVED OVAL SLOT DIMENSION TO BE CONSISTENT WITH OTHER CUSTOMER DRAWINGS	26938	5	JVL	DATE 11/28/94		DRAWING NO. SS-26938	DWG A SIZE	
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP		CHK'D HVP		