

Product data sheet

Specifications



module XPSAXE - stop and switch monitoring - 24 V DC/AC

XPSAXE5120P

- !

To be discontinued on: 31 July 2023
- !

To be end-of-service on: 31 December 2025

! To be discontinued

Main

Range of product	Preventa Safety automation
Product or component type	Preventa safety module
Safety module name	XPSAXE
Safety module application	For emergency stop and switch monitoring
Safety level	Can reach PL e/category 4 conforming to EN/ISO 13849-1 Can reach SILCL 3 conforming to EN/IEC 62061
Safety reliability data	DC > 99 % conforming to EN/ISO 13849-1 MTTFd = 457 years conforming to EN/ISO 13849-1 PFHd = 3E-8 1/h conforming to EN/IEC 62061
Connections - terminals	Captive screw clamp terminals, removable terminal block, 2 x 0.5...2 x 1.5 mm² flexible with cable end, with double bezel Captive screw clamp terminals, removable terminal block, 1 x 0.2...1 x 2.5 mm² solid without cable end Captive screw clamp terminals, removable terminal block, 1 x 0.2...1 x 2.5 mm² flexible without cable end Captive screw clamp terminals, removable terminal block, 1 x 0.25...1 x 2.5 mm² flexible with cable end, without bezel Captive screw clamp terminals, removable terminal block, 1 x 0.25...1 x 1.5 mm² flexible with cable end, with bezel Captive screw clamp terminals, removable terminal block, 2 x 0.2...2 x 1 mm² solid without cable end Captive screw clamp terminals, removable terminal block, 2 x 0.2...2 x 1 mm² flexible without cable end Captive screw clamp terminals, removable terminal block, 2 x 0.25...2 x 1 mm² flexible with cable end, without bezel
Output type	Relay instantaneous opening, 3 NO circuit(s), volt-free
Number of additional circuits	1 NC
[Us] rated supply voltage	24 V DC - 15...10 % 24 V AC

Complementary

Synchronisation time between inputs	< 0.5 s
Supply frequency	50/60 Hz
Maximum power consumption in VA	4 VA DC
[Uc] control circuit voltage	24 V DC
Breaking capacity	3600 VA inrush AC-15 B300 relay output 360 VA holding AC-15 B300 relay output
Breaking capacity	1.5 A at 24 V (DC-13) time constant: 50 ms for relay output
Output thermal current	6 A for instantaneous and time delay outputs

Associated fuse rating	6 A gG for instantaneous outputs
Minimum output current	10 mA for relay output
Minimum output voltage	17 V for relay output
Maximum response time on input open	80 ms
[Ui] rated insulation voltage	300 V (pollution degree 2) conforming to IEC 60947-5-1 300 V (pollution degree 2) conforming to DIN VDE 0110 part 1
[Uimp] rated impulse withstand voltage	4 kV overvoltage category III conforming to IEC 60947-5-1 4 kV overvoltage category III conforming to DIN VDE 0110 part 1
Local signalling	2 LEDs
Mounting support	35 mm symmetrical DIN rail
Net weight	0.229 kg

Environment

Standards	EN/IEC 60947-5-1 EN/IEC 60204-1 EN/ISO 13850 EN 1088/ISO 14119
Product certifications	UL BG CSA
IP degree of protection	IP20 conforming to EN/IEC 60529 IP40 conforming to EN/IEC 60529
Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-25...75 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	211.0 g
Package 1 Height	4 cm
Package 1 width	11.5 cm
Package 1 Length	12.5 cm
Unit Type of Package 2	S02
Number of Units in Package 2	20
Package 2 Weight	4.584 kg
Package 2 Height	15 cm
Package 2 width	30 cm
Package 2 Length	40 cm
Package 3 Height	77 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes


RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
PVC free	Yes
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)

XPSAXE5120P is replaced by:

1x		Estop or guard ,Harmony XPS, connected to supply terminals 24 V AC/DC , no inputs, screw XPSBAC14AP
----	--	--