

Features

- Good tensile strength and surface quality
- Easy to work at high print speed
- User-friendly for both home and office environments
- Due to the low shrinkage, PLA will not deform after cooling
- Minimal thermal tension
- Minimal deformation

3D Printer Filament, PLA Silk RS PRO 2.85mm Slate Grey 1 Kg

RS Stock No.: 0430141



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

General Specifications

- *This product is used for: Products requiring a high level of detail and precision, jewellery creations, decorative pieces, architectural models.*

General Specifications

Printing Technology	FDM
Printing Material	PLA
Machine Specific	No
Colour	Slate Grey
For Use With	Common Desktop 3D Printers
Material Type	PLA
Print Speed	80 – 120 mm/s for 0.2mm layer height
Bed Prep	Glass/ Glue, BuildTak, Bluetape, Garolite

Mechanical Specifications

Diameter	2.85 mm
Weight	1 Kg
Specific gravity	1,24 g/cc
MFI	6,0 g/10 min
Tensile strength	45 MPa
Tensile Modulus	3500 Mpa
Impact strength	< 5 KJ/m ²
Tolerance	± 0.05mm
Roundness	≥ 95%
Strain at yield	5% (max)
Spool weight	224 gr
Spool size	20cm (D) x 68mm (h) & Hub diameter 52mm
Ovality Tolerance (Max)	± 5%

Operation Environment Specifications

Printing Temperature	190-230°C
Melting Temperature	155°C ± 10 °C
Melting Point	145-160°C
Glass transition Temperature	55 - 60 °C
Storage Temperature	15-25°C

Approvals

Compliance/Certifications	IEC / CE / CSA
Declarations	MFR Declaration of Conformity