

SPU61A series

v3.9

The SPU61A series of AC/DC switching mode power supplies provide 60 Watts of continuous output power. All models meet FCC Part-15 class B and CISPR-32 class B emission Limits and are designed to comply with UL/c-UL, TUV/GS and CE marking conformity assessment.

All units pass burn-in test at full load condition.



APPROVALS:



60W External Power Supply for General Purpose

FEATURES:

- * Wide Operating Voltage 90 to 264 VAC, 47 to 63 Hz
- * IEC-320-C14 Input Inlet
- * Optional Output Connector (See Page Appendix)
- * Single Output
- * Approved as Limited Power Source (LPS)
- * CoC v5 (Tier2)
- * 3-Year Warranty

APPLICATIONS:

- * POS System
- * AV Equipment
- * Industrial PC
- * Note PC
- * Charger
- * LED Lighting

GENERAL SPECIFICATION:

- * **Short Circuit Protection:** Auto Recovery
- * **Cooling:** Free Air Convection
- * **Protection Classes:** Class I
- * **Safety:** IEC 62368-1 Edition 2.0, IEC 62368-1 Edition 3.0, UL 62368-1, CAN/CSA-C22.2 NO.62368-1, EN 62368-1

Electrical Characteristics:



Characteristic	Condition	Min.	Typ.	Max.	Unit
Safety Approval Input Voltage Range	Safety Approval & Specification in Label	100		240	VAC
Input Operate Voltage Range	Detail to See Fig.1	90		264	VAC
Input Frequency	Sine Wave	47		63	Hz
Output Power Range	See Rating Chart			60	W
Low Line Input Current	Full Load, Vin=100VAC		1.4		A
High Line Input Current	Full Load, Vin=240VAC		0.8		A
High Line Input Inrush Current	Full Load, 25°C, Cool Start, Vin=240VAC			130	A
Safety Ground Leakage Current	Vin=264VAC, Fi=63Hz			0.75	mA
Touch Current	Vin=264VAC, Fi=63Hz			0.25	mA
Efficiency	Full Load, Vin=230VAC, Detail to See Rating Chart	See Rating Chart			
Line Regulation	Full Load, Vin=100~120VAC			1	%
Load Regulation	Vin=230VAC, 10~90% Load Change at Condition			5	%
Over Load Protection	Recovers Automatically After Fault Condition is Removed	110		150	%
Time of Transient Response	Io=Full Load to Half Load, Vin=110VAC			4	ms
Hold-Up Time	Full Load, Vin=110VAC	See Rating Chart			
Start-up time	Full Load, Vin=100~240VAC			3	s
Temperature Coefficient	Full load, Vin=100~240VAC			±0.04	%/°C
Dielectric Withstanding Voltage (P-S)	Primary to Secondary			4242	VDC
Dielectric Withstanding Voltage (P-G)	Primary to PE			2652	VDC
EMC Emission	Compliance to EN55032 (CISPR32)			B	Class

Environmental:


Characteristic	Condition	Min.	Typ.	Max.	Unit
Operating Temperature	Detail to See Fig.2 (Derate Linearly from 100% Load at 40°C to 50% Load at 70°C)	0		70	°C
Storage Temperature	0 ~ 95% RH	-40		85	°C
Operating Humidity	Non-Condensing	0		95%	RH
Storage Humidity		0		95%	RH
Electro Static Discharge	Air Discharge, IEC61000-4-2			8	kV
Electro Static Discharge	Contact Discharge, IEC61000-4-2			6	kV
Mean Time Between Failure	Operating Temperature at 25°C, Calculated per MIL-HDBK-217F	100k			h
Operating Altitude (Elevation)	All Condition			2000	m
Vibration	10 ~ 500Hz, 10min./1cycle, 60min. Each Along X, Y, Z Axes			5	G
Surge Voltage	Line-Neutral			1	kV
Surge Voltage	Line-PE & Neutral-PE			2	kV

SPECIFICATION NOTE :

1. Output can provide up to peak load when the power supply starts up. Continuous staying in more than rated load is not allowed.
2. At factory, in 60% rated load condition, each output is checked to be within voltage accuracy.
3. Line regulation is defined by changing $\pm 10\%$ of input voltage from nominal line at rated load.
4. Load regulation is defined by changing $\pm 40\%$ of measured output load from 60% rated load.
5. The ripple is measured from peak to peak with a bandwidth-limit of 20MHz (Measured at the output connector with a 0.1uF ceramic capacitor and a 47uF electrolytic capacitor).
6. Hold up time is measured from the end of the last charging pulse to the time which the main output drops down to low limit of main output at rated load and nominal line.
7. Efficiency is measured at rated load, and nominal line.

MECHANICAL DIMENSIONS: (UNIT: mm[inch])

(FIG.1) INPUT VOLTAGE DERATING CURVE



(FIG.2) TEMPERATURE DERATING CURVE

OUTPUT CABLE RECOMMEND :

1. Selected output connectors and wire, please refer to Appendix.
3. SPU61A-105~107 are required to use AWG#16/4FT output cable.
4. SPU61A-108~111 is required to use AWG#18/4FT output cable.
5. The regulation and efficiency will be changed by modified output cable.

PACKING :

1. Net weight: 340g approx.
2. Optional output connectors available contact sales for details.

Rating Chart:

MODEL NO.	Setting Voltage Range (Factory setting, can't be adjusted)		Output Current (Based on the output volt.)		Maximum Output Power	Ripple & Noise	Total Regulation	Typ. Efficiency @230A	Typ. 10% Load Efficiency	Typ. No Load Consumption	Hold-Up Time	Protection Mode
	min	max	min	max								
	(VDC)	(VDC)	(A)	(A)							(ms)	
SPU61A-105	12.0	13.0	4.61	5.00	60	100	±5	89	79	0.15	10	Hiccup
SPU61A-106	13.0	16.0	3.75	4.61	60	100	±5	89	79	0.15	10	Hiccup
SPU61A-107	16.0	21.0	2.85	3.75	60	110	±5	89	79	0.15	10	Hiccup
SPU61A-108	21.0	27.0	2.22	2.85	60	130	±3	89	79	0.15	10	Hiccup
SPU61A-109	27.0	33.0	1.81	2.22	60	160	±3	89	79	0.15	10	Hiccup
SPU61A-110	33.0	40.0	1.50	1.81	60	200	±3	89	79	0.15	10	Hiccup
SPU61A-111	40.0	48.0	1.25	1.50	60	240	±3	89	79	0.15	10	Hiccup