

# DE-9P-NR

## Product Details

Part Number	DE-9P-NR
Status	Active
Features	D-Sub Connector, 9 pos., Cable side connector
Number of Positions	9 pos.
Contact Pitch (mm)	
Rated Current (A)	5
Rated Voltage (V)	
Applicable Specifications	
Waterproof/ Non-waterproof	
Applications	
Connector Type	Cable side connector
Connector Style	
Contact Type	Pin
Wire Termination Style	Soldering
Applicable Wire Size (AWG)	#20 AWG max.
EMI Shielded	FALSE
PCB Mounting Style	
SMD Flag	
Shell Size	E
Applicable Wire Size (mm <sup>2</sup> )	0.52 Max.
Applicable Wire Size	
Dielectric Withstanding	

<b>Voltage (VACr.m.s. 1minute)</b>	1250
<b>Insulation Resistance (megaohm min.)</b>	5000
<b>Contact Resistance (milliohm max.)</b>	2.7
<b>Operating Temperature Range (deg. C)</b>	-55 to +105
<b>Shell Type</b>	Standard type
<b>Material of Insulator</b>	Glass-filled PBT (UL94V-0, Black)
<b>Contact</b>	With Contacts
<b>Finish of Contact in Connecting Area</b>	Gold plating
<b>Finish of Contact in PCB Mounting Area</b>	
<b>Mounting Method</b>	
<b>Screw Lock Assembly</b>	
<b>Existence of Ferrite</b>	FALSE
<b>Applicable Contacts</b>	
<b>Applicable Product Part Numbers</b>	
<b>Use with Accessories</b>	
<b>Accessory Type</b>	
<b>Documents</b>	<div style="display: flex; justify-content: space-around; align-items: center;"> <div style="border: 1px solid #ccc; padding: 5px; text-align: center;"> <b>Drawings</b> <a href="#">↓</a> </div> <div style="border: 1px solid #ccc; padding: 5px; text-align: center;"> <b>PDF Download</b> <a href="#">↓</a> </div> </div>
<b>Stock Search</b>	<div style="border: 1px solid #ccc; padding: 5px; display: inline-block;"> <b>Stock Search</b> <a href="#">&gt;</a> </div>
<b>RoHS compliant</b>	10 substances (2011/65/EU)
<b>REACH compliant</b>	219 substances (08/07/2021)

Environment Information	<div data-bbox="887 138 1206 215" style="border: 1px solid black; padding: 2px; display: inline-block;"> <b>RoHS/Reach Certificate</b> &gt; </div>
Combination	<p style="text-align: center;"> <a href="#">DE-9S-T-NR</a>  <a href="#">DE-9SA-NR</a>  <a href="#">DE-9S-RR</a>  <a href="#">DE-9SA-J4R</a>  <a href="#">DE-9SA-J4-2R</a>  <a href="#">DE-9SA-N-S1R</a>  <a href="#">DE-9S-TR</a>  <a href="#">DE-9S-T-N-S1R</a> </p>
Remarks	

### Notice

1. The values specified in this web site are only for reference. The products and their specifications are subject to change without notice. Contact our sales staff for further information before considering or ordering any of our products.

For purchase, a product specification must be agreed upon.

2. Users are requested to provide protection circuits and redundancy circuits to ensure safety of the equipment, and sufficiently review the suitability of JAE's products to the equipment.

3. The products presented in this web site are designed for the uses recommended below.

We strongly suggest you contact our sales staff when considering use of any of the products in any other way than the recommended applications or for a specific use that requires an extremely high reliability.

(1) Applications that require consultation:

\* Please contact us if you are considering use involving a quality assurance program that you specify or that is peculiar to the industry, such as:

Automotive electrical components, train control, telecommunications devices (mainline), traffic light control, electric power, combustion control, fire prevention or security systems, disaster evention equipment, etc.

\* We may separately give you our support with a quality assurance program that

you specify, when you think of a use such as :

Aviation or space equipment, submarine repeaters, nuclear power control systems, medical equipment for life support, etc.

(2) Recommended applications include:

\* Computers, office appliances, telecommunications devices (terminals, mobile units), measuring equipment, audiovisual equipment, home electric appliances, factory automation equipment, etc