



SIP QT24/10 Low Noise Compressor

The SIP QT24/10 Low Noise Compressor has an innovative quiet system for 59dB operation for higher noise reductions, plus fan-cooled twin motor and pump units for powerful performance.

- 230v input supply; 1.3hp (1kW) slow-running 4-pole brushless induction motor for long life
- Oil-free; for a high-quality clean air supply
- 24ltr receiver; 145psi (10bar) max. pressure
- 7.3CFM (206ltr/min) max. piston displacement
- 5.4CFM (153ltr/min) max. free air delivery (FAD)
- Twin cylinder motor and pump units; fan-cooled
- Built-in pressure cut-off switch and air regulator
- Wheel kit and handle for easy manoeuvrability
- Innovative quiet system offers 59dB operation; high noise reductions in every environment

SIP Industrial are machinery specialists, with the SIP catalogue of products including welding, metalwork, air compressors and tools, power, cleaning, charging, heating, automotive, and more.

Technical Description:

ITEM NO.	04381
Input Supply:	230v (13A)
Motor Power:	1.3hp (1kW) 4-POLE
Receiver Size:	24ltr
Piston Displacement:	7.30CFM (206ltr/min)
Free Air Delivery (FAD):	5.40CFM (153ltr/min)
Max. Air Pressure:	145psi (10bar)
Noise Level:	59dB
Net Weight:	
Gross Weight:	28.70kg
Product Dimensions:	600(H) x 337(W) x 711mm(D)
Packaged Dimensions:	575(H) x 260(W) x 583mm(D)