



ENCL25-6MM-A

Ruland ENCL25-6MM-A, 6mm Thin Line Shaft Collar, Aluminum, One-Piece
Clamp Style, 25mm OD, 6mm Width



Description

Ruland ENCL25-6MM-A is a one-piece thin line shaft collar with a 6mm bore, 25mm OD, and 6mm width. The narrow profile reduces weight and allows for use in confined spaces. It has the clamp style benefits of not marring the shaft, easy removability, and indefinite adjustability while commonly being used for guiding, spacing, stopping, mounting, and component alignment. Equipment manufacturers benefit from the tightly controlled face to bore perpendicularity (TIR of ? .05mm). Perpendicularity is critical for alignment when the shaft collar is used as a load bearing face, mechanical stop, or for mounting components such as gears or bearings. Proprietary processes have been developed by Ruland to maintain superior fit, finish, and holding power. ENCL25-6MM-A is stamped with the Ruland name for ease of identification. Forged screws test beyond DIN 912 12.9 standards to ensure maximum holding power. ENCL25-6MM-A is manufactured from solid bar stock sourced from select North American mills and machined to a fine burr free finish. Ruland uses high grade 2024 aluminum for increased screw seating torque. ENCL25-6MM-A is RoHS3 and REACH compliant and manufactured in our Marlborough, MA factory under strict controls using proprietary processes.

Product Specifications

Bore (B1)	6 mm	Bore Tolerance	+0.050 mm / +0.012 mm
Outer Diameter (OD)	25 mm	Clearance Diameter (C) MAX	27.25 mm
Width (W)	6 mm	Width Tolerance	+0.076 mm / -0.254 mm
Recommended Shaft Tolerance	+0.000 mm / -0.013 mm	Forged Clamp Screw	M2.5 x 8
Screw Material	Alloy Steel	Hex Wrench Size	2.0 mm
Screw Finish	Black Oxide	Seating Torque	1.21 Nm
Screw Location (R)	10.25 mm	Number of Screws	1 ea
Material Specification	2024-T351 Aluminum Bar	Finish Specification	Bright, No Plating
Manufacturer	Ruland Manufacturing	Country of Origin	USA
Temperature	-40°F to 225°F (-40°C to 107°C)	Weight (lbs)	0.016300
UPC	634529137987	Tariff Code	8483.60.8000
UNSPC	31162811		

Note 1	Performance ratings are for guidance only. The user must determine suitability for a particular application.
Prop 65	WARNING This product can expose you to the chemical Ethylene Thiourea, known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov .

Installation Instructions

1. Use the ENCL25-6MM-A thin line shaft collar as it is received.
2. Wipe the bore clean.
3. Apply a thin coat of light oil to the shaft.
4. Place the collar onto the desired shaft location and tighten it using a 2.0 mm hex wrench until a slight resistance is felt.
5. Wring collar into its final position and tighten the screw to the full recommended seating torque of 1.21 Nm using a 2.0 mm torque wrench.

