

Project..... Comments.....

Fixture Type..... Prepared By.....

Product Description:

Product Image:



Product Features:

- Rotatable end caps
- SMD LEDs
- High colour rendering index (Ra)80
- 360° Impact resistant frosted polycarbonate tube covers the aluminium heatsink
- LED Starter allows for safe lamp replacement (starter included)
- High power factor >0.90
- Suitable for use at -20° to +45°C
- 1kV surge protection
- Voltage range 100-240V
- Life to 70% lumen maintenance (L70) - 30,000 hours
- 4 Year Warranty - see www.auroralighting.com for details

Product Specs:

Input Voltage	100~240V AC
Input Frequency	50/60Hz
Power Factor	0.9
Operating Temp (Min-Max)	-30-45°C
Dimmable	No
Dimensions	1800mm (OL)
Number of LEDs	290

Compliance & Approvals:



✓ RoHS

SKU Table and Ordering

Cat. No.	Diffuser	Color	lm	Wattage	Lumens/Watt	Quantity
AU-XT81830FRB/65	Frosted	6500K	2600lm	31W	83.87	
AU-XT81830FRB/40	Frosted	4000K	2600lm	31W	83.87	

Warranty:

This product has a warranty period of 4 Years from the date of purchase. The warranty is invalid in the case of improper use, installation, tampering, and removal of the Q.C. date label; installation in an improper working environment or installation not according to the current edition of the National Electric Code. Should this product fail during the warranty period it will be replaced free of charge, subject to the correct installation of the original product and subsequent return of the faulty unit. Aurora does not accept responsibility for any installation costs associated with the replacement of this product and Aurora reserves the right to alter specifications without prior notice.

UK Sales

16 Alban Park Hatfield Road
St. Albans AL4 0JJ

United Kingdom

Tel : +44 (0) 1727 83 66 11

Fax : +44 (0) 1727 83 66 22

UK Distribution

Apex Park 6 Little Burrow
Welwyn Garden City AL7 4SW

United Kingdom

Tel : +44 (0) 1707 35 18 20

Fax : +44 (0) 1727 35 18 21