




EN ISO 20345:2011



RITMO

TIMBA
91294-04L
S1P SRC
Size: 35-42 Lady

Weight: 415 gr.

Fit: 11

Working Environment:

 Logistics and Light Industry,
 Components and Automotive, ESD
 Areas, Multipurpose


FEATURES

UPPER

 Drummed Suede Leather Hydro
 1,6-1,8 mm
 Mesh H.T. no ladder
 3D Air circulation 320 gr.

LINING

3D Air circulation 320 gr.

ANTISLIP LINING DUALMICRO

INSOLE

Five 4 Fit

TOE CAP

Alu SXT 2.0 Toe cap

RESISTANCE TO PERFORATION

KX Antiperforation PS

TYPE

Low Shoe

SOLE

PU / PU ESD-PLUS SRC

Double density PU sole, Outer- and in-between sole with ESD compound. For use in contact with sensitive electronic equipment. Light and comfortable, very versatile, highly non-slip SRC Antislip standard.

TECHNOLOGIES

Removable Insole



Highly breathable and absorbent anatomic insole. Multilayer structure to take advantage of the peculiarities of each component. Dry and with a comfortable memory foam "pillow"



Protection elements

ZERO(k)

ANTIPERFORATION

alu-sxt2.0

aluminium

A new aluminium multi-thicknesses toecap, which delivers a highly performing protection where needed. Resistant to impact of over 200J. Non Metallic anti-perforation insert. Resistant to over 1100 N with zero perforation.



Lateral stability

 dynamic **HC** control
 technology

Ergonomic rigid internal structure. It houses the heel into the right seat, adjusting the foot support and control of the ankle sideways movements. It keeps the foot tight to the shoe, allowing the perfect fit.



Torsional stability

STABIL•ACTIVE

Support made of rigid plastic material. It stabilizes the heel bone, the instep and tarsal joints, without altering energy absorption. A support for the natural movement of the foot; it provides comfort and greater stability.



Electrical features



ESD footwear discharge static electricity and avoid damaging surrounding objects; they are designed in compliance with the following standards: IEC EN 61340-5-1:2016 - IEC EN 61340-4-3:2018 - IEC EN 61340-4-5:2018.

Other

Strip with 4 filaments of carbon fiber, ensuring proven anti-static properties of the footwear over time.



SRC (SRA+SRB)


 SOLE 91
 PU - PU

SRA CERAMIC + DETERGENT SOLUTION	FLAT ≥0.32	0.54
	HEEL (CONTACT ANGLE °°) ≥0.28	0.52
SRB STEEL + GLYCEROL	FLAT ≥0.18	0.29
	HEEL (CONTACT ANGLE °°) ≥0.13	0.23

EN ISO 20344:2011