

LOC		DIST		REVISIONS					
CM	00	P	LTR	DESCRIPTION			DATE	DWN	APVD
			K	REVISED PER ECO-09-025490			17NOV09	HMR	MS

- 1



0.00076[.000030] MIN GOLD AT POINT OF MEASUREMENT IN THE LOCALIZED GOLD PLATE AREA, 0.00127[.000050] MIN TIN-LEAD IN TIN-LEAD PLATE AREA, 0.00127[.000050] MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.
- 2

WIRE RANGE: 3-6mm² [12-10 AWG].
- 3


DIMENSIONS IN BRACKETS ARE IN INCHES.
- 4

0.00076[.000030] MIN GOLD AT POINT OF MEASUREMENT IN THE LOCALIZED GOLD PLATE AREA, 0.00127[.000050] MIN TIN IN TIN PLATE AREA, 0.00127[.000050] MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.
- 5

THIS CONTACT HAS NO INSULATION BARREL.



SECTION A-A
SCALE 10:1



DETAIL A
SCALE 20:1

GOLD 4	0.30 [.012] PH BRZ	1-770003-0
GOLD 1	0.30 [.012] PH BRZ	770003-4
PRE-TIN	0.30 [.012] PH BRZ	770003-3
FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER	02APR04	Tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608			
		CHK C. JONES	02APR04				
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
		APVD C. JONES	02APR04	-			
		PRODUCT SPEC		PIN, UNIVERSAL MATE-N-LOK(TM) II			
		APPLICATION SPEC		-			
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
-		-		A2	00779	G-770003	-
CUSTOMER DRAWING				SCALE	4:1	SHEET	1 OF 1
				REV K			

