

Safety data sheet

according to 1907/2006/EC, Article 31 and 453/2010/EC

Printing date 28.04.2020

Version number 3

Revision: 28.04.2020

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifierTrade name: **ISO-Core "EL" SnPb, PbSn****Sn 60,0-67,0; Pb 33,0-60,0;****Sn63Pb37(E); Sn60Pb40(E); Sn50Pb50; Pb60Sn40****UFI:**

ISO-Core "EL"Sn60Pb40: 62K9-E004-E00S-K5H2

ISO-Core "EL"Sn63Pb37: RPT2-039D-G00X-0165

ISO-Core "EL"Sn50Pb50: 0RT2-G3YS-T00E-NCS7

ISO-Core "EL"Pb60Sn40: YUT2-03P6-300W-AQC9

**1.2 Relevant identified uses of the substance or mixture and uses advised against**

No further relevant information available.

Application of the substance / the mixture

Brazing alloy

Soldering flux

1.3 Details of the supplier of the safety data sheet**Manufacturer/Supplier:**

Felder GmbH

Im Lipperfeld 11

D-46047 Oberhausen

Tel.: +49 (0)208/ 85035-0

Fax.: +49 (0)208/ 26080

<http://www.felder.de>e-mail: info@felder.de**Further information obtainable from:**

lab

(mo-thu. 8:00 a.m. - 4:00 p.m./ fr. 8:00 a.m. - 1:00 p.m.)

email: mprobst@felder.de**1.4 Emergency telephone number:**

24 hr. emergency information:

Poison emergency call Berlin

"Giftnotruf Berlin"

Tel.: 0049-30-30686 790

Information which should have been included on the identification label.**(Annex I No. 1.3.4 REGULATION (EC) No 1272/2008)**

Metals in massive form, alloys, mixtures containing polymers and mixtures containing elastomers do not require a label according to this Annex, if they do not present a hazard to human health by inhalation, ingestion or contact with skin or to the aquatic environment in the form in which they are placed on the market, although classified as hazardous in accordance with the criteria of this Annex.

see chapter 2.2

EuPCS: PC-TEC-24

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture**Classification according to Regulation (EC) No 1272/2008**

GHS08 health hazard

Repr. 1A H360FD-H362 May damage fertility. May damage the unborn child. May cause harm to breast-fed children.

STOT RE 1 H372 Causes damage to organs through prolonged or repeated exposure.

2.2 Label elements**Labelling according to Regulation (EC) No 1272/2008**

The product is classified according to the CLP regulation. A label is not required (CLP Annex I, 1.3.4.1.)

The information according to CLP Annex I, 1.3.4.2. will be announced in section 2.2.

(Contd. on page 2)

— EU —

Safety data sheet

according to 1907/2006/EC, Article 31 and 453/2010/EC

Printing date 28.04.2020

Version number 3

Revision: 28.04.2020

Trade name: ISO-Core "EL" SnPb, PbSn
 Sn 60,0-67,0; Pb 33,0-60,0;
 Sn63Pb37(E); Sn60Pb40(E); Sn50Pb50; Pb60Sn40

(Contd. of page 1)

Hazard pictograms

GHS08

Signal word *Danger***Hazard-determining components of labelling:***lead***Hazard statements***H360FD-H362 May damage fertility. May damage the unborn child. May cause harm to breast-fed children.**H372 Causes damage to organs through prolonged or repeated exposure.***Precautionary statements***P260 Do not breathe dust/fume/gas/mist/vapours/spray.**P263 Avoid contact during pregnancy and while nursing.**P264 Wash thoroughly after handling.**P280 Wear protective gloves/protective clothing/eye protection/face protection.**P405 Store locked up.**P501 Dispose of contents/container in accordance with local/regional/national/international regulations.***Additional information:***Contains Rosin. May produce an allergic reaction.**Restricted to professional users.***2.3 Other hazards****Results of PBT and vPvB assessment****PBT:** *Not applicable.***vPvB:** *Not applicable.*

SECTION 3: Composition/information on ingredients

3.2 Chemical characterisation: Mixtures**Description:** *Mixture: consisting of the following components.*

Dangerous components:			
CAS: 7440-31-5 EINECS: 231-141-8 Reg.nr.: 01-2119486474-28	<i>tin</i>	<i>substance with a Community workplace exposure limit</i>	<67%
CAS: 7439-92-1 EINECS: 231-100-4 Reg.nr.: 01-2119513221-59	<i>lead</i>	<i>Repr. 1A, H360FD-H362; STOT RE 1, H372</i>	<60%
CAS: 8050-09-7 EINECS: 232-475-7 Reg.nr.: 01-2119480418-32	<i>Rosin</i>	<i>Skin Sens. 1, H317</i>	<1%

SVHC7439-92-1 | *lead***Additional information:** *For the wording of the listed hazard phrases refer to section 16.*

SECTION 4: First aid measures

4.1 Description of first aid measures**General information:** *Take affected persons out into the fresh air.***After inhalation:** *Supply fresh air; consult doctor in case of complaints.***After skin contact:***After contact with the molten product, cool rapidly with cold water.**Do not pull solidified product off the skin.**Seek medical treatment.***After eye contact:** *Seek medical treatment.***After swallowing:***Rinse out mouth and then drink plenty of water.**Seek medical treatment.***4.2 Most important symptoms and effects, both acute and delayed** *No further relevant information available.*

(Contd. on page 3)

Safety data sheet

according to 1907/2006/EC, Article 31 and 453/2010/EC

Printing date 28.04.2020

Version number 3

Revision: 28.04.2020

Trade name: ISO-Core "EL" SnPb, PbSn
 Sn 60,0-67,0; Pb 33,0-60,0;
 Sn63Pb37(E); Sn60Pb40(E); Sn50Pb50; Pb60Sn40

(Contd. of page 2)

4.3 Indication of any immediate medical attention and special treatment needed
 No further relevant information available.

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing agents: Use fire extinguishing methods suitable to surrounding conditions.

5.2 Special hazards arising from the substance or mixture No further relevant information available.

5.3 Advice for firefighters

Protective equipment:

Wear self-contained respiratory protective device.

Do not inhale explosion gases or combustion gases.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

Ensure adequate ventilation

Use respiratory protective device against the effects of fumes/dust/aerosol.

6.2 Environmental precautions: Do not allow to penetrate the ground/soil.

6.3 Methods and material for containment and cleaning up:

Allow to solidify. Pick up mechanically.

Dispose contaminated material as waste according to item 13.

6.4 Reference to other sections

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Extractors are required on all machines used for thermal processing or splinter removal processes.

Provide suction extractors if dust is formed.

Any unavoidable deposit of dust must be regularly removed.

Use appropriate industrial vacuum cleaners or central vacuum systems for dust removal.

Information about fire - and explosion protection: No special measures required.

7.2 Conditions for safe storage, including any incompatibilities

Storage:

Requirements to be met by storerooms and receptacles: No special requirements.

Information about storage in one common storage facility:

Store away from foodstuffs.

Do not store together with oxidising and acidic materials.

Further information about storage conditions: Store in dry conditions.

Storage class: 6.1 D

7.3 Specific end use(s) No further relevant information available.

SECTION 8: Exposure controls/personal protection

Additional information about design of technical facilities: No further data; see item 7.

8.1 Control parameters

Ingredients with limit values that require monitoring at the workplace:

7440-31-5 tin

MAK (Germany) | vgl. Abschn. IIb

7439-92-1 lead

AGW (EU) | Long-term value: 0.15 mg/m³

BOELV (EU) | Long-term value: 0.15 mg/m³
as Pb

MAK (Germany) | vgl. Abschn. XII

(Contd. on page 4)

Safety data sheet

according to 1907/2006/EC, Article 31 and 453/2010/EC

Printing date 28.04.2020

Version number 3

Revision: 28.04.2020

Trade name: ISO-Core "EL" SnPb, PbSn
Sn 60,0-67,0; Pb 33,0-60,0;
Sn63Pb37(E); Sn60Pb40(E); Sn50Pb50; Pb60Sn40

(Contd. of page 3)

8050-09-7 Rosin

MAK (Germany) vgl. Abschn. IV

Regulatory information

MAK (Germany): MAK- und BAT-Liste

BOELV (EU): 98/24/EG

recommended monitoring procedures in accordance with 453/2010/EU no. 8.1.2:

7439-92-1 lead: NIOSH 7702(E), OSHA 1006(E), OSHA ID-206(E)

Ingredients with biological limit values:**7439-92-1 lead**

BAT (EU) 70 µg/dl

blood

lead

BGW (Germany) 300 µg/l

Untersuchungsmaterial: Vollblut

Probennahmezeitpunkt: keine Beschränkung

Parameter: Blei Frauen < 45 J.

400 µg/l

Untersuchungsmaterial: Vollblut

Probennahmezeitpunkt: keine Beschränkung

Parameter: Blei

Regulatory information BGW (Germany): TRGS 903**Additional information:** The lists valid during the making were used as basis.**8.2 Exposure controls****Appropriate engineering controls:**

Ensure adequate ventilation.

Remove the fumes by means of suitable suction devices.

Personal protective equipment:**General protective and hygienic measures:**

Pregnant women should strictly avoid inhalation or skin contact.

Do not eat, drink, smoke or sniff while working.

Keep away from foodstuffs, beverages and feed.

Wash hands before breaks and at the end of work.

Store protective clothing separately.

Respiratory protection:

Use suitable respiratory protective device in case of insufficient ventilation.

Filter P3

Protection of hands:

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

Material of gloves

heat-resistant glove with nitrile inner glove.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and

varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material cannot be calculated in advance and has therefore to be checked prior to the application.

Recommended thickness of the material: ≥ 0.2 mm**Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

The determined penetration times according to EN 16523-1:2015 are not performed under practical conditions.

Therefore a maximum wearing time, which corresponds to 50% of the penetration time, is recommended.

Value for the permeation: Level ≤ 6 **Eye protection:** in cases of application: protective goggles**Body protection:** Protective work clothing**SECTION 9: Physical and chemical properties****9.1 Information on basic physical and chemical properties****General Information****Appearance:****Form:**

Solid

Colour:

Silver-coloured

(Contd. on page 5)

EU

Safety data sheet

according to 1907/2006/EC, Article 31 and 453/2010/EC

Printing date 28.04.2020

Version number 3

Revision: 28.04.2020

Trade name: ISO-Core "EL" SnPb, PbSn
 Sn 60,0-67,0; Pb 33,0-60,0;
 Sn63Pb37(E); Sn60Pb40(E); Sn50Pb50; Pb60Sn40

(Contd. of page 4)

Odour:	<i>Characteristic</i>
Odour threshold:	<i>Not determined.</i>
pH-value:	<i>Not applicable.</i>
Change in condition	
Melting point/freezing point:	<i>183-235 °C</i>
Initial boiling point and boiling range:	<i>Undetermined.</i>
Flash point:	<i>Not applicable.</i>
Flammability (solid, gas):	<i>Not determined.</i>
Decomposition temperature:	<i>Not determined.</i>
Auto-ignition temperature:	<i>Product is not selfigniting.</i>
Explosive properties:	<i>Product does not present an explosion hazard.</i>
Explosion limits:	
Lower:	<i>Not determined.</i>
Upper:	<i>Not determined.</i>
Vapour pressure:	<i>Not applicable.</i>
Density:	<i>Not determined.</i>
Relative density	<i>Not determined.</i>
Vapour density	<i>Not applicable.</i>
Evaporation rate	<i>Not applicable.</i>
Solubility in / Miscibility with water:	
	<i>Insoluble.</i>
Partition coefficient: n-octanol/water:	<i>Not determined.</i>
Viscosity:	
Dynamic:	<i>Not applicable.</i>
Kinematic:	<i>Not applicable.</i>
Solvent content:	
VOC (EC)	<i>0,00 %</i>
Solids content:	<i>100.0 %</i>
9.2 Other information	<i>No further relevant information available.</i>

SECTION 10: Stability and reactivity

10.1 Reactivity *No further relevant information available.*

10.2 Chemical stability

Thermal decomposition / conditions to be avoided:

No decomposition if used and stored according to specifications.

10.3 Possibility of hazardous reactions

Toxic fumes may be released if heated above the decomposition point.

Reacts with acids, alkalis and oxidising agents.

Develops toxic gases/fumes.

10.4 Conditions to avoid *No further relevant information available.*

10.5 Incompatible materials: *No further relevant information available.*

10.6 Hazardous decomposition products:

Toxic metal oxide smoke

Leadoxide vapour

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute toxicity *Based on available data, the classification criteria are not met.*

Primary irritant effect:

Skin corrosion/irritation *Based on available data, the classification criteria are not met.*

Serious eye damage/irritation *Based on available data, the classification criteria are not met.*

Respiratory or skin sensitisation *Based on available data, the classification criteria are not met.*

CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)

Germ cell mutagenicity *Based on available data, the classification criteria are not met.*

Carcinogenicity *Based on available data, the classification criteria are not met.*

Reproductive toxicity

May damage fertility. May damage the unborn child. May cause harm to breast-fed children.

STOT-single exposure *Based on available data, the classification criteria are not met.*

(Contd. on page 6)

Safety data sheet

according to 1907/2006/EC, Article 31 and 453/2010/EC

Printing date 28.04.2020

Version number 3

Revision: 28.04.2020

Trade name: ISO-Core "EL" SnPb, PbSn
 Sn 60,0-67,0; Pb 33,0-60,0;
 Sn63Pb37(E); Sn60Pb40(E); Sn50Pb50; Pb60Sn40

(Contd. of page 5)

STOT-repeated exposure*Causes damage to organs through prolonged or repeated exposure.***Aspiration hazard** *Based on available data, the classification criteria are not met.***SECTION 12: Ecological information****12.1 Toxicity****Aquatic toxicity:** *No further relevant information available.***12.2 Persistence and degradability** *No further relevant information available.***12.3 Bioaccumulative potential** *No further relevant information available.***12.4 Mobility in soil** *No further relevant information available.***Additional ecological information:****General notes:***The product contains heavy metals. Avoid transfer into the environment. Specific preliminary treatments are necessary. Not hazardous for water.***12.5 Results of PBT and vPvB assessment****PBT:** *Not applicable.***vPvB:** *Not applicable.***12.6 Other adverse effects** *No further relevant information available.***SECTION 13: Disposal considerations****13.1 Waste treatment methods****Recommendation***Contact manufacturer for recycling information.**Must not be disposed together with household garbage. Do not allow product to reach sewage system.***European waste catalogue***17 04 09*: metal waste contaminated with hazardous substances**HP 5: Specific Target Organ Toxicity (STOT)/Aspiration Toxicity**HP 10: Toxic for reproduction**spool:**15 01 02: plastic packaging**packaging:**15 01 01: paper and cardboard packaging***Uncleaned packaging:** *void.***Recommendation:** *Disposal must be made according to official regulations.***SECTION 14: Transport information****14.1 UN-Number****ADR, ADN, IMDG, IATA**

Void

14.2 UN proper shipping name**ADR, ADN, IMDG, IATA**

Void

14.3 Transport hazard class(es)**ADR, ADN, IMDG, IATA****Class**

Void

14.4 Packing group**ADR, IMDG, IATA**

Void

14.5 Environmental hazards:**Marine pollutant:**

No

14.6 Special precautions for user*Not applicable.***14.7 Transport in bulk according to Annex II of Marpol****and the IBC Code***Not applicable.***UN "Model Regulation":**

Void

SECTION 15: Regulatory information**15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture****Directive 2012/18/EU****Named dangerous substances - ANNEX I** *None of the ingredients is listed.*

(Contd. on page 7)

Safety data sheet

according to 1907/2006/EC, Article 31 and 453/2010/EC

Printing date 28.04.2020

Version number 3

Revision: 28.04.2020

Trade name: ISO-Core "EL" SnPb, PbSn
Sn 60,0-67,0; Pb 33,0-60,0;
Sn63Pb37(E); Sn60Pb40(E); Sn50Pb50; Pb60Sn40

(Contd. of page 6)

REGULATION (EC) No 1907/2006 ANNEX XVII *Conditions of restriction: 63, 30*

National regulations:

Additional classification according to Decree on Hazardous Materials, Annex II:

Can cause cancer if present as respirable dust.

Information about limitation of use:

Employment restrictions concerning pregnant and lactating women must be observed.

Employment restrictions concerning women of child-bearing age must be observed.

Employment restrictions concerning juveniles must be observed.

Waterhazard class: *Generally not hazardous for water.*

Other regulations, limitations and prohibitive regulations

Substances of very high concern (SVHC) according to REACH, Article 57

7439-92-1	lead
-----------	------

15.2 Chemical safety assessment: *A Chemical Safety Assessment has not been carried out.*

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

Reasons for changes:

02.07.2018: section 3 SVHC

28.04.2020: section 1

Relevant phrases

H317 May cause an allergic skin reaction.

H360FD May damage fertility. May damage the unborn child.

H362 May cause harm to breast-fed children.

H372 Causes damage to organs through prolonged or repeated exposure.

Recommended restriction of use *For commercial use only.*

Contact: *Dr. M. Probst*

Abbreviations and acronyms:

RID: Règlement international concernant le transport des marchandises dangereuses par chemin de fer (Regulations Concerning the International Transport of Dangerous Goods by Rail)

ICAO: International Civil Aviation Organisation

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

GHS: Globally Harmonised System of Classification and Labelling of Chemicals

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

VOC: Volatile Organic Compounds (USA, EU)

PBT: Persistent, Bioaccumulative and Toxic

SVHC: Substances of Very High Concern

vPvB: very Persistent and very Bioaccumulative

Skin Sens. 1: Skin sensitisation – Category 1

Repr. 1A: Reproductive toxicity – Category 1A

STOT RE 1: Specific target organ toxicity (repeated exposure) – Category 1

Safety data sheet SD3460