PZTA92T1G, NSVPZTA92T1G

High Voltage Transistor

PNP Silicon

Features

- Complement to PZTA42T1G
- NSV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb–Free, Halogen Free/BFR Free and are RoHS Compliant

MAXIMUM RATINGS ($T_C = 25^{\circ}C$ unless otherwise noted)

Rating	Symbol	Value	Unit
Collector-Emitter Voltage	V _{CEO}	-300	Vdc
Collector-Base Voltage	V _{CBO}	-300	Vdc
Emitter-Base Voltage	V _{EBO}	-5.0	Vdc
Collector Current	Ic	-500	mAdc
Total Power Dissipation up to @ T _A = 25°C (Note 1)	P _D	1.5	W
Storage Temperature Range	T _{stg}	-65 to +150	°C
Junction Temperature	TJ	150	°C

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

1. Device mounted on a FR-4 glass epoxy printed circuit board 1.575 in x 1.575 in x 0.0625 in; mounting pad for the collector lead = 0.93 sq in.

THERMAL CHARACTERISTICS

Characteristic	Symbol	Max	Unit
Thermal Resistance, Junction-to-Ambient (Note 2)	$R_{\theta JA}$	83.3	°C/W

2. Device mounted on a FR-4 glass epoxy printed circuit board 1.575 in x 1.575 in x 0.0625 in; mounting pad for the collector lead = 0.93 sq in.




ON Semiconductor®

http://onsemi.com

SOT-223 PACKAGE PNP SILICON HIGH VOLTAGE TRANSISTOR SURFACE MOUNT

COLLECTOR 2,4




EMITTER 3



SOT-223 CASE 318E STYLE 1

MARKING DIAGRAM



P2D = Specific Device Code

A = Assembly Location

/ = Year

W = Work Week

= Pb-Free Package

(Note: Microdot may be in either location)

ORDERING INFORMATION

Device	Package	Shipping [†]
PZTA92T1G	SOT-223 (Pb-Free)	1,000 / Tape & Reel
NSVPZTA92T1G	SOT-223 (Pb-Free)	1,000 / Tape & Reel

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.

PZTA92T1G, NSVPZTA92T1G

ELECTRICAL CHARACTERISTICS ($T_A = 25^{\circ}C$ unless otherwise noted)

Characteristics	Symbol	Min	Max	Unit
OFF CHARACTERISTICS	<u>.</u>			
Collector–Emitter Breakdown Voltage (Note 3) (I _C = -1.0 mAdc, I _B = 0)	V _{(BR)CEO}	-300	-	Vdc
Collector–Base Breakdown Voltage (I _C = –100 μAdc, I _E = 0)	V _(BR) CBO	-300	-	Vdc
Emitter-Base Breakdown Voltage ($I_E = -100 \mu Adc, I_C = 0$)	V _{(BR)EBO}	V _{(BR)EBO} –5.0		Vdc
Collector-Base Cutoff Current (V _{CB} = -200 Vdc, I _E = 0)	I _{CBO}	-	-0.25	μAdc
Emitter-Base Cutoff Current (V _{BE} = -3.0 Vdc, I _C = 0)	I _{EBO}	-	-0.1	μAdc
ON CHARACTERISTICS	•	•	•	•
DC Current Gain	h _{FE}	25 40 40	- - -	-
Saturation Voltages ($I_C = -20 \text{ mAdc}$, $I_B = -2.0 \text{ mAdc}$) ($I_C = -20 \text{ mAdc}$, $I_B = -2.0 \text{ mAdc}$)	V _{CE(sat)} V _{BE(sat)}	- -	-0.5 -0.9	Vdc
DYNAMIC CHARACTERISTICS	<u>.</u>			
Collector–Base Capacitance @ f = 1.0 MHz (V _{CB} = -20 Vdc, I _E = 0)	C _{cb}	-	6.0	pF
Current–Gain – Bandwidth Product (I _C = -10 mAdc, V _{CE} = -20 Vdc, f = 100 MHz)	f _T	50	-	MHz
		•	•	•

^{3.} Pulse Test Conditions, t_p = 300 $\mu s, \, \delta$ 0.02.





Figure 1. DC Current Gain

PZTA92T1G, NSVPZTA92T1G







Figure 2. Capacitance

Figure 3. Current-Gain - Bandwidth






Figure 4. "ON" Voltages






Figure 5. Safe Operating Area

PZTA92T1G, NSVPZTA92T1G

PACKAGE DIMENSIONS

SOT-223 (TO-261) CASE 318E-04 ISSUE N






IOTES:

- 1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
- 2. CONTROLLING DIMENSION: INCH.

	MILLIMETERS			INCHES		
DIM	MIN	NOM	MAX	MIN	NOM	MAX
Α	1.50	1.63	1.75	0.060	0.064	0.068
A1	0.02	0.06	0.10	0.001	0.002	0.004
b	0.60	0.75	0.89	0.024	0.030	0.035
b1	2.90	3.06	3.20	0.115	0.121	0.126
С	0.24	0.29	0.35	0.009	0.012	0.014
D	6.30	6.50	6.70	0.249	0.256	0.263
E	3.30	3.50	3.70	0.130	0.138	0.145
е	2.20	2.30	2.40	0.087	0.091	0.094
e1	0.85	0.94	1.05	0.033	0.037	0.041
L	0.20			0.008		
L1	1.50	1.75	2.00	0.060	0.069	0.078
HE	6.70	7.00	7.30	0.264	0.276	0.287
θ	0°	-	10°	0°	-	10°

STYLE 1:

- PIN 1. BASE
 - COLLECTOR
 EMITTER
 - 3. EMITTER 4. COLLECTOR



*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of SCILLC's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless againstal claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA **Phone**: 303–675–2175 or 800–344–3860 Toll Free USA/Canada

Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800-282-9855 Toll Free USA/Canada

Europe, Middle East and Africa Technical Support:
Phone: 421 33 790 2910

Japan Customer Focus Center
Phone: 81–3–5817–1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative